




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlocks**

Screw Length: **12.7 mm [.5 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlocks

Mechanical Attachment

Screwlock Style	Screwlock Only
Mating Thread Size	14702
Screw & Hole Thread Size	4-40 UNC 2B (Female), M3 (Male)
Screw Length	12.7 mm[.5 in]

Dimensions

Thread Length	7.9 mm[.311 in]
---------------	-----------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Carton

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------





EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 174888-1 AMPLIMITE SCREWLOCK M3	 TE Part # 829261-5 SCHRAUBENSICHERUNG
--	---

Also in the Series | [AMPLIMITE Kit](#)



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Customers Also Bought



TE Part #1658543-2
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



TE Part #1609989-6
CORCOM BCF SERIES 3-PHASE FILTERS



TE Part #1-1337452-0
BNC Ins BHSkt 50Ohm Nickel Gol



TE Part #167501-2
FEMALE SCREWLOCK




TE Part #1-829261-6
HD FEMALE SCREWLOCK



TE Part #1-1879133-1
RN 0603 1K02 0.1% 10PPM 1K RL




TE Part #1676153-2
RN 0805 10K 0.1% 10PPM 1KRL



TE Part #926010-1
LOCKING CLIP HSG



TE Part #187752-000
CR-107-LSR



TE Part #1487588-1
USB, A-B, 28/24, WHITE, 2.0M

Documents

Product Drawings
HD FEMALE SCREWLOCK

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_829261-6_J.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_829261-6_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_829261-6_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[MD_829261-6_033020181156_dmtec](#)

English

[MD_829261-6_033020181156_dmtec](#)

English