



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Strain Relief**
Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Strain Relief
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment

Mating Connector Lock	Without
Mounting Angle	None
PCB Mount Retention Type	None

Dimensions

Length	53.6 mm
--------	---------

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5390377-7
68 POS A/P PLUG 25 CL 30AU

Also in the Series | AMPLIMITE 0.50 Series



D-Sub Backshells & Clamps(31)



D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(77)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(196)

Customers Also Bought



TE Part #806823-000
Bulbous Heat Shrink Boots: Lipped, Right Angle



TE Part #1437024-5
Female Socket Connectors: Strain Relief



TE Part #1393260-6
Forced Guided Relay, Reinforced Insulate



TE Part #1648211-1
423-0001-01100



TE Part #103688-2
03 MTE RCPT HSG SR PLAIN .100




TE Part #1676257-1
RN 0805 22K1 0.1% 10PPM CUT LENGTH



TE Part #1676315-1
RN 0805 36K5 0.1% 10PPM CUT LENGTH



TE Part #1571527-1
FSM2JSML=TACT SWITCH,SMT,BULK



TE Part #102448-8
20 AMPMODU MT ASSY DR .100CL



TE Part #1-2333149-5
DYNAMIC 1100D REC HSG 10P X BLACK 33%GF

Documents

Product Drawings
068 50SR STRAIN RELIEF
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_787043-7_F.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_787043-7_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_787043-7_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - .050 Series Connector](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Instruction Sheets

[Customer Manual \(U.S.\)](#)

English