




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlocks**

Screw Length: **9.65 mm [.38 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlocks

Mechanical Attachment

Screwlock Style	Screwlock Only
Screw & Hole Thread Size	2-56 UNC (Female), 4-40 UNC (Male)
Screw Length	9.65 mm[.38 in]

Dimensions

Thread Length	4.39 mm[.173 in]
---------------	------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag, Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-020-ADRV127
AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm

TE Part # CAT-018-DRARA127
D-Sub Receptacle Assembly: Right Angle, 1.27mm


TE Part # CAT-020-DRAVAP127
D-Sub Receptacle Assembly: Vertical, Action Pin, 1.27mm

TE Part # CAT-AM7-436507
IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm

TE Part # CAT-AM7-4365072
IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm

TE Part # 749066-3
50SR SCREWLOCK,SS

Also in the Series | **AMPLIMITE 0.50 Series**



D-Sub Backshells & Clamps(31)



D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(77)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(196)

Customers Also Bought



TE Part #2-767004-2
MICT,RECPT,038,ASSY,.025,REC



TE Part #1658685-1
HDP-22,RCPT,SIZE 5,78 POSN



TE Part #1888371-1
MJ,2X1RJ45+2USB,BLACK,NOLED



TE Part #2-1879215-6
CPF 0402 7K32 0.1% 25PPM 1K RL



TE Part #1622818-1
RH73 2A 10M 5% 250PPM



TE Part #152873
14-12 PIDG NYLON RT NO 8 WHITE



TE Part #1624112-4
3650 0603 27nH 5% 2K RL



TE Part #DT04-12PA-LE09
DEUTSCH DT Series Housings & Connectors



TE Part #2-1571551-2
DIP Socket: Standard, Stamped & Formed, Closed, Gold Flash



TE Part #1423158-1
7012L10BN=RLY,NAV,ON,2P,440VA

Documents



Product Drawings

50SR SCREWLOCK KIT,FEMALE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_749087-2_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_749087-2_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_749087-2_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - .050 Series Connector

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_749087-2_052120181213_dmtec

English

MD_749087-2_052120181213_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English