




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlocks**

Screw Length: **14.27 mm [.562 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlocks

Mechanical Attachment

Screwlock Style	Screwlock Only
Screw & Hole Thread Size	2-56 UNC (Female), 4-40 UNC (Male)
Screw Length	14.27 mm[.562 in]

Dimensions

Thread Length	9.02 mm[.355 in]
---------------	------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag, Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-020-ADRV127
AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm


TE Part # CAT-018-DRARA127
D-Sub Receptacle Assembly: Right Angle, 1.27mm

TE Part # CAT-020-DRAVAP127
D-Sub Receptacle Assembly: Vertical, Action Pin, 1.27mm

TE Part # CAT-AM7-436507
IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm

TE Part # CAT-AM7-4365072
IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm

Also in the Series | **AMPLIMITE 0.50 Series**



D-Sub Backshells & Clamps(31)



D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(77)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(196)

Customers Also Bought



TE Part #205560-2
AMPLIMITE,ASY,PLUG,STD,109,3



TE Part #2-767004-2
MICT,RECPT,038,ASSY,.025,REC




TE Part #221789-1
JACK,PCB,SERIES SMA




TE Part #1676359-2
RN 0805 4K53 0.1% 10PPM 1KRL



TE Part #786585-2
50SR SCREWLOCK KIT,FEMALE



TE Part #103906-7
08 MTE HDR SRRA LATCH .100CL



TE Part #208010-2
D-Sub Plug Assembly: Vertical, Shell Size 5, 2.74mm



TE Part #1410946-2
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW



TE Part #1825006-5
GDS0404=DIP SW,SLIDE,THRU/HL



TE Part #1-750877-9
100 50SR TERMINATOR COVER

Documents



Product Drawings

50SR SCREWLOCK KIT,FEMALE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_749087-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_749087-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_749087-1_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - .050 Series Connector

English

AMPLIMITE .050 Series D-sub Connectors QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English