




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Jackscrew**
Screw Length: **48.77 mm [1.92 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Jackscrew

Mechanical Attachment

Screw Finish	None
Screw & Hole Thread Size	4-40
Screw Length	48.77 mm[1.92 in]

Packaging Features

Packaging Quantity	1, 2
Packaging Method	Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021 (211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1393561-8
V42254A 262V 18=SUB D SCHRAUBE



TE Part # 747784-4
JACKSCREW KIT,4-40, BULK

Also in the Series | AMPLIMITE Kit



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Customers Also Bought



TE Part #207463-1
D-Sub Crimp Recpt Signal 25 Posn,
Socket Size 20, Shell Size 3

TE Part #1658670-2
D-Sub Connector Contacts: Pin, Brass,
Signal, Size 22

TE Part #102387-1
10 MODIV HSG COMP DR .100 POL

TE Part #102387-3
16 MODIV HSG COMP DR .100 POL

TE Part #184235-1
RECEPT,PIDG FASTON 16-14 187

TE Part #1-1414631-0
RESOLVER V23401-S1001-B101

TE Part #205206-3
D-Sub Crimp: Plug, Signal, 15 Posn,
Pin Size 20, Shell Size 2

TE Part #1-1377173-5
SMP 0-0327043-0

TE Part #YDIV44E21-11PNC009
RECP ASSY

TE Part #1877519-1
Dust Cover,24 Position

Documents

Product Drawings

AMPLI JACKSCREW 4-40 KIT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_747784-3_U.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_747784-3_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_747784-3_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance



[MD_747784-3_04032018111_dmtec](#)

English

[MD_747784-3_04032018111_dmtec](#)

English