




Connectors > Circular Connectors > Circular Connector Accessories > Unscreened Circular Connector Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Clamp**
Compatible With Circular Connector Shell Size: **11**
Body Orientation: **Right Angle**
Accepts Cable Diameter (Max): **11.51 mm [.453 in]**
Protective Cover: **With**

Features

Product Type Features

Product Type	Accessory
Backshell & Clamp Accessory Type	Cable Clamp
Protective Cover	With

Body Features

Strain Relief Type	Right Angle
Strain Relief Color	Black
Cable Clamp Material	Nylon
Strain Relief Material	Thermoplastic
Cable Clamp Color	Black

Mechanical Attachment

Screw & Hole Thread Size	3/4-20 UNEF-2B
--------------------------	----------------

Housing Features

Body Orientation	Right Angle
------------------	-------------

Dimensions

Accepts Cable Diameter (Max)	11.51 mm[.453 in]
------------------------------	-------------------

Operation/Application

Compatible With Circular Connector Shell Size	11
---	----

Packaging Features

--	--



Packaging Quantity	1
Packaging Method	Bag

Other

Comment	Screw finish is zinc plated non-hexavalent chromate, With Cover.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # CAT-AM71-C83998EE
MINI CPC

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)




Circular Connector Seals(36)



Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #1-66358-6
TYPE III CONTACTS STRIP



TE Part #1-2273083-3
M12 A-CODE FEMALE R/A PIGTAIL



TE Part #86561-4
2.54mm FFC Connectors Pin Contacts



TE Part #1-5225398-5
DUAL CRIMP BNC BLKHD JACK



TE Part #1-794617-0
10POS,MICRO MNL,RCPT HSG

TE Part #1-5227079-9
COMM BNC PLUG

TE Part #1445420-2
SEAL,FLANGE,SIZE 11

TE Part #103682-5
06 MTE PANEL MOUNT SR

TE Part #104503-3
04 MTE PIN HSG SR RIB .100CL

Documents

Product Drawings

R/A CABLE CLAMP KIT,SZ 11, MINI CPC

English

CAD Files

Customer View Model

ENG_CVM_1546746-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_1546746-4_C.3d_stp.zip

English

Customer View Model

ENG_CVM_1546746-4_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773902-9_CPC_Catalog

German

1-1773902-9_CPC_Catalog

English

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

1-1773902-9_CPC_Catalog

Japanese



[1-1773902-9_CPC_Catalog](#)