



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 747784-8

JACKSCREW KIT,4-40, BULK

Customers Also Bought

TE Part #1-747944-6

IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm

TE Part #1658641-1

D-Sub Crimp: Plug, Signal, 50 Posn, Pin Size 20, Shell Size 5

TE Part #1-216093-0

AMP-LATCH PRE-ASSY DIL WITHO

TE Part #1-1658622-0

50 NOVO MIL/CTR 30DP,LEAD FREE

TE Part #1658622-8

34 NOVO MIL/CTR 30DP,LEAD FREE

TE Part #1-1478401-0

BNC Str Plg PS 50Ohm Silver RG58C /U, 141

TE Part #1310851-1

B65N07G999X,SMB PCB VERT SOCKET

TE Part #1218441-2

R/A PLG ASSY 15 POS SER 109

TE Part #131332

PIDG TABS

TE Part #NB15932001

RT-375-1/16-X-STK

Documents

Product Drawings

609-002=HDW IDC JACKSCREW ASSY

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1437012-5_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437012-5_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437012-5_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English