



TE Internal #: 2299806-1
IC Socket Covers, Metric PQFP / LGA 3647 Compatible With IC
Socket Type, Carrier, Operating Temperature Range -25 – 100 °C
[-13 – 212 °F]
[View on TE.com >](#)

Connectors > Socket Connectors > IC & Component Socket Accessories > IC Socket Covers



Compatible With IC Socket Type: **LGA 3647, Metric PQFP**
Card & Socket Accessory Type: **Carrier**
Operating Temperature Range: **-25 – 100 °C [-13 – 212 °F]**

Features

Product Type Features

Card & Socket Accessory Type	Carrier
------------------------------	---------

Body Features

Color	Black
Cover Material	PC + ABS

Contact Features

Compatible With IC Socket Type	LGA 3647, Metric PQFP
--------------------------------	-----------------------

Usage Conditions

Operating Temperature Range	-25 – 100 °C[-13 – 212 °F]
-----------------------------	----------------------------

Industry Standards

Cover Flammability Rating	UL 94V-0
---------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	




Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-L59017-A76
LGA 3647 SOCKETS



TE Part # 2-2822549-5
LGA3647-0 SOCKET-P0 KIT (30U AU PLATING)



TE Part # 2821722-2
IFP/LEC CBL ASSY 1 PORT TYPE B STR INV




TE Part # 2821722-3
IFP/LEC CBL ASSY 1 PORT TYPE B STR INV



TE Part # 2821722-4
IFP/LEC CBL ASSY 1 PORT TYPE B STR INV

Customers Also Bought




TE Part #2-1926730-5
AssyMINIPAKHDL25a10pRAplugBdlk




TE Part #2-1926739-5
AssyMinipak Hdl25s10pRARecptSc



TE Part #1775485-2
Battery Holder, 3.6mm, BLU,low profile



TE Part #1775099-8
ATX PWR CONN 1 BDLK 12 POS



TE Part #1-2324271-4
LEFT SEGMENT LGA4189-4 SOCKET-
P4 FOR ODM



TE Part #2-2013289-2
EMBOSS TAPE DDR3 204P 5.2H STD
Au 0.25



TE Part #2-1734774-3
PCI EXP 3.1L 164 POS WHT 30u"



TE Part #2-2013298-1
EMBOSS TAPE DDR3 204P 8H RVS



TE Part #120955-3
UPM EXPANDED PIN ASSEMBLY



TE Part #6651430-1
TA CONN,PIN

Documents

Product Drawings

NRW NON-FABRIC CARRIER, SOCKET P0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2299806-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2299806-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2299806-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[LGA 3647 Socket Product Flyer](#)

English

[Product Environmental Compliance](#)

[MD_2299806-1_05112017057_dmtec](#)

English

[MD_2299806-1_05112017057_dmtec](#)

English