




Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC SERIES 1 SEALED ONE-PIECE



Connector Product Type: **Housing**
Operating Voltage: **600 VDC**
Connector System: **Wire-to-Wire**
Number of Positions: **9**
Sealable: **Yes**

[All CPC SERIES 1 SEALED ONE-PIECE \(33\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	9
Number of Power Positions	0
Seal Type	Wire Entry Seal
Keying	A
Number of Signal Positions	9

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Reverse Gender	No
----------------	----



Contact Type	Socket
Contact Protection	With

Mechanical Attachment

Screw & Hole Thread Size	3/4 - 20 UNEF-2A
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	Without
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Nylon (UV Resistant)
Circular Connector Shell Size	13

Dimensions

Accepts Wire Insulation Diameter Range	1.65 – 2.54 mm[.065 – .1 in]
--	------------------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	Immersion

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards


UL Flammability Rating	UL 94V-0
VDE Tested	No

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-C83998L
CPC SEALED ACCESSORIES



TE Part # CAT-AM71-C83998Y
CPC SERIES 1 SEALED ONE-PIECE



TE Part # CAT-AM71-T98
TYPE II CONTACTS



TE Part # CAT-AM71-T98E
TYPE III CONTACTS LP



TE Part # CAT-AM71-T98D
TYPE III CONTACTS LP EMEA



TE Part # CAT-AM71-T98A
TYPE III CONTACTS LP



TE Part # CAT-AM71-T98G
TYPE III CONTACTS LP HIGH CURRENT



TE Part # CAT-AM71-T98B
TYPE III CONTACTS STRIP



TE Part # CAT-AM71-T98F
TYPE III CONTACTS STRIP HIGH CURRENT



TE Part # CAT-AM71-C83998B
CPC CABLE CLAMPS



TE Part # CAT-AM71-C83998HH
CPC SEALED ACCESSORIES



TE Part # 91542-1
CCII TYPE III+ PIN SKT 24-22 ASSY



TE Part # 91515-1
CCII TYPE III+ MNL PIN SKT 30-20 ASSY



TE Part # 91519-1
CCII TYPE III+ PIN SKT 18-14 ASSY



TE Part # 91505-1
CCII TYPE III+ 24-16 ASSY



TE Part # 58495-1
PRO CRIMPER ASSY MULTIMATE



TE Part # 91523-1
CCII TYPE III+ PIN SKT 24-16 ASSY



TE Part # 91521-1
CCII TYPE III+ PIN SKT 18-14 ASSY



TE Part # 208338-1
SEAL PROTECTOR SOCKET



TE Part # 201328-1
CONTACT SOCKET ASSY.

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)




Circular Connector Hardware(3)




Circular Connector Keying Plugs(2)




Circular Connector Seals(36)




Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #1977882-1
CPC SERIES 1 SEALED ONE-PIECE




TE Part #1-66358-6
TYPE III CONTACTS STRIP



TE Part #2-1625999-8
Power Resistors: Aluminum Housed, HSC



TE Part #T4140L12051-000
M12 Panel Mount PCB



TE Part #1879452-6
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #206966-9
CPC CABLE CLAMPS



TE Part #206903-2
SEALING CAP ASSY,SZ 11,CPC

Documents

Product Drawings

SLD CPC PLUG ASSY,13-9,STD SEX, UV RESIS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1977884-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1977884-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1977884-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

6-1773700-2_UV_Resistant_Sealed_CPC

German

6-1773700-2_UV_Resistant_Sealed_CPC

English

6-1773700-2_UV_Resistant_Sealed_CPC

Japanese

6-1773700-2_UV_Resistant_Sealed_CPC