

8134-HC-6P3

✕ OBSOLETE

TE Internal #: 6-1437514-9

TE Internal Description: 8134-HC-6P3=HOLTITE 3.3.20

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



 TE Part #2007399-5 SFP+ Stacked Cage Assemblies	 TE Part #1-1744418-4 14 POS EP 2.5 HDR, GLOW WIRE	 TE Part #205555-3 AMPLIMITE,ASY,RCPT,STD,109,1,K	 TE Part #1551892-2 Cage Assy Behind Bezel QSFP28
 TE Part #2-87631-6 30 MODIV HSG DR MRKD .100 POL	 TE Part #103171-4 MOD IV RECP PLTD 30 DPLX	 TE Part #104361-4 05 MTE HDR SRRA LATCH W/HLDWN	 TE Part #1622513-6 LR1 1% 536R
 TE Part #1057853-1 3182 2240 00,TNC PLUG TO OSM	 TE Part #ZPF000000000018724 FDPA 50H 14-12 PN-K		

Documents

Product Drawings

8134-HC-6P3=HOLTITE 3.3.20

English

8134-HC-6P3=HOLTITE 3.3.20

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1437514-9_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1437514-9_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1437514-9_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



[Product Specifications](#)

[Application Specification](#)

English