



Triad 01 Panel/PCB Connector

TE Internal #: 9-1437719-6

Triad 01 Panel/PCB Connector, Standard Circular Connectors, Wire-to-Board, 3 Position, Sealable, 3A Contact Current Rating (Max), Signal, Panel Mount

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Board**

Number of Positions: **3**

Sealable: **Yes**

Contact Current Rating (Max): **3 A**

Circuit Application: **Signal**

Features

Product Type Features

Product Type	Connector
Connector System	Wire-to-Board
Sealable	Yes
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	60 VAC
-------------------	--------

Body Features

Shell Plating Material	Nickel
Shell Base Material	CuZn
Circular Connector Insulation Material Type	PBT
Hermetically Sealed	No

Contact Features



Contact Current Rating (Max)	3 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

Mechanical Attachment

Connector Mounting Type	Panel Mount
Mating Retention	With

Dimensions

Assembly Length	17.7 mm
Wire Size	.25 mm²

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	25
--------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1437719-5
T01-0550-P03-MALE PLUG
CONNECTOR SOLDER

Also in the Series | Triad 01 Panel/PCB Connector

Standard Circular Connectors(26)

Customers Also Bought

TE Part #1-1879378-1
Metal Chip Resistor: Current Sense

TE Part #1-1437719-5
T01-0550-P03-MALE PLUG
CONNECTOR SOLDER

TE Part #1-640525-0
24P MR II PLUG HSG V0 RED

TE Part #1-1337480-0
SMB FM BHSkt 50Ohm Gold Pltd





TE Part #1-1478904-0
SMA STR PLG DS RG405 GSS




TE Part #1437719-8
T01-0500-S=INDUSTRIAL CONNECTO




TE Part #1437720-3
T01-0580-S05-FEMALE REC PANEL MNT SOLDER



TE Part #CB03394012
Single Heavy Wall RW 200 E: Heat Shrink Tubing, 2:1 Shrink Ratio



TE Part #1337707-2
25MM CSA BRAID M8 - M8 400M



TE Part #1-160305-6
250 FASTON,REC.,10-12 AWG,TPBR

Documents

Product Drawings

T01-0580-S03-FEMALE REC PANEL MNT SOLDER

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_9-1437719-6_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_9-1437719-6_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_9-1437719-6_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Product Specification

English