



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Hardware Kits**

Screw Length: 19.05 mm [.75 in]

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Hardware Kits

Mechanical Attachment

Mounting Angle	Vertical
Screw & Hole Thread Size	4-40 UNC 2A
Screw Length	19.05 mm[.75 in]

Operation/Application

For Use With	Vertical Mount PCB Connectors
--------------	-------------------------------

Packaging Features

Packaging Quantity	1, 2
Packaging Method	Bag, Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-357-D658
IDC D-Sub: Plug Assembly, Signal,
Cable to Cable, 2.16 mm

Also in the Series | CHAMP Docking Connectors

 D-Sub Covers(27)	 D-Sub Locking & Mounting(31)	 Docking Connector Guide Hardware(5)	 Docking Connectors(33)
---	--	--	---



IDC D-Sub Connectors(85)



PCB D-Sub Connectors(1)

Customers Also Bought




TE Part #1658541-1
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



TE Part #1-2308340-1
D-SUB BACKSHELL SIZE 1



TE Part #1-2308272-1
CABLE CLAMP FOR SIZE 1-3STD/1-4 QL SHELL



TE Part #1-2176082-2
EP 3W (S) 680R 5%



TE Part #103327-2
02 MODII HDR SRST B/A .100CL




TE Part #1546931-3
3P UNSHROUD 5.0 HDR,HIGH TEMP



TE Part #1-5745967-4
D-Sub Receptacle Assembly: Vertical, Shell Size 3, 2.77mm



TE Part #F08497-000
MP METALIZED POLYESTER LABELS



TE Part #1-2176079-2
EP 3W 680R 5%



TE Part #1367710-1
assy guide frame x2 cast metal type 2

Documents

Product Drawings
HDW KIT, SCR LOCK, VERT MTG
English