




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Screw Retainer Kit**
Screw Length: **5.58 mm [.22 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Screw Retainer Kit

Mechanical Attachment

Screw Plating Material	Zinc
Screw Material	Steel
Screw Finish	Yellow Chromate
Screw & Hole Thread Size	4-40
Screw Length	5.58 mm[.22 in]

Operation/Application


For Use With	All Plastic Connectors (HDE)
--------------	------------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #2-6609028-0
CORCOM K SERIES SINGLE PHASE FILTERS

TE Part #1658640-1
D-Sub Crimp Recpt Signal 50 Posn, Socket Size 20, Shell Size 5

TE Part #1658686-3
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 22

TE Part #1-640519-0
04P MR II PLUG HSG V0 RED

TE Part #2-966067-0
ADERENDHUELSE HL GR

TE Part #1622417-1
LR1 1% 2K4

TE Part #1622191-1
LR0204 1% 20K

TE Part #YDTS26W21-11SNV001
D38999: Straight Plug, 21-11 Insert

TE Part #1658690-1
D-Sub Crimp Recpt Signal 15 Posn, Socket Size 22, Shell Size 1

TE Part #1052978-1
2054 1201 02

Documents

Product Drawings
HD KIT, MALE SCREW RET.

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5745647-1_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5745647-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5745647-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English