



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Universal Headers: Ejector Latch



Flat Flexible Cable Accessory Type: **Latch**

[All Universal Headers: Ejector Latch \(9\)](#)

Features

Product Type Features

Flat Flexible Cable Accessory Type	Latch
------------------------------------	-------

Body Features

Primary Product Material	Thermoplastic
Primary Product Color	Black

Dimensions

Product Length	20.27 mm
----------------	----------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	Receptacles With Strain Relief
---------	--------------------------------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS




TE Part # 1825851-1
AMPMODU MOD IV LATCH for AMPLA



TE Part # 678004-2
14P AMP-LATCH UNIV HDR ASSY



TE Part # 1-5111490-1
A/L UNIV HDR 60P VERT LG LAT SPC HSG



TE Part # 91269-1
TOOL, LATCH REMOVAL AL



Also in the Series

AMP-LATCH Universal Headers

Ribbon Cable Connectors(525)

Ribbon Connector Accessories(14)

Customers Also Bought

TE Part #1-5747150-4
D-Sub Receptacle Assembly: Vertical, Shell Size 1, 2.74mm

TE Part #1-5102154-0
AMP-LATCH UNIVERSAL HEADERS

TE Part #650473-5
096 EURO TYPE C PIN ST ASSY

TE Part #3-350945-0
05P UMNL HDR ASSY R/A 94VO LF

TE Part #390088-2
BLACK HSG WITH 15AU CONTACT

TE Part #206063-2
PLUG ASSY,44 POSN,AMPLIMITE

TE Part #102312-1
Universal Headers: Ejector Latch

TE Part #4-794682-6
16P MICRO MNL ASSY,VRT,THRU,LF

Documents

Product Drawings

UNIVERSAL HEADER LATCH

English

CAD Files

Customer View Model

ENG_CVM_102320-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_102320-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_102320-1_D.3d_stp.zip

English

3D PDF



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Ribbon Cable Interconnect Solutions

English

Agency Approvals
Agency Approval Document

English