


SLC41AC-1208A

✕ OBSOLETE

TE Internal #: CX5744-000

TE Internal Description: SLC41AC-1208A

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought





TE Part #5646533-1

Hard Metric Male Connector:
Traditional Backplane, Mezzanine,
2mm




TE Part #5646574-1

HM Receptacle Connector: Traditional
Backplane, Coplanar, 2mm




TE Part #904734-000

Low Profile HS Boots: Blow Molded,
Slim Line, Lipped, Straight




TE Part #364127-000

D-621-0415




TE Part #632785-000

Bulbous Heat Shrink Boots: Lipped,
Straight




TE Part #356327-000

TXR40AB90-1008BI




TE Part #381707-000

562A054-25/225-0




TE Part #138767-000

HET-A-03B



TE Part #F41443-000

D-500-L455-3-612-120



TE Part #435589-000

D-621-0413

Documents

Product Drawings

SLC41AC-1208A

English

Datasheets & Catalog Pages

Spin-Lock Variable Angle Backshell

English

Product Specifications

Spin-Lock Adapter Ordering Information

English

Assembly Guide for Raychem Spin-Lock Adapter with Aluminum Strain Relief

English