



Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): **Double Pole - Double Throw**

Bushing Thread Size: **M12 x .75**

Sealed Toggle Switch: **Yes**

Contact Base Material: **Copper Alloy**

Switch Contact Plating Material: **Silver**

Features

Product Type Features

Product Type	Switch
Sealed Toggle Switch	Yes
Toggle Style	Baton Standard
Toggle Switch Type	Toggle
Toggle Actuation	Vertical

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On (On)

Electrical Characteristics

Dielectric Strength	1500 VAC
Insulation Resistance	1000 MΩ
Contact Resistance	10 mΩ
Toggle Switch Voltage Rating	125 V, 250 V

Body Features

Color	Black
Bushing Thread Size	M12 x .75
Toggle Switch Seal Type	Waterproof
Bushing Style	Threaded



Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver
Toggle Switch Contact Current Rating	6 A

Termination Features

Termination Type	Lead Wire - Hooking Type, Vertical
------------------	------------------------------------

Mechanical Attachment

Toggle Switch Mounting Type	Solder
-----------------------------	--------

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	10.5 mm[.413 in]
---------------	------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-6437630-0
FTD0904=MINIATURE TOGGLE



TE Part # 7-6437630-2
AWTN1504 = POWER TOGGLE



TE Part # 7-6437630-0
AWTD1504 = POWER TOGGLE



TE Part # 8-6437630-0
A4TK15W04




TE Part # 3-6437630-5
F4TN0904=MINIATURE TOGGLE

Also in the Series | Alcoswitch F Series



Toggle Switches(28)

Customers Also Bought



TE Part #106012-1
Hard Metric Backplane Male Connector: Right Angle, Coplanar, 2mm



TE Part #152872
14-12 PIDG NYLON RT NO 10WHITE



TE Part #1-1879223-6
CPF 0603 340R 0.1% 25PPM 1K RL



TE Part #1622550-1
LR1 1% 68R



TE Part #1623720-8
CCR2 470R 10%

TE Part #1622405-1
LR1 1% 270K

TE Part #1-1337448-0
BNC BHSkt + TAG 50Ohm Nickel Pltd

TE Part #1-1337523-0
BNC Plg Term 50Ohm Nickel Pltd

TE Part #ZPF000000000110277
732-8254-16

TE Part #1-1478402-0
BNC Str Plg PS 50Ohm Silver RG174A /U, 18

Documents

Product Drawings
FTR0904=MINIATURE TOGGLE

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_4-6437630-4_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_4-6437630-4_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_4-6437630-4_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages
SWITCHES_CORE_PROGRAM_CATALOG
English
F_SERIES_SWITCHES_QUICK_REF_GUIDE_1-1773458-9
English