

MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLACK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
A-YELLOW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
B-LIGHT GRAY	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BROWN	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
C-DARK GRAY	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-GREEN	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
D-STONE GRAY	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
GCO	GROMMET CAP (STANDARD OPEN)	BLACK	SPS/NYLON GF20
GCP	GROMMET CAP (STANDARD PLUGGED)	BLACK	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE
PLR	PLR	NATURAL	SPS/NYLON GF20

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION							
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL					BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS		
MX150 ASSY BLD 2X2 BK A/4	334824001	A-BLACK	GCO	PLR	M	-	-	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 LG B/4	334824002	B-LIGHT GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BR C/4	334824003	C-BROWN	GCO	PLR	M	-	-	NOT RECOMMENDED	SEE 334824103	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 GR D/4	334824004	D-GREEN	GCO	PLR	M	-	-	NOT RECOMMENDED	SEE 334824104	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BK A/3	334824006	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 LG B/3	334824007	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BR C/3	334824008	C-BROWN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824105	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 GR D/3	334824009	D-GREEN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824106	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BK A/2	334824011	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 LG B/2	334824012	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 BR C/2	334824013	C-BROWN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824107	N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 GR D/2	334824014	D-GREEN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824108	N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 BK A/0	334824016	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 LG B/0	334824017	B-LIGHT GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 BR C/0	334824018	C-BROWN	GCP	PLR	M	1	2	NOT RECOMMENDED	SEE 334824109	N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 GR D/0	334824019	D-GREEN	GCP	PLR	M	1	2	NOT RECOMMENDED	SEE 334824110	N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 BK A/1	334824021	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A		
						3	-						

DATE 08/17/2021

DOCUMENT NO. 334820402










REVISION C
Page 1 of 2




MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION				BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL						
MX150 ASSY BLD 2X2 BK A/3	334824022	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/2	334824023	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/3	334824024	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 BK A/2	334824025	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/4	334824103	C-DARK GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 SG D/4	334824104	D-STONE GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/3	334824105	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 SG D/3	334824106	D-STONE GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/2	334824107	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 SG D/2	334824108	D-STONE GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 DG C/0	334824109	C-DARK GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 SG D/0	334824110	D-STONE GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/2	334824111	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 YW A/4	334824112	A-YELLOW	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 LG B/3	334824113	B-LIGHT GRAY	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/2	334824115	A-BLACK	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 DG C/2	334824116	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 LG B/2	334824117	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 LG B/3	334824118	B-LIGHT GRAY	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/2	334824119	A-BLACK	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/3	334824120	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				









SHEET DESCRIPTION	
CONFIGURATIONS	

		
2X2 - STANDARD (STD)	2X2 - UL V0*	
		
2X3 - STANDARD (STD)		2X3 - LENGTHENED
		
2X4 - STANDARD (STD)		
		
2X6 - STANDARD (STD)		
		
2X8 - STANDARD (STD)		
		
2X10 - STANDARD (STD)	2X10 - UL V0*	
DOCUMENT STATUS	P1	RELEASE DATE
		2018/02/16 22:02:26




UL V0 UNIQUE FEATURE
Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					molex						
	mm		1.5:1													
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)									MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
 = 0	ANGULAR TOL ± 1.0 °															
 = 0	4 PLACES		±		PRODUCT CUSTOMER DRAWING											
 = 0	3 PLACES		±							DOCUMENT NUMBER SD-33482-0001		DOC TYPE		DOC PART		REVISION
 = 0	2 PLACES		± 0.1		PSD		001		E2							
 = 0	1 PLACE		± 0.2													
 = 0	0 PLACES		±		THIRD ANGLE PROJECTION 		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A1-SIZE		33482		GENERAL MARKET		2 OF 11			

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



KEY B




KEY C




KEY D


2X10




KEY A




KEY B



KEY C










KEY D

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
mm		3:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
ANGULAR TOL ± 1.0°											
4 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				DOCUMENT NUMBER SD-33482-0001		DOC TYPE PSD	DOC PART 001	REVISION E2	
3 PLACES ±											
2 PLACES ± 0.1		THIRD ANGLE PROJECTION 				MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 4 OF 11	
1 PLACE ± 0.2											
0 PLACES ±		DRAWING A1-SIZE		SERIES 33482							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											


SHEET DESCRIPTION	
BLADE SEALED ASSEMBLY	

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION

SECTION W-W



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN FINAL-LOCK POSITION



SECTION V-V

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
		DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
= 0		mm		3:1		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14						PRODUCT CUSTOMER DRAWING					
= 0		GENERAL TOLERANCES (UNLESS SPECIFIED)															
= 0		ANGULAR TOL ± 1.0 °										DOCUMENT NUMBER					
= 0		4 PLACES ±										DOC TYPE		DOC PART		REVISION	
= 0		3 PLACES ±										SD-33482-0001		PSD		001	
= 0		2 PLACES ± 0.1				THIRD ANGLE PROJECTION		DRAWING		SERIES							
= 0		1 PLACE ± 0.2						A1-SIZE		33482		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
= 0		0 PLACES ±															
= 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				GENERAL MARKET 5 OF 11											

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION
SYSTEM PACKAGING

CHARTED DIMENSION				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X2	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT	72.78	28.50
		LENGTHENED	77.21	28.00
2X3	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT		30.50
	LENGTHENED	W/O CLIPSLOT	74.79	28.00
		W/ CLIPSLOT		30.50
2X4	STANDARD	W/O CLIPSLOT	72.78	29.50
		W/ CLIPSLOT		31.50
2X6	STANDARD	W/O CLIPSLOT	72.79	35.58
		W/ CLIPSLOT		
2X8	STANDARD	W/O CLIPSLOT	72.67	42.25
		W/ CLIPSLOT		
2X10	STANDARD	STANDARD	72.78	49.05



SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
<										


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:


- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX

CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR







MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20

BLADE SEALED ASSEMBLY

BACKSHELL (BKS)






90° ADAPTOR

SCALE 1.5:1


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex				
	mm		1.5:1									
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16			MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
	ANGULAR TOL ± 1.0 °											
 = 0	4 PLACES		±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			PRODUCT CUSTOMER DRAWING				
	3 PLACES		±									
 = 0	2 PLACES		± 0.1		DOCUMENT NUMBER SD-33482-0001			DOC TYPE		DOC PART		REVISION
	1 PLACE		± 0.2					PSD		001		E2
 = 0	0 PLACES		±		THIRD ANGLE PROJECTION			MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							GENERAL MARKET		7 OF 11		
 = 0					DRAWING			SERIES				
 = 0					A1-SIZE			33482				

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	




SECTION A-A




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
= 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL								
	mm		3.5:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16								PRODUCT CUSTOMER DRAWING				
	ANGULAR TOL ± 1.0 °																
	4 PLACES		±						INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
	3 PLACES		±										SD-33482-0001		PSD	001	E2
	2 PLACES		± 0.1														
	1 PLACE		± 0.2		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
	0 PLACES		±														
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A1-SIZE		33482		GENERAL MARKET				8 OF 11		

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------





SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	= 0	DIMENSION UNITS	mm	SCALE	3:1	CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
		GENERAL TOLERANCES (UNLESS SPECIFIED)													
	= 0	ANGULAR TOL		±	1.0 °						PRODUCT CUSTOMER DRAWING				
	= 0	4 PLACES	±	DOCUMENT NUMBER SD-33482-0001											
	= 0	3 PLACES	±								DOC TYPE PSD				
	= 0	2 PLACES	±	0.1	DOC PART 001										
	= 0	1 PLACE	±	0.2							REVISION E2				
	= 0	0 PLACES	±	SHEET NUMBER 9 OF 11											
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		
	= 0				A1-SIZE	33482		GENERAL MARKET							



SHEET DESCRIPTION	
SCHLEMMER BACKSHELL CONFIGURATIONS	





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




OVERALL MATED SYSTEM WITH BLADE BACKSHELL



OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	T
2X3	STANDARD	STANDARD	106.83	32.75	31.75	29.00	29.50
	LENGTHENED		108.71				
2X4	STANDARD	STANDARD	106.83	33.50	31.90	30.70	30.70
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:26
-----------------	----	--------------	------------	----------


SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
		DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex					
		mm		2:1												
		GENERAL TOLERANCES (UNLESS SPECIFIED)														
		ANGULAR TOL ± 1.0 °					EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
		4 PLACES ±														
		3 PLACES ±														
		2 PLACES ± 0.1														
		1 PLACE ± 0.2														
		0 PLACES ±					PRODUCT CUSTOMER DRAWING									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					DOCUMENT NUMBER			DOC TYPE		DOC PART		REVISION		
							SD-33482-0001			PSD		001		E2		
		THIRD ANGLE PROJECTION					MATERIAL NUMBER		CUSTOMER				SHEET NUMBER			
							A1-SIZE		33482		GENERAL MARKET				10 OF 11	




OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH BLADE BACKSHELL




(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE



ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED



(Ø DIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

CHARTED DIMENSIONS


CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex							
	mm		1:1														
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
 = 0																	
 = 0	ANGULAR TOL ± 1.0 °				INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					PRODUCT CUSTOMER DRAWING							
 = 0	4 PLACES		±														
 = 0	3 PLACES		±														
 = 0	2 PLACES		± 0.1														
 = 0	1 PLACE		± 0.2		THIRD ANGLE PROJECTION					DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
 = 0	0 PLACES		±							SD-33482-0001		PSD		001		E2	
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER				
= 0					A1-SIZE		33482				GENERAL MARKET		11 OF 11				



MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET




ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4												
KEY A, BLACK	33482-4001	A-BLK	GCO	PLR	M												SALEABLE				
KEY B, LIGHT GRAY	33482-4002	B-LG	GCO	PLR	M												SALEABLE				
KEY C, BROWN	33482-4003	C-BR	GCO	PLR	M												NOT RECOMMENDED	SEE 33482-4103			
KEY D, GREEN	33482-4004	D-GR	GCO	PLR	M												NOT RECOMMENDED	SEE 33482-4104			
KEY A, BLACK	33482-4006	A-BLK	GCP	PLR	M		2										SALEABLE				
KEY B, LIGHT GRAY	33482-4007	B-LG	GCP	PLR	M		2										SALEABLE				
KEY C, BROWN	33482-4008	C-BR	GCP	PLR	M		2										NOT RECOMMENDED	SEE 33482-4105			
KEY D, GREEN	33482-4009	D-GR	GCP	PLR	M		2										NOT RECOMMENDED	SEE 33482-4106			
KEY A, BLACK	33482-4011	A-BLK	GCP	PLR	M		2	3									SALEABLE				
KEY B, LIGHT GRAY	33482-4012	B-LG	GCP	PLR	M		2	3									SALEABLE				
KEY C, BROWN	33482-4013	C-BR	GCP	PLR	M		2	3									NOT RECOMMENDED	SEE 33482-4107			
KEY D, GREEN	33482-4014	D-GR	GCP	PLR	M		2	3									NOT RECOMMENDED	SEE 33482-4108			
KEY A, BLACK	33482-4016	A-BLK	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY B, LIGHT GRAY	33482-4017	B-LG	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY C, BROWN	33482-4018	C-BR	GCP	PLR	M	1	2	3	4								NOT RECOMMENDED	SEE 33482-4109			
KEY D, GREEN	33482-4019	D-GR	GCP	PLR	M	1	2	3	4								NOT RECOMMENDED	SEE 33482-4110			
KEY A, BLACK	33482-4021	A-BLK	GCP	PLR	M	1	2	3									SALEABLE				
KEY A, BLACK	33482-4022	A-BLK	GCP	PLR	M				4								SALEABLE				
KEY A, BLACK	33482-4023	A-BLK	GCP	PLR	M			3	4								SALEABLE				
KEY A, BLACK	33482-4024	A-BLK	GCP	PLR	M			3									SALEABLE				
KEY A, BLACK	33482-4025	A-BLK	GCP	PLR	M	1	2										SALEABLE				
KEY C, DARK GRAY	33482-4103	C-DG	GCO	PLR	M												SALEABLE				
KEY D, STONE GRAY	33482-4104	D-SG	GCO	PLR	M												SALEABLE				
KEY C, DARK GRAY	33482-4105	C-DG	GCP	PLR	M		2										SALEABLE				
KEY D, STONE GRAY	33482-4106	D-SG	GCP	PLR	M		2										SALEABLE				
KEY C, DARK GRAY	33482-4107	C-DG	GCP	PLR	M		2	3									SALEABLE				
KEY D, STONE GRAY	33482-4108	D-SG	GCP	PLR	M		2	3									SALEABLE				
KEY C, DARK GRAY	33482-4109	C-DG	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY D, STONE GRAY	33482-4110	D-SG	GCP	PLR	M	1	2	3	4								SALEABLE				
KEY A, BLACK	33482-4111	A-BLK	GCP	PLR	M		2		4								SALEABLE				
KEY A, YELLOW	33482-4112	A-YW	GCO	PLR	M												SALEABLE				
KEY B, LIGHT GRAY	33482-4113	B-LG	GCP	PLR	M	1											SALEABLE				
KEY A, BLACK	33482-4115	A-BLK	GCP	PLR	M	1		3									SALEABLE				
KEY C, DARK GRAY	33482-4116	C-DG	GCP	PLR	M		2		4								SALEABLE				
KEY B, LIGHT GRAY	33482-4117	B-LG	GCP	PLR	M		2		4								SALEABLE				
KEY B, LIGHT GRAY	33482-4118	B-LG	GCP	PLR	M				4								SALEABLE				
KEY A, BLACK	33482-4119	A-BLK	GCP	PLR	M	1			4								SALEABLE				



MX150 2X3 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GC	GROMMET CAP (STANDARD)	BLACK	SPS/NYLON GF20
GCL	GROMMET CAP (LENGTHENED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS										STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION												BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6									
KEY A, BLACK	33482-3601	A-BLK	GC	PLR	M												SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3602	B-LG	GC	PLR	M												SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3603	C-BR	GC	PLR	M												NOT RECOMMENDED	SEE 33482-3628	34950-0610	34950-0620
KEY D, GREEN	33482-3604	D-GR	GC	PLR	M												NOT RECOMMENDED	SEE 33482-3629	34950-0610	34950-0620
VOID KEY	33482-3605																			
KEY A, BLACK	33482-3606	A-BLK	GC	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3607	B-LG	GC	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3608	C-BR	GC	PLR	M				3								NOT RECOMMENDED	SEE 33482-3638	34950-0610	34950-0620
KEY D, GREEN	33482-3609	D-GR	GC	PLR	M				3								NOT RECOMMENDED	SEE 33482-3641	34950-0610	34950-0620
VOID KEY	33482-3610																			
KEY A, BLACK	33482-3611	A-BLK	GC	PLR	M				3	4							SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3612	B-LG	GC	PLR	M				3	4							SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3613	C-BR	GC	PLR	M				3	4							NOT RECOMMENDED	SEE 33482-3642	34950-0610	34950-0620
KEY D, GREEN	33482-3614	D-GR	GC	PLR	M				3	4							NOT RECOMMENDED	SEE 33482-3643	34950-0610	34950-0620
VOID KEY	33482-3615																			
KEY A, BLACK	33482-3616	A-BLK	GC	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3617	A-BLK	GC	PLR	M			2									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3618	A-BLK	GC	PLR	M						5	6					SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3619	A-BLK	GC	PLR	M			2	3	4	5						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3620	A-BLK	GC	PLR	M	1	2	3	4	5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3621	A-BLK	GC	PLR	M	1			4	5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3622	A-BLK	GC	PLR	M				4	5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3623	A-BLK	GC	PLR	M					5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3624	A-BLK	GC	PLR	M						6						SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3625	B-LG	GC	PLR	M	1				5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3626	A-BLK	GC	PLR	M	1	2	3	4								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3627	A-BLK	GC	PLR	M		2	3		5	6						SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3628	C-DG	GC	PLR	M												SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3629	D-SG	GC	PLR	M												SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3630	A-BLK	GC	PLR	M				3		6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3631	A-BLK	GCL	PLR	M												SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3632	B-LG	GCL	PLR	M												SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3633	C-DG	GCL	PLR	M												SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3634	D-SG	GCL	PLR	M												SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3635	C-DG	GCL	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3636	A-BLK	GCL	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3637	A-BLK	GC	PLR	M			2			6						SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3638	C-DG	GC	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3639	A-BLK	GCL	PLR	M	1	2	3	4	5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3640	A-BLK	GC	PLR	M				4								SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3641	D-SG	GC	PLR	M				3								SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3642	C-DG	GC	PLR	M				3	4							SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3643	D-SG	GC	PLR	M				3	4							SALEABLE		34950-0610	34950-0620
KEY A, YELLOW	33482-3644	A-YW	GC	PLR	M												SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3645	A-BLK	GC	PLR	M				3	4	5	6					SALEABLE		34950-0610	34950-0620




MX150 2X3 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS											STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION													BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6									
KEY A, BLACK	33482-3646	A-BLK	GC	PLR	M		2	3									SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3647	B-LG	GC	PLR	M		2	3									SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3648	C-DG	GC	PLR	M						6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3649	A-BLK	GC	PLR	M				4		6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3650	A-BLK	GC	PLR	M	1		3		5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3651	A-BLK	GC	PLR	M		2		4		6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3652	A-BLK	GC	PLR	M	1					6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3653	A-BLK	GC	PLR	M		2			5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3654	A-BLK	GC	PLR	M	1		3	4								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3655	A-BLK	GC	PLR	M	1	2	3		5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3656	A-BLK	GC	PLR	M	1	2	3									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3657	A-BLK	GC	PLR	M				4	5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3658	A-BLK	GC	PLR	M	1											SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3659	B-LG	GC	PLR	M	1											SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3660	B-LG	GC	PLR	M					5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3661	A-BLK	GC	PLR	M	1				5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3662	A-BLK	GC	PLR	M			3	4		6						SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3663	B-LG	GC	PLR	M					5	6						SALEABLE		34950-0610	34950-0620



MX150 2X4 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8										
KEY A, BLACK	33482-0801	A-BLK	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4801	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0802	B-LG	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4802	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0803	C-BR	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4803	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0804	D-GR	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4804	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0805																						
KEY A, BLACK	33482-0806	A-BLK	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4806	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0807	B-LG	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4807	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0808	C-BR	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4808	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0809	D-GR	GCP	PLR	M-R				4									PLANNED OBSOLESCENCE	SEE 33482-4809	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0810																						
KEY A, BLACK	33482-0811	A-BLK	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4811	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0812	B-LG	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4812	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0813	C-BR	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4813	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0814	D-GR	GCP	PLR	M-R				4	5								PLANNED OBSOLESCENCE	SEE 33482-4814	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0815																						
KEY A, BLACK	33482-0816	A-BLK	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4816	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0817	B-LG	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4817	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0818	C-BR	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4818	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0819	D-GR	GCP	PLR	M-R	1			4	5								PLANNED OBSOLESCENCE	SEE 33482-4819	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0820																						
KEY A, BLACK	33482-0821	A-BLK	GCP	PLR	M-R	1			4	5				8				PLANNED OBSOLESCENCE	SEE 33482-4821	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0822	B-LG	GCP	PLR	M-R	1			4	5				8				PLANNED OBSOLESCENCE	SEE 33482-4822	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0823	C-BR	GCP	PLR	M-R	1			4	5				8				PLANNED OBSOLESCENCE	SEE 33482-4823	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0824	D-GR	GCP	PLR	M-R	1			4	5				8				PLANNED OBSOLESCENCE	SEE 33482-4824	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0825																						
KEY A, BLACK	33482-0826	A-BLK	GCP	PLR	M-R	1	2	3			6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4826	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0827	A-BLK	GCP	PLR	M-R									8				PLANNED OBSOLESCENCE	SEE 33482-4827	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0828	A-BLK	GCP	PLR	M-R			3		5								PLANNED OBSOLESCENCE	SEE 33482-4828	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0829	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7						PLANNED OBSOLESCENCE	SEE 33482-4829	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0830	A-BLK	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-4830	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0831	A-BLK	GCP	PLR	M-R			3		5	6							PLANNED OBSOLESCENCE	SEE 33482-4831	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0832	A-BLK	GCP	PLR	M-R					5	6		8					PLANNED OBSOLESCENCE	SEE 33482-4832	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0833	A-BLK	GCP	PLR	M-R	1		3		5								PLANNED OBSOLESCENCE	SEE 33482-4833	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0834	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4834	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0835	A-BLK	GCP	PLR	M-R							7	8					PLANNED OBSOLESCENCE	SEE 33482-4835	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0836	A-BLK	GCP	PLR	M-R		2	3			6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4836	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0837	A-BLK	GCP	PLR	M-R	1			4									PLANNED OBSOLESCENCE	SEE 33482-4837	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0838	A-BLK	GCP	PLR	M-R		2	3		5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4838	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0839	B-LG	GCP	PLR	M-R								8					PLANNED OBSOLESCENCE	SEE 33482-4839	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0840	A-BLK	GCP	PLR	M-R		2	3		5	6		8					PLANNED OBSOLESCENCE	SEE 33482-4840	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0841	A-BLK	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-4841	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0842	A-BLK	GCP	PLR	M-R							7						PLANNED OBSOLESCENCE	SEE 33482-4842	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0843	A-BLK	GCP	PLR	M-R				4			7						PLANNED OBSOLESCENCE	SEE 33482-4843	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0844	A-BLK	GCP	PLR	M-R			3			6							PLANNED OBSOLESCENCE	SEE 33482-4844	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0845	A-BLK	GCP	PLR	M-R		2	3	4	5	6							PLANNED OBSOLESCENCE	SEE 33482-4845	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0846	A-BLK	GCP	PLR	M-R				4	5		7	8					PLANNED OBSOLESCENCE	SEE 33482-4846	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0847	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4847	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0848	A-BLK	GCP	PLR	M-R	1				5								PLANNED OBSOLESCENCE	SEE 33482-4848	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0849	B-LG	GCP	PLR	M-R	1					6							PLANNED OBSOLESCENCE	SEE 33482-4849	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-0850	A-YW	GCP	PLR	M-R	1			4									PLANNED OBSOLESCENCE	SEE 33482-4850	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-0851	A-YW	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4851	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY	33482-0852	C-DG	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4852	34950-0811	34950-0821	34951-0831	34951-0841

MX150 2X4 BLADE SEALED ASSEMBLY MAT SEAL																							
BOM AND PIN OUT SHEET																							
ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8										
KEY D, STONE GRAY	33482-0853	D-SG	GCO	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-4853	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0854	A-BLK	GCP	PLR	M-R	1	2	3	4									PLANNED OBSOLESCENCE	SEE 33482-4854	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0855	A-BLK	GCP	PLR	M-R	1	2			5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4855	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0856	A-BLK	GCP	PLR	M-R	1	2											PLANNED OBSOLESCENCE	SEE 33482-4856	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0857	A-BLK	GCP	PLR	M-R	1	2	3		5								PLANNED OBSOLESCENCE	SEE 33482-4857	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0858	A-BLK	GCP	PLR	M-R	1	2	3	4	5			8					PLANNED OBSOLESCENCE	SEE 33482-4858	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0859	A-BLK	GCP	PLR	M-R	1		3		5	6	7						PLANNED OBSOLESCENCE	SEE 33482-4859	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0860	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6							PLANNED OBSOLESCENCE	SEE 33482-4860	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0861	A-BLK	GCP	PLR	M-R	1	2	3			6							PLANNED OBSOLESCENCE	SEE 33482-4861	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0862	A-BLK	GCP	PLR	M-R	1					6							PLANNED OBSOLESCENCE	SEE 33482-4862	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0863	A-BLK	GCP	PLR	M-R	1					6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4863	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0864	A-BLK	GCP	PLR	M-R			3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4864	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0865	A-BLK	GCP	PLR	M-R				4			7	8					PLANNED OBSOLESCENCE	SEE 33482-4865	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0866	A-BLK	GCP	PLR	M-R				4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4866	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0867	A-BLK	GCP	PLR	M-R		2	3	4		6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4867	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0868	A-BLK	GCP	PLR	M-R					5	6	7						PLANNED OBSOLESCENCE	SEE 33482-4868	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0869	A-BLK	GCP	PLR	M-R			3	4									PLANNED OBSOLESCENCE	SEE 33482-4869	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0870	A-BLK	GCP	PLR	M-R						6	7	8					PLANNED OBSOLESCENCE	SEE 33482-4870	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0871	B-LG	GCP	PLR	M-R							7	8					PLANNED OBSOLESCENCE	SEE 33482-4871	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0872	A-BLK	GCP	PLR	M-R	1							8					PLANNED OBSOLESCENCE	SEE 33482-4872	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0873	A-BLK	GCP	PLR	M-R						6		8					PLANNED OBSOLESCENCE	SEE 33482-4873	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0874	A-BLK	GCP	PLR	M-R		2			5								PLANNED OBSOLESCENCE	SEE 33482-4874	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0875	A-BLK	GCP	PLR	M-R					5								PLANNED OBSOLESCENCE	SEE 33482-4875	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0876	B-LG	GCP	PLR	M-R	1		3					8					PLANNED OBSOLESCENCE	SEE 33482-4876	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0877	B-LG	GCP	PLR	M-R			3					8					PLANNED OBSOLESCENCE	SEE 33482-4877	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0878	B-LG	GCP	PLR	M-R	1												PLANNED OBSOLESCENCE	SEE 33482-4878	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0879	A-BLK	GCP	PLR	M-R	1	2	3	4	5		7						PLANNED OBSOLESCENCE	SEE 33482-4879	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0880	A-BLK	GCP	PLR	M-R	1												PLANNED OBSOLESCENCE	SEE 33482-4880	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0881	A-BLK	GCP	PLR	M-R					5			8					PLANNED OBSOLESCENCE	SEE 33482-4881	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0882	A-BLK	GCP	PLR	M-R				4		6							PLANNED OBSOLESCENCE	SEE 33482-4882	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0883	A-BLK	GCP	PLR	M-R	1						7						PLANNED OBSOLESCENCE	SEE 33482-4883	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0884	A-BLK	GCP	PLR	M-R	1	2	3	4			7						PLANNED OBSOLESCENCE	SEE 33482-4884	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0885	A-BLK	GCP	PLR	M-R	1	2			5	6		8					PLANNED OBSOLESCENCE	SEE 33482-4885	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0886	A-BLK	GCP	PLR	M-R		2	3					8					PLANNED OBSOLESCENCE	SEE 33482-4886	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0887	A-BLK	GCP	PLR	M-R	1		3	4			7	8					PLANNED OBSOLESCENCE	SEE 33482-4887	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0888	A-BLK	GCP	PLR	M-R				4	5	6							PLANNED OBSOLESCENCE	SEE 33482-4888	34950-			



MX150 2X4 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8										
KEY A, BLACK	33482-4835	A-BLK	GCP	PLR	M-B								7	8				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4836	A-BLK	GCP	PLR	M-B		2	3			6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4837	A-BLK	GCP	PLR	M-B	1			4									SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4838	A-BLK	GCP	PLR	M-B		2	3		5	6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4839	B-LG	GCP	PLR	M-B								8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4840	A-BLK	GCP	PLR	M-B		2	3		5	6		8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4841	A-BLK	GCP	PLR	M-B						6	7						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4842	A-BLK	GCP	PLR	M-B							7						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4843	A-BLK	GCP	PLR	M-B				4			7						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4844	A-BLK	GCP	PLR	M-B			3			6							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4845	A-BLK	GCP	PLR	M-B		2	3	4	5	6							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4846	A-BLK	GCP	PLR	M-B				4	5		7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4847	B-LG	GCP	PLR	M-B	1	2	3	4	5	6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4848	A-BLK	GCP	PLR	M-B	1				5								SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4849	B-LG	GCP	PLR	M-B	1					6							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-4850	A-YW	GCP	PLR	M-B	1			4									SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-4851	A-YW	GCO	PLR	M-B													SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY	33482-4852	C-DG	GCO	PLR	M-B													SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY	33482-4853	D-SG	GCO	PLR	M-B													SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4854	A-BLK	GCP	PLR	M-B	1	2	3	4									SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4855	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4856	A-BLK	GCP	PLR	M-B	1	2											SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4857	A-BLK	GCP	PLR	M-B	1	2	3		5								SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4858	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4859	A-BLK	GCP	PLR	M-B	1		3		5	6	7						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4860	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4861	A-BLK	GCP	PLR	M-B	1	2	3			6							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4862	A-BLK	GCP	PLR	M-B	1					6							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4863	A-BLK	GCP	PLR	M-B	1					6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4864	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4865	A-BLK	GCP	PLR	M-B				4			7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4866	A-BLK	GCP	PLR	M-B				4	5	6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4867	A-BLK	GCP	PLR	M-B		2	3	4		6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4868	A-BLK	GCP	PLR	M-B					5	6	7						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4869	A-BLK	GCP	PLR	M-B			3	4									SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4870	A-BLK	GCP	PLR	M-B						6	7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4871	B-LG	GCP	PLR	M-B							7	8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4872	A-BLK	GCP	PLR	M-B	1							8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4873	A-BLK	GCP	PLR	M-B						6		8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4874	A-BLK	GCP	PLR	M-B		2			5								SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4875	A-BLK	GCP	PLR	M-B					5								SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4876	B-LG	GCP	PLR	M-B	1		3					8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4877	B-LG	GCP	PLR	M-B			3					8					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4878	B-LG	GCP	PLR	M-B	1												SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4879	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7						SALEABLE					



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Diagram illustrating the components of the MX150 2X6 Blade Sealed Assembly:

- GROMMET CAP
- CONNECTOR HOUSING
- PRIMARY LOCK REINFORCEMENT (PLR)
- MAT SEAL

Terminal positions are labeled on the main assembly:

- TERMINAL POSITION 1
- TERMINAL POSITION 6
- TERMINAL POSITION 7
- TERMINAL POSITION 12

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
A-YL	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-1201	A-BLK	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6201	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1202	B-LG	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6202	34950-1210	34950-1220
KEY C, BROWN	33482-1203	C-BR	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6203	34950-1210	34950-1220
KEY D, GREEN	33482-1204	D-GR	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6204	34950-1210	34950-1220
VOID KEY	33482-1205																				
KEY A, BLACK	33482-1206	A-BLK	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6206	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1207	B-LG	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6207	34950-1210	34950-1220
KEY C, BROWN	33482-1208	C-BR	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6208	34950-1210	34950-1220
KEY D, GREEN	33482-1209	D-GR	GCP	PLR	M-R						6							PLANNED OBSOLESCENCE	SEE 33482-6209	34950-1210	34950-1220
VOID KEY	33482-1210																				
KEY A, BLACK	33482-1211	A-BLK	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6211	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1212	B-LG	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6212	34950-1210	34950-1220
KEY C, BROWN	33482-1213	C-BR	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6213	34950-1210	34950-1220
KEY D, GREEN	33482-1214	D-GR	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6214	34950-1210	34950-1220
VOID KEY	33482-1215																				
KEY A, BLACK	33482-1216	A-BLK	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6216	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1217	B-LG	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6217	34950-1210	34950-1220
KEY C, BROWN	33482-1218	C-BR	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6218	34950-1210	34950-1220
KEY D, GREEN	33482-1219	D-GR	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6219	34950-1210	34950-1220
VOID KEY	33482-1220																				
KEY A, BLACK	33482-1221	A-BLK	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6221	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1222	B-LG	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6222	34950-1210	34950-1220
KEY C, BROWN	33482-1223	C-BR	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6223	34950-1210	34950-1220
KEY D, GREEN	33482-1224	D-GR	GCP	PLR	M-R	1					6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6224	34950-1210	34950-1220
VOID KEY	33482-1225																				
KEY A, BLACK	33482-1226	A-BLK	GCP	PLR	M-R						6						12	PLANNED OBSOLESCENCE	SEE 33482-6226	34950-1210	34950-1220
KEY A, BLACK	33482-1227	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6227	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1228	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6228	34950-1210	34950-1220
KEY C, BROWN	33482-1229	C-BR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6229	34950-1210	34950-1220
KEY D, GREEN	33482-1230	D-GR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6230	34950-1210	34950-1220
VOID KEY	33482-1231																				
KEY A, BLACK	33482-1232	A-BLK	GCP	PLR	M-R		2	3					8			11		PLANNED OBSOLESCENCE	SEE 33482-6232	34950-1210	34950-1220
KEY A, BLACK	33482-1233	A-BLK	GCP	PLR	M-R		2	3		5	6	7	8			11		PLANNED OBSOLESCENCE	SEE 33482-6233	34950-1210	34950-1220
KEY A, BLACK	33482-1234	A-BLK	GCP	PLR	M-R						6	7						PLANNED OBSOLESCENCE	SEE 33482-6234	34950-1210	34950-1220
KEY A, BLACK	33482-1235	A-BLK	GCP	PLR	M-R		2	3			6	7	8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6235	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1236	B-LG	GCP	PLR	M-R	1				5	6	7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6236	34950-1210	34950-1220
KEY A, BLACK	33482-1237	A-BLK	GCP	PLR	M-R		2											PLANNED OBSOLESCENCE	SEE 33482-6237	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1238	B-LG	GCP	PLR	M-R		2							9	10			PLANNED OBSOLESCENCE	SEE 33482-6238	34950-1210	34950-1220
KEY A, BLACK	33482-1239	A-BLK	GCP	PLR	M-R	1				5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-6239	34950-1210	34950-1220
KEY A, BLACK	33482-1240	A-BLK	GCP	PLR	M-R		2	3					8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6240	34950-1210	34950-1220
KEY A, BLACK	33482-1241	A-BLK	GCP	PLR	M-R							7	8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6241	34950-1210	34950-1220
KEY A, BLACK	33482-1242	A-BLK	GCP	PLR	M-R							7	8					PLANNED OBSOLESCENCE	SEE 33482-6242	34950-1210	34950-1220
KEY A, BLACK	33482-1243	A-BLK	GCP	PLR	M-R		2							9	10			PLANNED OBSOLESCENCE	SEE 33482-6243	34950-1210	34950-1220
KEY A, BLACK	33482-1244	A-BLK	GCP	PLR	M-R		2		4									PLANNED OBSOLESCENCE	SEE 33482-6244	34950-1210	34950-1220
KEY A, BLACK	33482-1245	A-BLK	GCP	PLR	M-R									9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6245	34950-1210	34950-1220
KEY A, BLACK	33482-1246	A-BLK	GCP	PLR	M-R											11		PLANNED OBSOLESCENCE	SEE 33482-6246	34950-1210	34950-1220
KEY A, BLACK	33482-1247	A-BLK	GCP	PLR	M-R		2	3	4			7	8					PLANNED OBSOLESCENCE	SEE 33482-6247	34950-1210	34950-1220
KEY A, BLACK	33482-1248	A-BLK	GCP	PLR	M-R	1		3	4	5	6	7	8					PLANNED OBSOLESCENCE	SEE 33482-6248	34950-1210	34950-1220



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-1249	A-BLK	GCP	PLR	M-R										10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6249	34950-1210	34950-1220
KEY A, BLACK	33482-1250	A-BLK	GCP	PLR	M-R				4	5	6	7	8	9				PLANNED OBSOLESCENCE	SEE 33482-6250	34950-1210	34950-1220
KEY A, BLACK	33482-1251	A-BLK	GCP	PLR	M-R		2		4	5			8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6251	34950-1210	34950-1220
KEY A, BLACK	33482-1252	A-BLK	GCP	PLR	M-R							7						PLANNED OBSOLESCENCE	SEE 33482-6252	34950-1210	34950-1220
KEY A, BLACK	33482-1253	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7	8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6253	34950-1210	34950-1220
KEY A, BLACK	33482-1254	A-BLK	GCP	PLR	M-R		2	3	4	5					10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6254	34950-1210	34950-1220
KEY A, BLACK	33482-1255	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7			10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6255	34950-1210	34950-1220
KEY A, BLACK	33482-1256	A-BLK	GCP	PLR	M-R	1					6	7		9				PLANNED OBSOLESCENCE	SEE 33482-6256	34950-1210	34950-1220
KEY A, BLACK	33482-1257	A-BLK	GCP	PLR	M-R									9	10		12	PLANNED OBSOLESCENCE	SEE 33482-6257	34950-1210	34950-1220
KEY A, BLACK	33482-1258	A-BLK	GCP	PLR	M-R		2	3								11		PLANNED OBSOLESCENCE	SEE 33482-6258	34950-1210	34950-1220
KEY A, BLACK	33482-1259	A-BLK	GCP	PLR	M-R	1	2	3	4	5				9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6259	34950-1210	34950-1220
KEY A, BLACK	33482-1260	A-BLK	GCP	PLR	M-R											11	12	PLANNED OBSOLESCENCE	SEE 33482-6260	34950-1210	34950-1220
KEY C, DARK GRAY	33482-1261	C-DG	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6261	34950-1210	34950-1220
KEY D, STONE GRAY	33482-1262	D-SG	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6262	34950-1210	34950-1220
KEY C, DARK GRAY	33482-1263	C-DG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6263	34950-1210	34950-1220
KEY D, STONE GRAY	33482-1264	D-SG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6264	34950-1210	34950-1220
KEY A, BLACK	33482-1265	A-BLK	GCP	PLR	M-R						6	7	8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6265	34950-1210	34950-1220
KEY A, BLACK	33482-1266	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6266	34950-1210	34950-1220
KEY A, BLACK	33482-1267	A-BLK	GCP	PLR	M-R			3	4	5	6	7						PLANNED OBSOLESCENCE	SEE 33482-6267	34950-1210	34950-1220
KEY A, BLACK	33482-1268	A-BLK	GCP	PLR	M-R			3	4	5	6	7	8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6268	34950-1210	34950-1220
KEY A, BLACK	33482-1269	A-BLK	GCP	PLR	M-R	1	2	3	4	5			8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6269	34950-1210	34950-1220
KEY A, BLACK	33482-1270	A-BLK	GCP	PLR	M-R		2		4			7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6270	34950-1210	34950-1220
KEY A, BLACK	33482-1271	A-BLK	GCP	PLR	M-R		2					7	8	9				PLANNED OBSOLESCENCE	SEE 33482-6271	34950-1210	34950-1220
KEY A, BLACK	33482-1272	A-BLK	GCP	PLR	M-R		2					7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6272	34950-1210	34950-1220
KEY A, BLACK	33482-1273	A-BLK	GCP	PLR	M-R								8					PLANNED OBSOLESCENCE	SEE 33482-6273	34950-1210	34950-1220
KEY A, BLACK	33482-1274	A-BLK	GCP	PLR	M-R	1		3	4	5	6		8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6274	34950-1210	34950-1220
KEY A, BLACK	33482-1275	A-BLK	GCP	PLR	M-R				4				8		10			PLANNED OBSOLESCENCE	SEE 33482-6275	34950-1210	34950-1220
KEY A, BLACK	33482-1276	A-BLK	GCP	PLR	M-R	1	2	3	4		6		8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6276	34950-1210	34950-1220
KEY A, BLACK	33482-1277	A-BLK	GCP	PLR	M-R	1	2	3								11	12	PLANNED OBSOLESCENCE	SEE 33482-6277	34950-1210	34950-1220
KEY A, BLACK	33482-1278	A-BLK	GCP	PLR	M-R						6						12	PLANNED OBSOLESCENCE	SEE 33482-6278	34950-1210	34950-1220
KEY A, BLACK	33482-1279	A-BLK	GCP	PLR	M-R	1	2	3	4	5		7	8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6279	34950-1210	34950-1220
KEY A, BLACK	33482-1280	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6			9				PLANNED OBSOLESCENCE	SEE 33482-6280	34950-1210	34950-1220
KEY A, BLACK	33482-1281	A-BLK	GCP	PLR	M-R		2		4		6		8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6281	34950-1210	34950-1220
KEY A, BLACK	33482-1282	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6			9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6282	34950-1210	34950-1220
KEY A, BLACK	33482-1283	A-BLK	GCP	PLR	M-R						6			9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6283	34950-1210	34950-1220
KEY A, BLACK	33482-1284	A-BLK	GCP	PLR	M-R	1		3	4	5	6	7	8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6284	34950-1210	34950-1220
KEY D, STONE GRAY	33482-1285	D-SG	GCP	PLR	M-R	1					6	7						PLANNED OBSOLESCENCE	SEE 33482-6285	34950-1210	34950-1220
KEY A, BLACK	33482-1286	A-BLK	GCP	PLR	M-R		2	3					8	9				PLANNED OBSOLESCENCE	SEE 33482-6286	34950-1210	34950-1220
KEY A, BLACK	33482-1287	A-BLK	GCP	PLR	M-R	1						7						PLANNED OBSOLESCENCE	SEE 33482-6287	34950-1210	34950-1220
KEY A, BLACK	33482-1288	A-BLK	GCP	PLR	M-R	1					6							PLANNED OBSOLESCENCE	SEE 33482-6288	34950-1210	34950-1220
KEY A, BLACK	33482-1289	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6		8					PLANNED OBSOLESCENCE	SEE 33482-6289	34950-1210	34950-1220
KEY A, BLACK	33482-1290	A-BLK	GCP	PLR	M-R	1						7					12	PLANNED OBSOLESCENCE	SEE 33482-6290	34950-1210	34950-1220
KEY A, BLACK	33482-1291	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8				12	PLANNED OBSOLESCENCE	SEE 33482-6291	34950-1210	34950-1220
KEY A, BLACK																					



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY C, BROWN	33482-1322	C-BR	GCP	PLR	M-R	1	2			5	6							PLANNED OBSOLESCENCE	SEE 33482-6322	34950-1210	34950-1220
KEY A, BLACK	33482-1323	A-BLK	GCP	PLR	M-R			3				7		9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6323	34950-1210	34950-1220
KEY A, BLACK	33482-1324	A-BLK	GCP	PLR	M-R			3						9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6324	34950-1210	34950-1220
KEY A, BLACK	33482-1325	A-BLK	GCP	PLR	M-R			3						9				PLANNED OBSOLESCENCE	SEE 33482-6325	34950-1210	34950-1220
KEY A, BLACK	33482-1326	A-BLK	GCP	PLR	M-R					5	6	7			10	11		PLANNED OBSOLESCENCE	SEE 33482-6326	34950-1210	34950-1220
KEY A, BLACK	33482-1327	A-BLK	GCP	PLR	M-R							7				11		PLANNED OBSOLESCENCE	SEE 33482-6327	34950-1210	34950-1220
KEY C, DARK GRAY	33482-1328	C-DG	GCP	PLR	M-R	1	2	3	4	5	6							PLANNED OBSOLESCENCE	SEE 33482-6328	34950-1210	34950-1220
KEY C, DARK GRAY	33482-1329	C-DG	GCP	PLR	M-R	1	2			5	6							PLANNED OBSOLESCENCE	SEE 33482-6329	34950-1210	34950-1220
KEY A, BLACK	33482-1330	A-BLK	GCP	PLR	M-R	1	2	3	4					9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6330	34950-1210	34950-1220
KEY A, BLACK	33482-1331	A-BLK	GCP	PLR	M-R	1	2				6	7	8				12	PLANNED OBSOLESCENCE	SEE 33482-6331	34950-1210	34950-1220
KEY A, BLACK	33482-1332	A-BLK	GCP	PLR	M-R				4	5		7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6332	34950-1210	34950-1220
KEY A, BLACK	33482-1333	A-BLK	GCP	PLR	M-R				4					9	10			PLANNED OBSOLESCENCE	SEE 33482-6333	34950-1210	34950-1220
KEY A, BLACK	33482-1334	A-BLK	GCP	PLR	M-R				4	5			8		10			PLANNED OBSOLESCENCE	SEE 33482-6334	34950-1210	34950-1220
KEY A, BLACK	33482-1335	A-BLK	GCP	PLR	M-R	1	2		4	5	6	7					12	PLANNED OBSOLESCENCE	SEE 33482-6335	34950-1210	34950-1220
KEY A, YELLOW	33482-1336	A-YL	GCP	PLR	M-R													PLANNED OBSOLESCENCE	SEE 33482-6336	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1337	B-LG	GCP	PLR	M-R					5			8					PLANNED OBSOLESCENCE	SEE 33482-6337	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1338	B-LG	GCP	PLR	M-R					5			8			11	12	PLANNED OBSOLESCENCE	SEE 33482-6338	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1339	B-LG	GCP	PLR	M-R			3	4	5		8	9	10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6339	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1340	B-LG	GCP	PLR	M-R	1	2	3	4	5		8	9	10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6340	34950-1210	34950-1220
KEY A, BLACK	33482-1341	A-BLK	GCP	PLR	M-R	1	2	3		5			9		11			PLANNED OBSOLESCENCE	SEE 33482-6341	34950-1210	34950-1220
KEY A, BLACK	33482-1342	A-BLK	GCP	PLR	M-R		2	3		5						11		PLANNED OBSOLESCENCE	SEE 33482-6342	34950-1210	34950-1220
KEY A, BLACK	33482-1343	A-BLK	GCP	PLR	M-R	1	2	3						9		11		PLANNED OBSOLESCENCE	SEE 33482-6343	34950-1210	34950-1220
KEY A, BLACK	33482-1344	A-BLK	GCP	PLR	M-R	1	2	3	4	5				9		11	12	PLANNED OBSOLESCENCE	SEE 33482-6344	34950-1210	34950-1220
KEY A, BLACK	33482-1345	A-BLK	GCP	PLR	M-R		2	3	4	5						11	12	PLANNED OBSOLESCENCE	SEE 33482-6345	34950-1210	34950-1220
KEY A, BLACK	33482-1346	A-BLK	GCP	PLR	M-R	1												PLANNED OBSOLESCENCE	SEE 33482-6346	34950-1210	34950-1220
KEY A, BLACK	33482-1347	A-BLK	GCP	PLR	M-R	1	2	3										PLANNED OBSOLESCENCE	SEE 33482-6347	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1348	B-LG	GCP	PLR	M-R	1	2	3	4		6					11	12	PLANNED OBSOLESCENCE	SEE 33482-6348	34950-1210	34950-1220
KEY A, BLACK	33482-1349	A-BLK	GCP	PLR	M-R				4			7	8					PLANNED OBSOLESCENCE	SEE 33482-6349	34950-1210	34950-1220
KEY A, BLACK	33482-1350	A-BLK	GCP	PLR	M-R		2					8						PLANNED OBSOLESCENCE	SEE 33482-6350	34950-1210	34950-1220
KEY A, BLACK	33482-1351	A-BLK	GCP	PLR	M-R		2		4			8			10			PLANNED OBSOLESCENCE	SEE 33482-6351	34950-1210	34950-1220
KEY A, BLACK	33482-1352	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6		8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6352	34950-1210	34950-1220
KEY A, BLACK	33482-1353	A-BLK	GCP	PLR	M-R	1					6	7	8				12	PLANNED OBSOLESCENCE	SEE 33482-6353	34950-1210	34950-1220
KEY A, BLACK	33482-1354	A-BLK	GCP	PLR	M-R		2	3	4		6		8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6354	34950-1210	34950-1220
KEY A, BLACK	33482-1355	A-BLK	GCP	PLR	M-R		2				6	7	8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6355	34950-1210	34950-1220
KEY A, BLACK	33482-1356	A-BLK	GCP	PLR	M-R	1	2	3	4		6				10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6356	34950-1210	34950-1220
KEY A, BLACK	33482-1357	A-BLK	GCP	PLR	M-R					5			8					PLANNED OBSOLESCENCE	SEE 33482-6357	34950-1210	34950-1220
KEY A, BLACK	33482-1358	A-BLK	GCP	PLR	M-R				4						10			PLANNED OBSOLESCENCE	SEE 33482-6358	34950-1210	34950-1220
KEY A, BLACK	33482-1359	A-BLK	GCP	PLR	M-R				4			7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6359	34950-1210	34950-1220
KEY A, BLACK	33482-1360	A-BLK	GCP	PLR	M-R					5	6		8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6360	34950-1210	34950-1220
KEY A, BLACK	33482-1361	A-BLK	GCP	PLR	M-R				4	5	6		8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6361	34950-1210	34950-1220
KEY A, BLACK	33482-1362	A-BLK	GCP	PLR	M-R	1	2	3		5	6	7	8	9		11	12	PLANNED OBSOLESCENCE	SEE 33482-6362	34950-1210	34950-1220
KEY A, BLACK	33482-1363	A-BLK	GCP	PLR	M-R				4	5		7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6363	34950-1210	34950-1220
KEY A, BLACK	33482-1364	A-BLK	GCP	PLR	M-R				4			7		9	10			PLANNED OBSOLESCENCE	SEE 33482-6364	34950-1210	34950-1220
KEY A, BLACK	33482-1365	A-BLK	GCP																		



MX150 2X6 BLADE SEALED ASSY MAT SEAL

BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY B, LIGHT GRAY	33482-1395	B-LG	GCP	PLR	M-R	1	2	3	4				8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6395	34950-1210	34950-1220
KEY A, BLACK	33482-1396	A-BLK	GCP	PLR	M-R	1					6	7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6396	34950-1210	34950-1220
KEY A, BLACK	33482-1397	A-BLK	GCP	PLR	M-R				4		6		8					PLANNED OBSOLESCENCE	SEE 33482-6397	34950-1210	34950-1220
KEY A, BLACK	33482-1398	A-BLK	GCP	PLR	M-R				4	5	6	7				11	12	PLANNED OBSOLESCENCE	SEE 33482-6398	34950-1210	34950-1220
KEY A, BLACK	33482-1399	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8			11	12	PLANNED OBSOLESCENCE	SEE 33482-6399	34950-1210	34950-1220
KEY A, BLACK	33482-1400	A-BLK	GCP	PLR	M-R	1	2	3				7	8					PLANNED OBSOLESCENCE	SEE 33482-6400	34950-1210	34950-1220
KEY A, BLACK	33482-1401	A-BLK	GCP	PLR	M-R	1	2	3				7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6401	34950-1210	34950-1220
KEY A, BLACK	33482-1402	A-BLK	GCP	PLR	M-R				4	5	6		8					PLANNED OBSOLESCENCE	SEE 33482-6402	34950-1210	34950-1220
KEY A, BLACK	33482-1403	A-BLK	GCP	PLR	M-R					5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6403	34950-1210	34950-1220
KEY A, BLACK	33482-1404	A-BLK	GCP	PLR	M-R						5	6	7	8			12	PLANNED OBSOLESCENCE	SEE 33482-6404	34950-1210	34950-1220
KEY A, BLACK	33482-1405	A-BLK	GCP	PLR	M-R							7	8				12	PLANNED OBSOLESCENCE	SEE 33482-6405	34950-1210	34950-1220
KEY A, BLACK	33482-1406	A-BLK	GCP	PLR	M-R		2	3		5	6	7		9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6406	34950-1210	34950-1220
KEY A, BLACK	33482-1407	A-BLK	GCP	PLR	M-R			3							10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6407	34950-1210	34950-1220
KEY A, BLACK	33482-1408	A-BLK	GCP	PLR	M-R				4	5	6	7	8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6408	34950-1210	34950-1220
KEY A, BLACK	33482-1409	A-BLK	GCP	PLR	M-R			3	4	5	6	7	8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6409	34950-1210	34950-1220
KEY A, BLACK	33482-1410	A-BLK	GCP	PLR	M-R	1	2	3	4				8	9				PLANNED OBSOLESCENCE	SEE 33482-6410	34950-1210	34950-1220
KEY A, BLACK	33482-1411	A-BLK	GCP	PLR	M-R		2	3						9				PLANNED OBSOLESCENCE	SEE 33482-6411	34950-1210	34950-1220
KEY A, BLACK	33482-1412	A-BLK	GCP	PLR	M-R								8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6412	34950-1210	34950-1220
KEY A, BLACK	33482-1413	A-BLK	GCP	PLR	M-R	1		3		5						11		PLANNED OBSOLESCENCE	SEE 33482-6413	34950-1210	34950-1220
KEY A, BLACK	33482-1414	A-BLK	GCP	PLR	M-R	1		3		5			8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6414	34950-1210	34950-1220
KEY A, BLACK	33482-1415	A-BLK	GCP	PLR	M-R		2	3		5	6	7		9		11	12	PLANNED OBSOLESCENCE	SEE 33482-6415	34950-1210	34950-1220
KEY A, BLACK	33482-1416	A-BLK	GCP	PLR	M-R	1			4	5	6		8		10		12	PLANNED OBSOLESCENCE	SEE 33482-6416	34950-1210	34950-1220
KEY A, BLACK	33482-1417	A-BLK	GCP	PLR	M-R	1			4	5			8		10		12	PLANNED OBSOLESCENCE	SEE 33482-6417	34950-1210	34950-1220
KEY A, BLACK	33482-1418	A-BLK	GCP	PLR	M-R	1	2	3	4	5			8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6418	34950-1210	34950-1220
KEY A, BLACK	33482-1419	A-BLK	GCP	PLR	M-R		2	3		5	6	7		9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6419	34950-1210	34950-1220
KEY A, BLACK	33482-1420	A-BLK	GCP	PLR	M-R	1	2	3	4				8	9				PLANNED OBSOLESCENCE	SEE 33482-6420	34950-1210	34950-1220
KEY A, BLACK	33482-1421	A-BLK	GCP	PLR	M-R		2	3						9				PLANNED OBSOLESCENCE	SEE 33482-6421	34950-1210	34950-1220
KEY A, BLACK	33482-1422	A-BLK	GCP	PLR	M-R								8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6422	34950-1210	34950-1220
KEY A, BLACK	33482-1423	A-BLK	GCP	PLR	M-R	1		3		5						11		PLANNED OBSOLESCENCE	SEE 33482-6423	34950-1210	34950-1220
KEY A, BLACK	33482-1424	A-BLK	GCP	PLR	M-R	1		3		5			8		10	11		PLANNED OBSOLESCENCE	SEE 33482-6424	34950-1210	34950-1220
KEY A, BLACK	33482-1425	A-BLK	GCP	PLR	M-R		2		4		6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6425	34950-1210	34950-1220
KEY A, BLACK	33482-1426	A-BLK	GCP	PLR	M-R			3	4							11	12	PLANNED OBSOLESCENCE	SEE 33482-6426	34950-1210	34950-1220
KEY A, BLACK	33482-1427	A-BLK	GCP	PLR	M-R			3	4					9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6427	34950-1210	34950-1220
KEY A, BLACK	33482-1428	A-BLK	GCP	PLR	M-R	1	2			5	6	7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6428	34950-1210	34950-1220
KEY A, BLACK	33482-1429	A-BLK	GCP	PLR	M-R									9	10			PLANNED OBSOLESCENCE	SEE 33482-6429	34950-1210	34950-1220
KEY A, BLACK	33482-1430	A-BLK	GCP	PLR	M-R			3	4	5	6		8	9				PLANNED OBSOLESCENCE	SEE 33482-6430	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1431	B-LG	GCP	PLR	M-R	1	2	3	4				8			11	12	PLANNED OBSOLESCENCE	SEE 33482-6431	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1432	B-LG	GCP	PLR	M-R	1	2	3	4				8					PLANNED OBSOLESCENCE	SEE 33482-6432	34950-1210	34950-1220
KEY A, BLACK	33482-1433	A-BLK	GCP	PLR	M-R										10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6433	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1434	B-LG	GCP	PLR	M-R							7	8	9			12	PLANNED OBSOLESCENCE	SEE 33482-6434	34950-1210	34950-1220
KEY A, BLACK	33482-1435	A-BLK	GCP	PLR	M-R							7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6435	34950-1210	34950-1220
KEY A, BLACK	33482-1436	A-BLK	GCP	PLR	M-R		2						8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6436	34950-1210	34950-1220
KEY A, BLACK	33482-1437	A-BLK	GCP	PLR	M-R		2						8	9				PLANNED OBSOLESCENCE	SEE 33482-6437	34950-1210	34950-1220
KEY B, LIGHT GRAY	3																				



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12					
KEY A, BLACK	33482-1468	A-BLK	GCP	PLR	M-R				4	5			8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6468	34950-1210	34950-1220	
KEY A, BLACK	33482-1469	A-BLK	GCP	PLR	M-R	1								9	10			PLANNED OBSOLESCENCE	SEE 33482-6469	34950-1210	34950-1220	
KEY A, BLACK	33482-1470	A-BLK	GCP	PLR	M-R							7	8	9			12	PLANNED OBSOLESCENCE	SEE 33482-6470	34950-1210	34950-1220	
KEY C, DARK GRAY	33482-1471	C-DG	GCP	PLR	M-R			3	4				8					PLANNED OBSOLESCENCE	SEE 33482-6471	34950-1210	34950-1220	
KEY A, BLACK	33482-1472	A-BLK	GCP	PLR	M-R	1	2					7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6472	34950-1210	34950-1220	
KEY A, BLACK	33482-1473	A-BLK	GCP	PLR	M-R					5		7	8	9		11		PLANNED OBSOLESCENCE	SEE 33482-6473	34950-1210	34950-1220	
KEY A, BLACK	33482-1474	A-BLK	GCP	PLR	M-R	1	2				5				10		12	PLANNED OBSOLESCENCE	SEE 33482-6474	34950-1210	34950-1220	
KEY A, BLACK	33482-1475	A-BLK	GCP	PLR	M-R						5							PLANNED OBSOLESCENCE	SEE 33482-6475	34950-1210	34950-1220	
KEY A, BLACK	33482-1476	A-BLK	GCP	PLR	M-R			3	4	5								PLANNED OBSOLESCENCE	SEE 33482-6476	34950-1210	34950-1220	
KEY A, BLACK	33482-1477	A-BLK	GCP	PLR	M-R	1	2				5			9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6477	34950-1210	34950-1220	
KEY A, BLACK	33482-1478	A-BLK	GCP	PLR	M-R						5			9		11		PLANNED OBSOLESCENCE	SEE 33482-6478	34950-1210	34950-1220	
KEY A, BLACK	33482-1479	A-BLK	GCP	PLR	M-R	1							8			11		PLANNED OBSOLESCENCE	SEE 33482-6479	34950-1210	34950-1220	
KEY A, BLACK	33482-1480	A-BLK	GCP	PLR	M-R	1			4	5	6	7						PLANNED OBSOLESCENCE	SEE 33482-6480	34950-1210	34950-1220	
KEY A, BLACK	33482-1481	A-BLK	GCP	PLR	M-R	1			4	5	6	7	8			11		PLANNED OBSOLESCENCE	SEE 33482-6481	34950-1210	34950-1220	
KEY A, BLACK	33482-1482	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8			11		PLANNED OBSOLESCENCE	SEE 33482-6482	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1483	B-LG	GCP	PLR	M-R	1					6	7			10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6483	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1484	B-LG	GCP	PLR	M-R	1					6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6484	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1485	B-LG	GCP	PLR	M-R	1					5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6485	34950-1210	34950-1220
KEY A, BLACK	33482-1486	A-BLK	GCP	PLR	M-R	1	2				5		7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6486	34950-1210	34950-1220
KEY A, BLACK	33482-1487	A-BLK	GCP	PLR	M-R							7				11	12	PLANNED OBSOLESCENCE	SEE 33482-6487	34950-1210	34950-1220	
KEY A, BLACK	33482-1488	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8			11	12	PLANNED OBSOLESCENCE	SEE 33482-6488	34950-1210	34950-1220	
KEY A, BLACK	33482-1489	A-BLK	GCP	PLR	M-R			3				7	8			11	12	PLANNED OBSOLESCENCE	SEE 33482-6489	34950-1210	34950-1220	
KEY A, BLACK	33482-1490	A-BLK	GCP	PLR	M-R	1	2	3	4						11	12		PLANNED OBSOLESCENCE	SEE 33482-6490	34950-1210	34950-1220	
KEY A, BLACK	33482-1491	A-BLK	GCP	PLR	M-R	1		3		5		7		9				PLANNED OBSOLESCENCE	SEE 33482-6491	34950-1210	34950-1220	
KEY A, BLACK	33482-1492	A-BLK	GCP	PLR	M-R		2				6	7	8					PLANNED OBSOLESCENCE	SEE 33482-6492	34950-1210	34950-1220	
KEY A, BLACK	33482-1493	A-BLK	GCP	PLR	M-R					5		7		9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6493	34950-1210	34950-1220	
KEY A, BLACK	33482-1494	A-BLK	GCP	PLR	M-R					5				9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6494	34950-1210	34950-1220	
KEY A, BLACK	33482-1495	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6		8	9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6495	34950-1210	34950-1220	
KEY A, BLACK	33482-1496	A-BLK	GCP	PLR	M-R	1	2	3	4		6	7	8	9			12	PLANNED OBSOLESCENCE	SEE 33482-6496	34950-1210	34950-1220	
KEY A, BLACK	33482-1497	A-BLK	GCP	PLR	M-R							7		9			12	PLANNED OBSOLESCENCE	SEE 33482-6497	34950-1210	34950-1220	
KEY A, BLACK	33482-1498	A-BLK	GCP	PLR	M-R	1	2		4	5	6	7	8	9			12	PLANNED OBSOLESCENCE	SEE 33482-6498	34950-1210	34950-1220	
KEY A, BLACK	33482-1499	A-BLK	GCP	PLR	M-R			3						9	10	11		PLANNED OBSOLESCENCE	SEE 33482-6499	34950-1210	34950-1220	
KEY A, BLACK	33482-1500	A-BLK	GCP	PLR	M-R		2			5		7			10			PLANNED OBSOLESCENCE	SEE 33482-6500	34950-1210	34950-1220	
KEY A, BLACK	33482-1501	A-BLK	GCP	PLR	M-R				4			7						PLANNED OBSOLESCENCE	SEE 33482-6501	34950-1210	34950-1220	
KEY A, BLACK	33482-1502	A-BLK	GCP	PLR	M-R				4		6	7						PLANNED OBSOLESCENCE	SEE 33482-6502	34950-1210	34950-1220	
KEY A, BLACK	33482-1503	A-BLK	GCP	PLR	M-R						6	7	8					PLANNED OBSOLESCENCE	SEE 33482-6503	34950-1210	34950-1220	
KEY A, BLACK	33482-1504	A-BLK	GCP	PLR	M-R		2	3	4	5	6		8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6504	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1505	B-LG	GCP	PLR	M-R					5			8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6505	34950-1210	34950-1220	
KEY A, BLACK	33482-1506	A-BLK	GCP	PLR	M-R								8	9			12	PLANNED OBSOLESCENCE	SEE 33482-6506	34950-1210	34950-1220	
KEY A, BLACK	33482-1507	A-BLK	GCP	PLR	M-R	1	2		4	5	6		8					PLANNED OBSOLESCENCE	SEE 33482-6507	34950-1210	34950-1220	
KEY A, BLACK	33482-6201	A-BLK	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6202	B-LG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220	
KEY C, BROWN	33482-6203	C-BR	GCP	PLR	M-B													NOT RECOMMENDED	SEE 33482-6261	34950-1210	34950-1220	
KEY D, GREEN	33482-6204	D-GR	GCP	PLR	M-B													NOT				



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-6234	A-BLK	GCP	PLR	M-B						6	7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6235	A-BLK	GCP	PLR	M-B		2	3			6	7	8		10	11		SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6236	B-LG	GCP	PLR	M-B	1				5	6	7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6237	A-BLK	GCP	PLR	M-B		2											SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6238	B-LG	GCP	PLR	M-B		2							9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6239	A-BLK	GCP	PLR	M-B	1				5	6	7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6240	A-BLK	GCP	PLR	M-B		2	3					8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6241	A-BLK	GCP	PLR	M-B							7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6242	A-BLK	GCP	PLR	M-B							7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6243	A-BLK	GCP	PLR	M-B		2							9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6244	A-BLK	GCP	PLR	M-B		2		4									SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6245	A-BLK	GCP	PLR	M-B									9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6246	A-BLK	GCP	PLR	M-B											11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6247	A-BLK	GCP	PLR	M-B		2	3	4			7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6248	A-BLK	GCP	PLR	M-B	1		3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6249	A-BLK	GCP	PLR	M-B										10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6250	A-BLK	GCP	PLR	M-B				4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6251	A-BLK	GCP	PLR	M-B		2		4	5			8		10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6252	A-BLK	GCP	PLR	M-B							7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6253	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6254	A-BLK	GCP	PLR	M-B		2	3	4	5					10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6255	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6256	A-BLK	GCP	PLR	M-B	1					6	7		9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6257	A-BLK	GCP	PLR	M-B									9	10		12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6258	A-BLK	GCP	PLR	M-B		2	3								11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6259	A-BLK	GCP	PLR	M-B	1	2	3	4	5				9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6260	A-BLK	GCP	PLR	M-B											11	12	SALEABLE		34950-1210	34950-1220
KEY C, DARK GRAY	33482-6261	C-DG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220
KEY D, STONE GRAY	33482-6262	D-SG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220
KEY C, DARK GRAY	33482-6263	C-DG	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY D, STONE GRAY	33482-6264	D-SG	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6265	A-BLK	GCP	PLR	M-B						6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6266	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7					12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6267	A-BLK	GCP	PLR	M-B			3	4	5	6	7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6268	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6269	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6270	A-BLK	GCP	PLR	M-B		2		4			7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6271	A-BLK	GCP	PLR	M-B		2					7	8	9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6272	A-BLK	GCP	PLR	M-B		2					7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6273	A-BLK	GCP	PLR	M-B								8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6274	A-BLK	GCP	PLR	M-B	1		3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6275	A-BLK	GCP	PLR	M-B				4				8		10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6276	A-BLK	GCP	PLR	M-B	1	2	3	4		6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6277	A-BLK	GCP	PLR	M-B	1	2	3								11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6278	A-BLK	GCP	PLR	M-B						6						12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6279	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6280	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6			9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6281	A-BLK	GCP	PLR	M-B		2		4		6		8		10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6282	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6			9	10	11	12	SALEABLE		34950-1210	34950-1220



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-6307	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6308	A-BLK	GCP	PLR	M-B							7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6309	A-BLK	GCP	PLR	M-B	1							8		10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6310	A-BLK	GCP	PLR	M-B	1			4							11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6311	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7		9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6312	A-BLK	GCP	PLR	M-B								8	9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6313	A-BLK	GCP	PLR	M-B			3	4	5	6		8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6314	A-BLK	GCP	PLR	M-B			3			6	7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6315	A-BLK	GCP	PLR	M-B						6	7	8	9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6316	A-BLK	GCP	PLR	M-B					5	6	7	8			11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6317	A-BLK	GCP	PLR	M-B	1	2											SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6318	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6319	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220
KEY C, DARK GRAY	33482-6320	C-DG	GCP	PLR	M-B	1					6	7						SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-6321	C-BR	GCP	PLR	M-B	1	2	3	4	5	6							NOT RECOMMENDED	SEE 33482-6328	34950-1210	34950-1220
KEY C, BROWN	33482-6322	C-BR	GCP	PLR	M-B	1	2			5	6							NOT RECOMMENDED	SEE 33482-6329	34950-1210	34950-1220
KEY A, BLACK	33482-6323	A-BLK	GCP	PLR	M-B			3				7		9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6324	A-BLK	GCP	PLR	M-B			3						9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6325	A-BLK	GCP	PLR	M-B			3						9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6326	A-BLK	GCP	PLR	M-B					5	6	7			10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6327	A-BLK	GCP	PLR	M-B							7				11		SALEABLE		34950-1210	34950-1220
KEY C, DARK GRAY	33482-6328	C-DG	GCP	PLR	M-B	1	2	3	4	5	6							SALEABLE		34950-1210	34950-1220
KEY C, DARK GRAY	33482-6329	C-DG	GCP	PLR	M-B	1	2			5	6							SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6330	A-BLK	GCP	PLR	M-B	1	2	3	4					9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6331	A-BLK	GCP	PLR	M-B	1	2				6	7	8				12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6332	A-BLK	GCP	PLR	M-B				4	5		7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6333	A-BLK	GCP	PLR	M-B				4					9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6334	A-BLK	GCP	PLR	M-B				4	5			8		10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6335	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7					12	SALEABLE		34950-1210	34950-1220
KEY A, YELLOW	33482-6336	A-YL	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6337	B-LG	GCP	PLR	M-B					5			8					SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6338	B-LG	GCP	PLR	M-B					5			8			11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6339	B-LG	GCP	PLR	M-B			3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6340	B-LG	GCP	PLR	M-B	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6341	A-BLK	GCP	PLR	M-B	1	2	3		5				9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6342	A-BLK	GCP	PLR	M-B		2	3		5						11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6343	A-BLK	GCP	PLR	M-B	1	2	3						9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6344	A-BLK	GCP	PLR	M-B	1	2	3	4	5				9		11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6345	A-BLK	GCP	PLR	M-B		2	3	4	5						11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6346	A-BLK	GCP	PLR	M-B	1												SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6347	A-BLK	GCP	PLR	M-B	1	2	3										SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6348	B-LG	GCP	PLR	M-B	1	2	3	4		6					11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6349	A-BLK	GCP	PLR	M-B				4			7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6350	A-BLK	GCP	PLR	M-B		2						8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6351	A-BLK	GCP	PLR	M-B		2		4				8		10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6352	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6353	A-BLK	GCP	PLR	M-B	1					6	7	8				12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6354	A-BLK	GCP	PLR	M-B		2	3	4		6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6355	A-BLK	GCP	PLR	M-B		2				6	7	8		10	11		SALEABLE		34950-12	



MX150 2X6 BLADE SEALED ASSY MAT SEAL

BOM AND PIN OUT SHEET


ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12					
KEY A, BLACK	33482-6380	A-BLK	GCP	PLR	M-B		2						7	8				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6381	A-BLK	GCP	PLR	M-B		2			4			7	8				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6382	A-BLK	GCP	PLR	M-B					4	5	6		8		10	11	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6383	A-BLK	GCP	PLR	M-B	1	2	3	4				7	8	9	10	11	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6384	A-BLK	GCP	PLR	M-B				3	4					9	10		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6385	A-BLK	GCP	PLR	M-B				3	4							11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6386	A-BLK	GCP	PLR	M-B	1	2	3	4		6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6387	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9			12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6388	A-BLK	GCP	PLR	M-B	1	2	3							10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6389	A-BLK	GCP	PLR	M-B	1	2	3			6					11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6390	A-BLK	GCP	PLR	M-B	1			3	4						11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6391	A-BLK	GCP	PLR	M-B	1	2	3			6				10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6392	A-BLK	GCP	PLR	M-B	1			3	4						11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6393	A-BLK	GCP	PLR	M-B				4	5		7				11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6394	B-LG	GCP	PLR	M-B	1	2	3	4				8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6395	B-LG	GCP	PLR	M-B	1	2	3	4				8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6396	A-BLK	GCP	PLR	M-B	1					6	7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6397	A-BLK	GCP	PLR	M-B				4		6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6398	A-BLK	GCP	PLR	M-B				4	5	6	7				11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6399	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6400	A-BLK	GCP	PLR	M-B	1	2	3				7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6401	A-BLK	GCP	PLR	M-B	1	2	3				7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6402	A-BLK	GCP	PLR	M-B				4	5	6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6403	A-BLK	GCP	PLR	M-B					5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6404	A-BLK	GCP	PLR	M-B					5	6	7	8				12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6405	A-BLK	GCP	PLR	M-B							7	8				12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6406	A-BLK	GCP	PLR	M-B		2	3		5	6	7		9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6407	A-BLK	GCP	PLR	M-B			3							10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6408	A-BLK	GCP	PLR	M-B				4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6409	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6410	A-BLK	GCP	PLR	M-B	1	2	3	4				8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6411	A-BLK	GCP	PLR	M-B		2	3						9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6412	A-BLK	GCP	PLR	M-B								8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6413	A-BLK	GCP	PLR	M-B	1		3		5						11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6414	A-BLK	GCP	PLR	M-B	1		3		5			8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6415	A-BLK	GCP	PLR	M-B		2	3		5	6	7		9		11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6416	A-BLK	GCP	PLR	M-B	1			4	5	6		8		10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6417	A-BLK	GCP	PLR	M-B	1			4	5			8		10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6418	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6419	A-BLK	GCP	PLR	M-B		2	3		5	6	7		9	10	11	12	SALEABLE	SEE 33482-6406	34950-1210	34950-1220	
KEY A, BLACK	33482-6420	A-BLK	GCP	PLR	M-B	1	2	3	4				8	9				SALEABLE	SEE 33482-6410	34950-1210	34950-1220	
KEY A, BLACK	33482-6421	A-BLK	GCP	PLR	M-B		2	3						9				SALEABLE	SEE 33482-6411	34950-1210	34950-1220	
KEY A, BLACK	33482-6422	A-BLK	GCP	PLR	M-B								8		10	11		SALEABLE	SEE 33482-6412	34950-1210	34950-1220	
KEY A, BLACK	33482-6423	A-BLK	GCP	PLR	M-B	1		3		5						11		SALEABLE	SEE 33482-6413	34950-1210	34950-1220	
KEY A, BLACK	33482-6424	A-BLK	GCP	PLR	M-B	1		3		5			8		10	11		SALEABLE	SEE 33482-6414	34950-1210	34950-1220	
KEY A, BLACK	33482-6425	A-BLK	GCP	PLR	M-B		2		4		6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6426	A-BLK	GCP	PLR	M-B				3	4						11	12	SALEABLE	SEE 33482-6385	34950-1210	34950-1220-	



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-6453	A-BLK	GCP	PLR	M-B	1	2	3	4				8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6454	A-BLK	GCP	PLR	M-B	1		3	4			7	8	9			12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6455	A-BLK	GCP	PLR	M-B	1			4			7	8				12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6456	A-BLK	GCP	PLR	M-B	1	2		4	5	6					11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6457	A-BLK	GCP	PLR	M-B		2		4	5	6	7					12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6458	A-BLK	GCP	PLR	M-B		2				6						12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6459	A-BLK	GCP	PLR	M-B			3				7	8	9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6460	A-BLK	GCP	PLR	M-B	1						7	8				12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6461	A-BLK	GCP	PLR	M-B		2			5	6	7	8			11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6462	A-BLK	GCP	PLR	M-B		2	3		5	6	7	8	9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6463	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7				11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6464	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6465	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7		9		11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6466	A-BLK	GCP	PLR	M-B												12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6467	A-BLK	GCP	PLR	M-B		2	3	4									SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6468	A-BLK	GCP	PLR	M-B				4	5			8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6469	A-BLK	GCP	PLR	M-B	1								9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6470	A-BLK	GCP	PLR	M-B							7	8	9			12	SALEABLE		34950-1210	34950-1220
KEY C, DARK GRAY	33482-6471	C-DG	GCP	PLR	M-B			3	4				8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6472	A-BLK	GCP	PLR	M-B	1	2					7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6473	A-BLK	GCP	PLR	M-B					5		7	8	9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6474	A-BLK	GCP	PLR	M-B	1	2			5					10		12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6475	A-BLK	GCP	PLR	M-B					5								SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6476	A-BLK	GCP	PLR	M-B			3	4	5								SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6477	A-BLK	GCP	PLR	M-B	1	2			5				9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6478	A-BLK	GCP	PLR	M-B					5				9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6479	A-BLK	GCP	PLR	M-B	1							8			11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6480	A-BLK	GCP	PLR	M-B	1			4	5	6	7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6481	A-BLK	GCP	PLR	M-B	1			4	5	6	7	8			11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6482	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11		SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6483	B-LG	GCP	PLR	M-B	1					6	7			10	11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6484	B-LG	GCP	PLR	M-B	1					6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-6485	B-LG	GCP	PLR	M-B	1				5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6486	A-BLK	GCP	PLR	M-B	1	2			5		7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6487	A-BLK	GCP	PLR	M-B							7				11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6488	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6489	A-BLK	GCP	PLR	M-B			3				7	8			11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6490	A-BLK	GCP	PLR	M-B	1	2	3	4							11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6491	A-BLK	GCP	PLR	M-B	1		3		5		7		9				SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6492	A-BLK	GCP	PLR	M-B		2				6	7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6493	A-BLK	GCP	PLR	M-B					5		7		9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6494	A-BLK	GCP	PLR	M-B					5				9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6495	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6496	A-BLK	GCP	PLR	M-B	1	2	3	4		6	7	8	9			12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6497	A-BLK	GCP	PLR	M-B							7		9			12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6498	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7	8	9			12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6499	A-BLK	GCP	PLR	M-B			3						9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6500	A-BLK	GCP	PLR	M-B		2			5		7			10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6501	A-BLK	GCP	PLR	M-B				4			7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6502	A-BLK	GCP	PLR	M-B				4		6	7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6503	A-BLK	GCP	PLR	M-B						6	7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6504	A-BLK	GCP	PLR	M-B		2	3	4	5	6		8	9	10	11	12	SALEABLE</			

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16							
KEY A, BLACK	33482-1601	A-BLK	GCP	PLR	M-R																	PLANNED OBSOLESCENCE	SEE 33482-8601	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1602	B-LG	GCP	PLR	M-R																	PLANNED OBSOLESCENCE	SEE 33482-8602	34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, BROWN	33482-1603	C-BR	GCP	PLR	M-R																	PLANNED OBSOLESCENCE	SEE 33482-8603	34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, GREEN	33482-1604	D-GR	GCP	PLR	M-R																	PLANNED OBSOLESCENCE	SEE 33482-8604	34950-1611	34950-1621	34951-1631	34951-1641	
VOID KEY	33482-1605																											
KEY A, BLACK	33482-1606	A-BLK	GCP	PLR	M-R								8									PLANNED OBSOLESCENCE	SEE 33482-8606	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1607	B-LG	GCP	PLR	M-R								8									PLANNED OBSOLESCENCE	SEE 33482-8607	34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, BROWN	33482-1608	C-BR	GCP	PLR	M-R								8									PLANNED OBSOLESCENCE	SEE 33482-8608	34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, GREEN	33482-1609	D-GR	GCP	PLR	M-R								8									PLANNED OBSOLESCENCE	SEE 33482-8609	34950-1611	34950-1621	34951-1631	34951-1641	
VOID KEY	33482-1610																											
KEY A, BLACK	33482-1611	A-BLK	GCP	PLR	M-R								8	9								PLANNED OBSOLESCENCE	SEE 33482-8611	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1612	B-LG	GCP	PLR	M-R								8	9								PLANNED OBSOLESCENCE	SEE 33482-8612	34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, BROWN	33482-1613	C-BR	GCP	PLR	M-R								8	9								PLANNED OBSOLESCENCE	SEE 33482-8613	34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, GREEN	33482-1614	D-GR	GCP	PLR	M-R								8	9								PLANNED OBSOLESCENCE	SEE 33482-8614	34950-1611	34950-1621	34951-1631	34951-1641	
VOID KEY	33482-1615																											
KEY A, BLACK	33482-1616	A-BLK	GCP	PLR	M-R	1							8	9								PLANNED OBSOLESCENCE	SEE 33482-8616	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1617	B-LG	GCP	PLR	M-R	1							8	9								PLANNED OBSOLESCENCE	SEE 33482-8617	34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, BROWN	33482-1618	C-BR	GCP	PLR	M-R	1							8	9								PLANNED OBSOLESCENCE	SEE 33482-8618	34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, GREEN	33482-1619	D-GR	GCP	PLR	M-R	1							8	9								PLANNED OBSOLESCENCE	SEE 33482-8619	34950-1611	34950-1621	34951-1631	34951-1641	
VOID KEY	33482-1620																											
KEY A, BLACK	33482-1621	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8621	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1622	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8622	34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, BROWN	33482-1623	C-BR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8623	34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, GREEN	33482-1624	D-GR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8624	34950-1611	34950-1621	34951-1631	34951-1641	
VOID KEY	33482-1625																											
KEY A, BLACK	33482-1626	A-BLK	GCP	PLR	M-R								8	9						15		PLANNED OBSOLESCENCE	SEE 33482-8626	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1627	A-BLK	GCP	PLR	M-R	1							8	9							16	PLANNED OBSOLESCENCE	SEE 33482-8627	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1628	B-LG	GCP	PLR	M-R	1							8	9							16	PLANNED OBSOLESCENCE	SEE 33482-8628	34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, BROWN	33482-1629	C-BR	GCP	PLR	M-R	1							8	9							16	PLANNED OBSOLESCENCE	SEE 33482-8629	34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, GREEN	33482-1630	D-GR	GCP	PLR	M-R	1							8	9							16	PLANNED OBSOLESCENCE	SEE 33482-8630	34950-1611	34950-1621	34951-1631	34951-1641	
VOID KEY	33482-1631																											
KEY A, BLACK	33482-1632	A-BLK	GCP	PLR	M-R				4			7	8				12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8632	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1633	A-BLK	GCP	PLR	M-R			3	4	5					10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8633	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1634	A-BLK	GCP	PLR	M-R							7	8				12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8634	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1635	B-LG	GCP	PLR	M-R								8					13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8635	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1636	A-BLK	GCP	PLR	M-R										10	11		13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8636	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1637	A-BLK	GCP	PLR	M-R										10	11				15	16	PLANNED OBSOLESCENCE	SEE 33482-8637	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1638	A-BLK	GCP	PLR	M-R								8	9	10	11	12				15	16	PLANNED OBSOLESCENCE	SEE 33482-8638	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1639	A-BLK	GCP	PLR	M-R															15		PLANNED OBSOLESCENCE	SEE 33482-8639	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1640	A-BLK	GCP	PLR	M-R					5											16	PLANNED OBSOLESCENCE	SEE 33482-8640	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1641	A-BLK	GCP	PLR	M-R					5												PLANNED OBSOLESCENCE	SEE 33482-8641	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1642	B-LG	GCP	PLR	M-R				4		6	7	8				12		14			PLANNED OBSOLESCENCE	SEE 33482-8642	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1643	A-BLK	GCP	PLR	M-R															15	16	PLANNED OBSOLESCENCE	SEE 33482-8643	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1644	B-LG	GCP	PLR	M-R				4													PLANNED OBSOLESCENCE	SEE 33482-8644	34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-1645	B-LG	GCP	PLR	M-R				4		6	7	8									PLANNED OBSOLESCENCE	SEE 33482-8645	34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-1646	A-BLK	GCP	PLR	M-R				4		6	7	8				12											

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16						
KEY A, BLACK	33482-1669	A-BLK	GCP	PLR	M-R		2				6				10			13	14			PLANNED OBSOLESCENCE	SEE 33482-8669	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1670	A-BLK	GCP	PLR	M-R		2		4	5	6	7	8		10	11	12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8670	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1671	A-BLK	GCP	PLR	M-R		2		4	5	6				10		12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8671	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1672	A-BLK	GCP	PLR	M-R				4				8									PLANNED OBSOLESCENCE	SEE 33482-8672	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1673	A-BLK	GCP	PLR	M-R		2				6	7	8									PLANNED OBSOLESCENCE	SEE 33482-8673	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1674	A-BLK	GCP	PLR	M-R		2			5	6											PLANNED OBSOLESCENCE	SEE 33482-8674	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1675	A-BLK	GCP	PLR	M-R		2			5	6					11						PLANNED OBSOLESCENCE	SEE 33482-8675	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1676	A-BLK	GCP	PLR	M-R					5	6	7	8					13				PLANNED OBSOLESCENCE	SEE 33482-8676	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1677	A-BLK	GCP	PLR	M-R					5	6	7	8			11		13				PLANNED OBSOLESCENCE	SEE 33482-8677	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1678	A-BLK	GCP	PLR	M-R					5	6	7	8				12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8678	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1679	A-BLK	GCP	PLR	M-R					5	6	7	8			11	12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8679	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1680	A-BLK	GCP	PLR	M-R					5	6	7	8			11	12	13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8680	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1681	A-BLK	GCP	PLR	M-R							7								15		PLANNED OBSOLESCENCE	SEE 33482-8681	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1682	A-BLK	GCP	PLR	M-R						5	6								15	16	PLANNED OBSOLESCENCE	SEE 33482-8682	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1683	A-BLK	GCP	PLR	M-R			3	4	5	6									15	16	PLANNED OBSOLESCENCE	SEE 33482-8683	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1684	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6		8					13		15	16	PLANNED OBSOLESCENCE	SEE 33482-8684	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1685	A-BLK	GCP	PLR	M-R													13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8685	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1686	A-BLK	GCP	PLR	M-R								8					13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8686	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1687	A-BLK	GCP	PLR	M-R								7	8		11	12	13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8687	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1688	A-BLK	GCP	PLR	M-R							7	8				12	13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8688	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1689	A-BLK	GCP	PLR	M-R							7	8			11		13				PLANNED OBSOLESCENCE	SEE 33482-8689	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1690	A-BLK	GCP	PLR	M-R							7	8					13				PLANNED OBSOLESCENCE	SEE 33482-8690	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1691	A-BLK	GCP	PLR	M-R					5								13				PLANNED OBSOLESCENCE	SEE 33482-8691	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1692	A-BLK	GCP	PLR	M-R		2							9	10					15	16	PLANNED OBSOLESCENCE	SEE 33482-8692	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1693	A-BLK	GCP	PLR	M-R		2								10					15		PLANNED OBSOLESCENCE	SEE 33482-8693	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1694	A-BLK	GCP	PLR	M-R		2			5	6	7	8	9	10		12		14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8694	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1695	A-BLK	GCP	PLR	M-R		2			5	6	7	8		10		12		14	15		PLANNED OBSOLESCENCE	SEE 33482-8695	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1700	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6				10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8700	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1701	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6					11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8701	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1702	A-BLK	GCP	PLR	M-R							7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8702	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1703	A-BLK	GCP	PLR	M-R								8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8703	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1704	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6								14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8704	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1705	A-BLK	GCP	PLR	M-R										10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8705	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1706	A-BLK	GCP	PLR	M-R											11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8706	34950-1611	349504		

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16						
KEY A, BLACK	33482-1765	A-BLK	GCP	PLR	M-R		2			5		7		9			12	13	14		16	PLANNED OBSOLESCENCE	SEE 33482-8765	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1766	A-BLK	GCP	PLR	M-R					5	6	7		9	10	11	12	13	14		16	PLANNED OBSOLESCENCE	SEE 33482-8766	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1767	A-BLK	GCP	PLR	M-R					5	6	7		9							16	PLANNED OBSOLESCENCE	SEE 33482-8767	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1768	A-BLK	GCP	PLR	M-R					5	6	7		9	10						16	PLANNED OBSOLESCENCE	SEE 33482-8768	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1769	A-BLK	GCP	PLR	M-R	1			4	5	6		8				12	13	14		16	PLANNED OBSOLESCENCE	SEE 33482-8769	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1770	A-BLK	GCP	PLR	M-R	1	2		4	5	6		8	9	10		12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8770	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1771	A-BLK	GCP	PLR	M-R	1			4		6	7	8		10			13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8771	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1772	A-BLK	GCP	PLR	M-R										10			13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8772	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1773	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6				11	12						PLANNED OBSOLESCENCE	SEE 33482-8773	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1774	A-BLK	GCP	PLR	M-R										10					15		PLANNED OBSOLESCENCE	SEE 33482-8774	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1775	A-BLK	GCP	PLR	M-R									9	10					15	16	PLANNED OBSOLESCENCE	SEE 33482-8775	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1776	A-BLK	GCP	PLR	M-R			3	4					9	10					15	16	PLANNED OBSOLESCENCE	SEE 33482-8776	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, YELLOW	33482-1777	A-YW	GCP	PLR	M-R																	PLANNED OBSOLESCENCE	SEE 33482-8777	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1778	A-BLK	GCP	PLR	M-R					5			8									PLANNED OBSOLESCENCE	SEE 33482-8778	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1779	A-BLK	GCP	PLR	M-R					5	6	7	8	9	10	11	12					PLANNED OBSOLESCENCE	SEE 33482-8779	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1780	A-BLK	GCP	PLR	M-R													13	14			PLANNED OBSOLESCENCE	SEE 33482-8780	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1781	A-BLK	GCP	PLR	M-R	1			4	5	6	7	8	9	10			13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8781	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1782	A-BLK	GCP	PLR	M-R	1			4		6	7	8		10	11	12	13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8782	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1783	A-BLK	GCP	PLR	M-R											11	12			15		PLANNED OBSOLESCENCE	SEE 33482-8783	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1784	A-BLK	GCP	PLR	M-R			3														PLANNED OBSOLESCENCE	SEE 33482-8784	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1785	A-BLK	GCP	PLR	M-R	1				5		7				11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8785	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1786	A-BLK	GCP	PLR	M-R		2			5		7		9		11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8786	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1787	A-BLK	GCP	PLR	M-R	1	2			5				9								PLANNED OBSOLESCENCE	SEE 33482-8787	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1788	A-BLK	GCP	PLR	M-R	1	2					7		9		11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8788	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1789	A-BLK	GCP	PLR	M-R	1	2			5				9						15		PLANNED OBSOLESCENCE	SEE 33482-8789	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1790	A-BLK	GCP	PLR	M-R	1	2			5		7		9		11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8790	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1791	A-BLK	GCP	PLR	M-R	1	2	3														PLANNED OBSOLESCENCE	SEE 33482-8791	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1792	A-BLK	GCP	PLR	M-R					5		7									16	PLANNED OBSOLESCENCE	SEE 33482-8792	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1793	A-BLK	GCP	PLR	M-R		2	3							10	11						PLANNED OBSOLESCENCE	SEE 33482-8793	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1794	A-BLK	GCP	PLR	M-R	1	2	3		5	6						12	13				PLANNED OBSOLESCENCE	SEE 33482-8794	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1795	A-BLK	GCP	PLR	M-R				3						10			13	14	15		PLANNED OBSOLESCENCE	SEE 33482-8795	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1796	A-BLK	GCP	PLR	M-R							7		9				14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8796	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1797	A-BLK	GCP	PLR	M-R							7	8				12					PLANNED OBSOLESCENCE	SEE 33482-8797	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1798	A-BLK	GCP	PLR	M-R			3							10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8798	34950-1611	34950-1621	34951-1631	349

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16							
KEY A, BLACK	33482-1857	A-BLK	GCP	PLR	M-R	1	2		4		6	7	8	9	10			12					PLANNED OBSOLESCENCE	SEE 33482-8857	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1858	A-BLK	GCP	PLR	M-R	1	2	3	4		6	7	8	9	10			13	14		16		PLANNED OBSOLESCENCE	SEE 33482-8858	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1859	A-BLK	GCP	PLR	M-R		2			5		7		9	10	11	12	13	14		16		PLANNED OBSOLESCENCE	SEE 33482-8859	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1860	A-BLK	GCP	PLR	M-R										10	11	12	13			16		PLANNED OBSOLESCENCE	SEE 33482-8860	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1861	A-BLK	GCP	PLR	M-R	1	2	3		5	6	7	8		10	11		13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8861	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1862	A-BLK	GCP	PLR	M-R	1	2	3		5	6	7	8			11		13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8862	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1863	A-BLK	GCP	PLR	M-R							7	8					13			16		PLANNED OBSOLESCENCE	SEE 33482-8863	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1864	A-BLK	GCP	PLR	M-R							7	8	9				13			16		PLANNED OBSOLESCENCE	SEE 33482-8864	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1865	A-BLK	GCP	PLR	M-R								7	8	9	10	11	12	13	14			PLANNED OBSOLESCENCE	SEE 33482-8865	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1866	A-BLK	GCP	PLR	M-R						6					11	12	13	14				PLANNED OBSOLESCENCE	SEE 33482-8866	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1867	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8		10	11	12	13	14	15			PLANNED OBSOLESCENCE	SEE 33482-8867	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1868	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11				15	16		PLANNED OBSOLESCENCE	SEE 33482-8868	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1869	A-BLK	GCP	PLR	M-R			3			6												PLANNED OBSOLESCENCE	SEE 33482-8869	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-1870	B-LG	GCP	PLR	M-R						6							13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8870	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-1871	B-LG	GCP	PLR	M-R					5								13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8871	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1872	A-BLK	GCP	PLR	M-R			3	4											15	16		PLANNED OBSOLESCENCE	SEE 33482-8872	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1873	A-BLK	GCP	PLR	M-R										10	11		13			16		PLANNED OBSOLESCENCE	SEE 33482-8873	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1874	A-BLK	GCP	PLR	M-R													13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8874	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1875	A-BLK	GCP	PLR	M-R						6				10	11	12						PLANNED OBSOLESCENCE	SEE 33482-8875	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1876	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6												PLANNED OBSOLESCENCE	SEE 33482-8876	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1877	A-BLK	GCP	PLR	M-R					5				9			12	13					PLANNED OBSOLESCENCE	SEE 33482-8877	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1878	A-BLK	GCP	PLR	M-R								7	9	10	11	12	13	14		16		PLANNED OBSOLESCENCE	SEE 33482-8878	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1879	A-BLK	GCP	PLR	M-R	1	2	3	4	5		7	8							15	16		PLANNED OBSOLESCENCE	SEE 33482-8879	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1880	A-BLK	GCP	PLR	M-R								7	8	9		11	12		14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8880	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1881	A-BLK	GCP	PLR	M-R	1	2																PLANNED OBSOLESCENCE	SEE 33482-8881	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1882	A-BLK	GCP	PLR	M-R			3			6			9	10	11	12	13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8882	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1883	A-BLK	GCP	PLR	M-R						6		8							15	16		PLANNED OBSOLESCENCE	SEE 33482-8883	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1884	A-BLK	GCP	PLR	M-R						6		8	9	10	11	12						PLANNED OBSOLESCENCE	SEE 33482-8884	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1885	A-BLK	GCP	PLR	M-R			3	4		6		8	9	10	11	12			15	16		PLANNED OBSOLESCENCE	SEE 33482-8885	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1886	A-BLK	GCP	PLR	M-R			3	4		6		8							15	16		PLANNED OBSOLESCENCE	SEE 33482-8886	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1887	A-BLK	GCP	PLR	M-R				4				8	9	10					15	16		PLANNED OBSOLESCENCE	SEE 33482-8887	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1888	A-BLK	GCP	PLR	M-R								8	9						15	16		PLANNED OBSOLESCENCE	SEE 33482-8888	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1889	A-BLK	GCP	PLR	M-R				4				8	9	10			13	14	15	16		PLANNED OBSOLESCENCE	SEE 33482-8889	34950-1611	34950-1621	34951-1631	34951-1641

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16							
KEY A, BLACK	33482-8640	A-BLK	GCP	PLR	M-B					5											16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8641	A-BLK	GCP	PLR	M-B					5												SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8642	B-LG	GCP	PLR	M-B				4		6	7	8				12		14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8643	A-BLK	GCP	PLR	M-B															15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8644	B-LG	GCP	PLR	M-B				4													SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8645	B-LG	GCP	PLR	M-B				4		6	7	8				12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8646	A-BLK	GCP	PLR	M-B				4		6	7	8				12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8647	A-BLK	GCP	PLR	M-B																16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8648	A-BLK	GCP	PLR	M-B				4								12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8649	B-LG	GCP	PLR	M-B																16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8650	B-LG	GCP	PLR	M-B				4								12		14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8651	B-LG	GCP	PLR	M-B														14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8652	B-LG	GCP	PLR	M-B						6	7	8						14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8653	A-BLK	GCP	PLR	M-B									9						15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8654	A-BLK	GCP	PLR	M-B				4				8				12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8655	B-LG	GCP	PLR	M-B				4				8				12		14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8656	B-LG	GCP	PLR	M-B								8						14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8657	A-BLK	GCP	PLR	M-B	1						7										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8658	B-LG	GCP	PLR	M-B			2	4		6	7	8				12		14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8659	B-LG	GCP	PLR	M-B			2			6	7	8						14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8660	B-LG	GCP	PLR	M-B			2					8						14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8661	A-BLK	GCP	PLR	M-B			2		4			8				12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-8662	B-LG	GCP	PLR	M-B			2	4				8				12		14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8663	A-BLK	GCP	PLR	M-B			2					8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8664	A-BLK	GCP	PLR	M-B					3			8		10	11				15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8665	A-BLK	GCP	PLR	M-B					3	4	5	6	7	8	10	11			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8666	A-BLK	GCP	PLR	M-B			2				6	7	8		10			13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8667	A-BLK	GCP	PLR	M-B			2				5	6			10			13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8668	A-BLK	GCP	PLR	M-B			2				5	6			10	11		13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8669	A-BLK	GCP	PLR	M-B			2				6				10			13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8670	A-BLK	GCP	PLR	M-B			2		4	5	6	7	8		10	11	12	13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8671	A-BLK	GCP	PLR	M-B			2		4	5	6				10		12	13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8672	A-BLK	GCP	PLR	M-B				4				8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8673	A-BLK	GCP	PLR	M-B			2				6	7	8								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8674	A-BLK	GCP	PLR	M-B			2				5	6									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8675	A-BLK	GCP	PLR	M-B			2				5	6				11					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8676	A-BLK	GCP	PLR	M-B						5	6	7	8					13			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8677	A-BLK	GCP	PLR	M-B						5	6	7															

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16							
KEY A, BLACK	33482-8736	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6							13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8737	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6					10	11	12	13	14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8738	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8739	A-BLK	GCP	PLR	M-B			3	4							11	12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8740	A-BLK	GCP	PLR	M-B									9			13	14	15	16		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8741	A-BLK	GCP	PLR	M-B			3	4					9	10	11	12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8742	A-BLK	GCP	PLR	M-B											11	12	13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8743	A-BLK	GCP	PLR	M-B											11			14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8744	A-BLK	GCP	PLR	M-B		2					7		9		11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8745	A-BLK	GCP	PLR	M-B		2							9			12	13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8746	A-BLK	GCP	PLR	M-B		2							9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8747	A-BLK	GCP	PLR	M-B												12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8748	A-BLK	GCP	PLR	M-B		2							9			12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8749	A-BLK	GCP	PLR	M-B	1										10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8750	A-BLK	GCP	PLR	M-B	1	2							9	10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, DARK GRAY	33482-8751	C-DG	GCP	PLR	M-B								8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, STONE GRAY	33482-8752	D-SG	GCP	PLR	M-B								8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, DARK GRAY	33482-8753	C-DG	GCP	PLR	M-B								8	9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, STONE GRAY	33482-8754	D-SG	GCP	PLR	M-B								8	9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, DARK GRAY	33482-8755	C-DG	GCP	PLR	M-B	1							8	9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, STONE GRAY	33482-8756	D-SG	GCP	PLR	M-B	1							8	9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY C, DARK GRAY	33482-8757	C-DG	GCP	PLR	M-B	1							8	9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY D, STONE GRAY	33482-8758	D-SG	GCP	PLR	M-B	1							8	9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8759	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8	9	10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8760	A-BLK	GCP	PLR	M-B		2					7		9								16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8761	A-BLK	GCP	PLR	M-B		2			5				9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8762	A-BLK	GCP	PLR	M-B	1	2			5		7		9	10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8763	A-BLK	GCP	PLR	M-B							7										16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8764	A-BLK	GCP	PLR	M-B					5	6	7		9		11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8765	A-BLK	GCP	PLR	M-B		2			5		7		9			12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8766	A-BLK	GCP	PLR	M-B					5	6	7		9	10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8767	A-BLK	GCP	PLR	M-B					5	6	7		9								16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8768	A-BLK	GCP	PLR	M-B					5	6	7		9	10							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8769	A-BLK	GCP	PLR	M-B	1			4	5	6		8				12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8770	A-BLK	GCP	PLR	M-B	1	2		4	5	6		8	9	10		12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8771	A-BLK	GCP	PLR	M-B	1			4			6	7	8		10		13	14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641	
KEY A, BLACK	33482-8772	A-BLK	GCP	PLR	M-B										10			13	14	15	16	SALEABLE						

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET


ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16						
KEY A, BLACK	33482-8828	A-BLK	GCP	PLR	M-B						6	7		9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8829	A-BLK	GCP	PLR	M-B	1	2		4	5		7	8	9						15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8830	A-BLK	GCP	PLR	M-B											11	12	13	14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8831	A-BLK	GCP	PLR	M-B												12	13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8832	B-LG	GCP	PLR	M-B														14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8833	A-BLK	GCP	PLR	M-B		2						8		10	11				15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8834	A-BLK	GCP	PLR	M-B											10	11			15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8835	A-BLK	GCP	PLR	M-B	1							8		10	11				15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8836	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8		10	11				15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8837	A-BLK	GCP	PLR	M-B	1							8	9	10	11				15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8838	A-BLK	GCP	PLR	M-B									9	10	11				15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8839	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8840	A-BLK	GCP	PLR	M-B	1																SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8841	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11					16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8842	A-BLK	GCP	PLR	M-B	1			4	5	6	7										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8843	A-BLK	GCP	PLR	M-B	1			4	5	6	7	8			11						SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8844	A-BLK	GCP	PLR	M-B													13			16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8845	A-BLK	GCP	PLR	M-B											11	12	13			16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8846	A-BLK	GCP	PLR	M-B	1							8			11						SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8847	A-BLK	GCP	PLR	M-B	1	2				6	7	8	9	10				14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8848	A-BLK	GCP	PLR	M-B	1	2					7	8	9	10					15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8849	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8			11	12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8850	A-BLK	GCP	PLR	M-B						6	7	8						14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8851	A-BLK	GCP	PLR	M-B							7	8							15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8852	A-BLK	GCP	PLR	M-B			3	4	5	6	7		9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8853	A-BLK	GCP	PLR	M-B				4					9			12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8854	A-BLK	GCP	PLR	M-B				4					9	10		12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8855	A-BLK	GCP	PLR	M-B			3	4					9	10			13	14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8856	A-BLK	GCP	PLR	M-B	1	2		4		6	7	8	9			12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8857	A-BLK	GCP	PLR	M-B	1	2		4		6	7	8	9	10		12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8858	A-BLK	GCP	PLR	M-B	1	2	3	4		6	7	8	9	10			13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8859	A-BLK	GCP	PLR	M-B		2			5		7		9	10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8860	A-BLK	GCP	PLR	M-B										10	11	12	13			16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8861	A-BLK	GCP	PLR	M-B	1	2	3		5	6	7	8		10	11		13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8862	A-BLK	GCP	PLR	M-B	1	2	3		5	6	7	8			11		13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8863	A-BLK	GCP	PLR	M-B							7	8					13			16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8864	A-BLK	GCP	PLR	M-B							7	8	9				13			16	SALEABLE		34			



MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16						
KEY A, BLACK	33482-8920	A-BLK	GCP	PLR	M-B				4			7	8		10		12			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8921	A-BLK	GCP	PLR	M-B				4			7	8	9			12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8922	A-BLK	GCP	PLR	M-B						6	7	8		10	11	12			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8923	A-BLK	GCP	PLR	M-B	1	2	3	4	5				9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8924	A-BLK	GCP	PLR	M-B							7	8				12			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8925	A-BLK	GCP	PLR	M-B	1		3	4								12	13				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8926	A-BLK	GCP	PLR	M-B	1	2												14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8927	A-BLK	GCP	PLR	M-B				4		6	7	8	9	10	11	12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8928	A-BLK	GCP	PLR	M-B	1	2	3	4		6	7	8	9	10	11	12			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8929	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9			12			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8930	A-BLK	GCP	PLR	M-B						6	7	8		10	11	12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8931	A-BLK	GCP	PLR	M-B	1	2	3			6	7	8		10	11	12			15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8932	A-BLK	GCP	PLR	M-B	1	2		4								12	13				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8933	A-BLK	GCP	PLR	M-B		2	3	4	5												SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8934	A-BLK	GCP	PLR	M-B		2	3	4	5					10	11	12	13	14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8935	A-BLK	GCP	PLR	M-B									9						15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8936	A-BLK	GCP	PLR	M-B									9		11	12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8937	A-BLK	GCP	PLR	M-B						6	7		9	10	11	12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8938	A-BLK	GCP	PLR	M-B										10	11	12	13	14	15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8939	A-BLK	GCP	PLR	M-B						6		8	9	10	11	12				15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8940	A-BLK	GCP	PLR	M-B						6		8								15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8941	A-BLK	GCP	PLR	M-B			3	4	5	6		8	9	10	11	12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8942	A-BLK	GCP	PLR	M-B			3	4	5	6		8							15		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8943	A-BLK	GCP	PLR	M-B			3	4				8	9	10	11	12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8944	A-BLK	GCP	PLR	M-B			3	4				8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8945	A-BLK	GCP	PLR	M-B								8	9	10	11	12					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8946	A-BLK	GCP	PLR	M-B	1	2	3			6	7	8		10	11			14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8947	A-BLK	GCP	PLR	M-B		2	3			6	7			10	11				14		SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8948	A-BLK	GCP	PLR	M-B		2				6	7			10				14			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET



FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20							
KEY A, BLACK	33482-2001	A-BLK	GCO	PLR	M-R																					OBSOLETE	SEE 33482-2101	34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-2002	B-LG	GCO	PLR	M-R																					OBSOLETE	SEE 33482-2102	34950-2011	34950-2021	34951-1631	34951-1641	
KEY C, BROWN	33482-2003	C-BR	GCO	PLR	M-R																					OBSOLETE	SEE 33482-2103	34950-2011	34950-2021	34951-1631	34951-1641	
KEY D, GREEN	33482-2004	D-GR	GCO	PLR	M-R																					OBSOLETE	SEE 33482-2104	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2006	A-BLK	GCP	PLR	M-R																					OBSOLETE	SEE 33482-2106	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2007	A-BLK	GCP	PLR	M-R										11										20	OBSOLETE	SEE 33482-2107	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2008	A-BLK	GCP	PLR	M-R				4	5	6	7							14	15	16	17				OBSOLETE	SEE 33482-2108	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2009	A-BLK	GCP	PLR	M-R							7									16					OBSOLETE	SEE 33482-2109	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2010	A-BLK	GCP	PLR	M-R									10	11	12									20	OBSOLETE	SEE 33482-2110	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2011	A-BLK	GCP	PLR	M-R	1	2																		20	OBSOLETE	SEE 33482-2111	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2012	A-BLK	GCP	PLR	M-R	1	2								10	11	12								20	OBSOLETE	SEE 33482-2112	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2013	A-BLK	GCP	PLR	M-R	1	2								10	11	12	13	14						20	OBSOLETE	SEE 33482-2113	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2014	A-BLK	GCP	PLR	M-R				3	4	5								14			17		19		OBSOLETE	SEE 33482-2114	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2015	A-BLK	GCP	PLR	M-R																	17				OBSOLETE	SEE 33482-2115	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2016	A-BLK	GCP	PLR	M-R		2		3	4	5												18	19	20	OBSOLETE	SEE 33482-2116	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2017	A-BLK	GCP	PLR	M-R																		18	19	20	OBSOLETE	SEE 33482-2117	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2018	A-BLK	GCP	PLR	M-R									10		12	13	14					19			OBSOLETE	SEE 33482-2118	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2019	A-BLK	GCP	PLR	M-R					3	4								14			17		19		OBSOLETE	SEE 33482-2119	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2020	A-BLK	GCP	PLR	M-R					3	4	5							14			17	18	19	20	OBSOLETE	SEE 33482-2120	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2021	A-BLK	GCP	PLR	M-R	1	2			3	4	5			10				14			17	18	19	20	OBSOLETE	SEE 33482-2121	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2022	A-BLK	GCP	PLR	M-R				3	4					10				14			17		19		OBSOLETE	SEE 33482-2122	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2023	A-BLK	GCP	PLR	M-R										10	11	12			15	16	17			20	OBSOLETE	SEE 33482-2123	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2024	A-BLK	GCP	PLR	M-R															15	16	17			20	OBSOLETE	SEE 33482-2124	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2025	A-BLK	GCP	PLR	M-R										10				14			17		19		OBSOLETE	SEE 33482-2125	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2026	A-BLK	GCP	PLR	M-R					4	5				10				14	15		17		19		OBSOLETE	SEE 33482-2126	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2027	A-BLK	GCP	PLR	M-R						5				10				14	15		17	18	19		OBSOLETE	SEE 33482-2127	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2028	A-BLK	GCP	PLR	M-R	1			3	4	5	6	7	8	9	10	11		13	14	15	16	17	18	19	20	OBSOLETE	SEE 33482-2128	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2029	A-BLK	GCP	PLR	M-R					5	6	7									16	17					OBSOLETE	SEE 33482-2129	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2030	A-BLK	GCP	PLR	M-R				3	4	5								13	14	15			18	19		OBSOLETE	SEE 33482-2130	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2031	A-BLK	GCP	PLR	M-R					4											16						OBSOLETE	SEE 33482-2131	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2032	A-BLK	GCP	PLR	M-R				3	4	5								13		15			18	19		OBSOLETE	SEE 33482-2132	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2033	A-BLK	GCP	PLR	M-R										10								17		19		OBSOLETE	SEE 33482-2133	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2034	A-BLK	GCP	PLR	M-R																	17	18	19	20	OBSOLETE	SEE 33482-2134	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2035	A-BLK	GCP	PLR	M-R																16						OBSOLETE	SEE 33482-2135	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2036	A-BLK	GCP	PLR	M-R																	17	18	19	20	OBSOLETE	SEE 33482-2136	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2037	A-BLK	GCP	PLR	M-R																	17	18	19	20	OBSOLETE	SEE 33482-2137	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2038	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10		12					17		19			OBSOLETE	SEE 33482-2138	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2039	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8		10							17		19			OBSOLETE	SEE 33482-2139	34950-2011			

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20							
KEY A, BLACK	33482-2082	A-BLK	GCP	PLR	M-R	1			3	4				8	9	10	11			13	14			18	19	20	OBSOLETE	SEE 33482-2182	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2083	A-BLK	GCP	PLR	M-R	1								8	9	10	11							19	20		OBSOLETE	SEE 33482-2183	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2084	A-BLK	GCP	PLR	M-R	1									9												OBSOLETE	SEE 33482-2184	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2085	A-BLK	GCP	PLR	M-R	1																		19			OBSOLETE	SEE 33482-2185	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2086	A-BLK	GCP	PLR	M-R			2	3		5									14				19	20		OBSOLETE	SEE 33482-2186	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2087	A-BLK	GCP	PLR	M-R	1												12	13				19				OBSOLETE	SEE 33482-2187	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2088	A-BLK	GCP	PLR	M-R	1												12	13			15		19			OBSOLETE	SEE 33482-2188	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2089	A-BLK	GCP	PLR	M-R	1		2	3	4	5	6	7	8	9			12	13	14	15	16		19			OBSOLETE	SEE 33482-2189	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2090	A-BLK	GCP	PLR	M-R	1		2	3	4	5	6	7	8	9	10		12	13	14	15	16		19	20		OBSOLETE	SEE 33482-2190	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2101	A-BLK	GCO	PLR	M-B																						SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-2102	B-LG	GCO	PLR	M-B																						SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY C, BROWN	33482-2103	C-BR	GCO	PLR	M-B																						NOT RECOMMENDED	SEE 33482-2154	34950-2011	34950-2021	34951-1631	34951-1641
KEY D, GREEN	33482-2104	D-GR	GCO	PLR	M-B																						NOT RECOMMENDED	SEE 33482-2155	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2106	A-BLK	GCP	PLR	M-B																				20		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2107	A-BLK	GCP	PLR	M-B												11										SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2108	A-BLK	GCP	PLR	M-B					4	5	6		7						14	15	16	17				SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2109	A-BLK	GCP	PLR	M-B																	16					SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2110	A-BLK	GCP	PLR	M-B												10	11	12							20	SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2111	A-BLK	GCP	PLR	M-B	1		2																		20	SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2112	A-BLK	GCP	PLR	M-B	1		2									10	11	12							20	SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2113	A-BLK	GCP	PLR	M-B	1		2									10	11	12	13	14					20	SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2114	A-BLK	GCP	PLR	M-B					3	4	5									14			17		19		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2115	A-BLK	GCP	PLR	M-B																		17				SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2116	A-BLK	GCP	PLR	M-B			2															18	19	20		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2117	A-BLK	GCP	PLR	M-B																		18	19	20		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2118	A-BLK	GCP	PLR	M-B												10		12	13	14						SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2119	A-BLK	GCP	PLR	M-B																		17				SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2120	A-BLK	GCP	PLR	M-B					3	4	5											17	18	19	20		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2121	A-BLK	GCP	PLR	M-B	1		2	3	4	5						10						17	18	19	20		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2122	A-BLK	GCP	PLR	M-B					3	4						10						17					SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2123	A-BLK	GCP	PLR	M-B												10	11	12			15	16	17		20	SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2124	A-BLK	GCP	PLR	M-B																	15	16	17		20	SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2125	A-BLK	GCP	PLR	M-B												10				14			17		19		SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2126	A-BLK	GCP	PLR	M-B												10				14	15					SALEABLE	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A																																

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20							
KEY A, BLACK	33482-2198	A-BLK	GCP	PLR	M-B	1	2	3				7		9								16			19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2199	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8	9				13	14	15	16				19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2200	A-BLK	GCP	PLR	M-B	1	2	3	4	5						11	12			14			17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2201	A-BLK	GCP	PLR	M-B	1	2							9	10	11					15				19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2202	A-BLK	GCP	PLR	M-B		2	3	4	5			8	9								16				20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2203	A-BLK	GCP	PLR	M-B	1	2	3						9										19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2204	A-BLK	GCP	PLR	M-B						6						12			15	16	17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-2205	B-LG	GCP	PLR	M-B			3	4	5			8	9	10				14					19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2206	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6												17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2207	B-LG	GCP	PLR	M-B				4	5	6			9	10											20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2208	B-LG	GCP	PLR	M-B									9	10	11											SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2209	B-LG	GCP	PLR	M-B				4	5	6		7										17	18			SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2210	A-BLK	GCP	PLR	M-B	1								9	10	11	12				16					20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2211	A-BLK	GCP	PLR	M-B	1	2						7			10	11	12							20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2213	A-BLK	GCP	PLR	M-B													13						19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2214	A-BLK	GCP	PLR	M-B																16					SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2215	A-BLK	GCP	PLR	M-B			2					8		10							17		19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2216	A-BLK	GCP	PLR	M-B																16				20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2217	A-BLK	GCP	PLR	M-B								7					12							20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2218	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6													19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2219	A-BLK	GCP	PLR	M-B						6														20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2220	A-BLK	GCP	PLR	M-B	1		3		5		7		9			12		14		16		18		20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2221	A-BLK	GCP	PLR	M-B		2		4		6		8		10	11		13		15		17		19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2222	A-BLK	GCP	PLR	M-B	1	2	3						9							16				20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2223	A-BLK	GCP	PLR	M-B							7					12				16					SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2224	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8			10				14	15		17		19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2225	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6												17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2226	B-LG	GCP	PLR	M-B															15	16		17			20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2227	A-BLK	GCP	PLR	M-B			3										13	14				17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2228	A-BLK	GCP	PLR	M-B				3	4	5	6	7	8	9	10		13	14				17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2229	A-BLK	GCP	PLR	M-B				3	4	5	6	7	8	9	10		13	14				17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2230	A-BLK	GCP	PLR	M-B			3										13	14				17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2231	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8			10							18		20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2232	A-BLK	GCP	PLR	M-B																				20	SALEABLE		3495				

WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION

NO.: 642855
 : 8/17/2020

DOCUMENT NO.: SD-33482-0002

REVISION:
 PAGE: 27