

EKU 30-T

FIBOX
Enclosing innovations

Order symbol: EKU 30-T

Product nbr: 3720320

Description: Cover

Remarks: Transparent. PC


Including:

EAN: 64 18074000408

El. number:

- Finland: 3420180
- Denmark: 82 12007259
- Sweden: 2537874

Sample image



Dimensions:	Height	Width	Depth
mm:	560	380	30
inch:	22.05	14.96	1.18

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term): -40 ... 120

Temperature °C (continuous):

Temperature °F (short term): -40 ... 250

Temperature °F (continuous): -40 ... 175

Accessories:

EKUVT Back Panel. for enclosures:
(518 x 338 x 1)

EKV 32 DIN-35 Mounting rail. for enclosures:
(335 x 35 x 1)

EKUZR Extension frame. for enclosures:
(560 x 380 x 50)

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Certificates:

SGSFIMKO_EK