

Order symbol: EKTH

EAN: 6418074000125

Product nbr: 3530132

El. number:


Description: Base. PC

- Finland: 3420125
- Denmark: 8212006603
- Sweden: 2537822

Remarks: Openings, 6x size 2 flange

Including:

Sample image



Dimensions:	Height	Width	Depth
mm:	560	280	100
inch:	22.05	11.02	3.94

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Accessories:

EKTZR Extension frame. for enclosures:
(560 x 280 x 50)

EKTVT Back Panel. for enclosures:
(518 x 238 x 1)

EKV 22 DIN-35 Mounting rail. for enclosures:
(235 x 35 x 1)

EKV 50 DIN-35 Mounting rail. for enclosures:
(515 x 35 x 1)

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Certificates:

SGSFIMKO_EK