

RLP73K1E1R0FTDF

✓ ACTIVE

CGS | CGS RLP73

TE Internal #: 3-2176049-2

Surface Mount Resistors, Low Ohmic Resistor, 2 Termination, 0402, Taped & Reeled, 1 %, Thick Film, Resistance Class Up to 1kΩ, 1 Ω, .125 W, CGS RLP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Low Ohmic Resistor**

Number of Terminations: **2**

Package Size Code: **0402**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

[All Thick Film Resistor: Current Sense \(214\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Low Ohmic Resistor
Package Size Code	0402
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	1 Ω
Power Rating	.125 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	1 x .5 x .2 mm
------------------------------	----------------



Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C339-R529A
Thick Film Resistor: Current Sense

TE Part # 2176050-8
RLP73N 1E R10 5% 5K RL



Also in the Series | CGS RLP73

[Surface Mount Resistors\(396\)](#)

Customers Also Bought

TE Part #1-5747299-4
[15 RCPT SP/FMS SCRLK](#)

TE Part #1-5745967-4
[25 RCPT SP/FMS SCRLK](#)TE Part #5499913-9
[A/L UNIV HDR 40P RA SHT LAT](#)TE Part #5-5179010-5
[0.8FH,R13H.5,120,08/Sn,TU](#)TE Part #5747840-5
[HD-20 PLUG RA .318 FMS BD-LK S](#)TE Part #1-5747301-4
[37 RCPT SP/FMS SCRLK](#)TE Part #1761606-5
[IDC LOW PRO HDR 14P VERT LG LA](#)TE Part #9-1879213-7
[CPF 0402 301R 0.1% 25PPM 1K RL](#)TE Part #1-1879208-3
[CPF 0402 33R 0.1% 25PPM 1K RL](#)TE Part #1546927-3
[3P .325 TRI-BARRIER W/COVER](#)

Documents

[Product Drawings](#)
[RLP73K 1E 1R0 1% 1K RL](#)

English

[CAD Files](#)
[3D PDF](#)
3D



Customer View Model

[ENG_CVM_CVM_3-2176049-2_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2176049-2_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2176049-2_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD Low Ohmic Current Sense Resistors - Type RL73 Series](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English