

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731120621](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT DIN Coaxial Contact, Female, Straight, Solder Cable Termination, 75 Ohms, 0.50µm Gold Plating, for RG-179BU or RG-187AU Cable

Documents:

Drawing (PDF)	Brochure (PDF)
Application Specification 2195600660-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	D-Sub Products
Series	173112
Contact Type	Coaxial
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Taxonomy	D-Sub Contacts
Type	Mixed Layout
UPC	191128458559
Wire/Cable Type	RG-179BU, RG-187AU

Physical

Durability (mating cycles max)	200
Gender	Female
Material - Contact	Copper Alloy
Net Weight	1.300/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	Gold over Nickel
Plating min - Mating	0.500µm
Plating min - Termination	0.500µm
Temperature Range - Operating	-55° to +135°C
Termination Style	Solder

Electrical

Current - Maximum per Contact	2.0A
Impedance	75Ω

Material Info

Engineering Number	FDX013S116
--------------------	------------

Reference - Drawing Numbers

Application Specification	2195600660-000
Sales Drawing	1731120268-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[173112](#) Series

Use With

FCT Mixed Layout Connectors