

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0466261405

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK Plus 250 Female Crimp Terminal, 26-28 AWG, Tin (Sn) Plating, Reel

- Documents:
- Drawing (PDF)

Product Specification 2079020001-PS-000 (PDF)

Product Specification 2079020001-PS-CH-000 (PDF)

Product Specification 2079020001-PS-ES-000 (PDF)

Product Specification 2079020001-PS-JP-000 (PDF)

Product Specification 2079020001-PS-SK-000 (PDF)

Application Specification 2079020001-AS-000 (PDF)

Packaging Specification PK-46626-001-001 (PDF)

Test Summary 2079020000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

Taxonomy

UPC

Crimp Terminals

46626

Power, Wire-to-Board

Yes

KK Interconnect Systems

KK Plus

Crimp Terminals

191130122141

Physical

Durability (mating cycles max)

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

25

Female

Copper Alloy

Tin

Tin

0.043/g

Reel

Crimp or Compression

1.17mm-1.30mm

26, 28

0.08-0.13

Electrical

Current - Maximum per Contact

Voltage - Maximum

6.5A

250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

2079020001-AS-000

PK-46626-001-001

2079020001-PS-000, 2079020001-PS-CH-000, 2079020001-PS-ES-000, 2079020001-PS-JP-000, 2079020001-PS-SK-000

466260002-SD-000

2079020000-TS-000

Sales Drawing

Test Summary

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

46626 Series

Use With

KK Plus 250 Receptacle Housing [207841](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for KK Plus 250 Receptacle Crimp Terminals, 22-28 AWG	2002221000
Hand Crimp Tool for KK Plus 250 Female Crimp Terminals, 22-28 AWG, UL1007 Wire	2133090300

Hand Crimp Tool for [2133092200](#)
KK Plus 250 Female
Crimp Terminals,
26-28 AWG, UL1061
Wire
FineAdjust Applicator[639047500](#)
for KK Plus 250
Female Crimp
Terminal, 26-28
AWG, UL1007 Wire

This document was generated on 10/20/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION