

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731120205

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Machined Contact, Male, Crimp, 1.30µm Gold Plating, 18-22 AWG

Documents:

Drawing (PDF)

Packaging Specification 1731120004-PK-000 (PDF)

Datasheet (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	D-Sub Products
Series	173112
Contact Type	Machined Crimp
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Taxonomy	D-Sub Contacts
Type	Standard Density
UPC	889056489607
Physical	
Durability (mating cycles max)	500
Gender	Male
Material - Contact	Brass
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	Gold over Nickel
Plating min - Mating	1.300µm
Plating min - Termination	1.300µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size AWG	18, 20, 22

Electrical	
Current - Maximum per Contact	7.5A
Material Info	
Engineering Number	FK20P18-13V-5783
Reference - Drawing Numbers	
Packaging Specification	1731120004-PK-000
Sales Drawing	1731120203-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - ED/71/2019 (16 July 2019)	
Lead	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

173112 Series

Use With

FCT Standard-Density Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION