

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008650811

Status:

Active

Description:

KK 100 Crp Term Std 22-30 Awg SGold

Documents:

Drawing (PDF)	Test Summary TS-10-07-001 (PDF)
Product Specification PS-10-07-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-2759-002-001 (PDF)	

General

Product Family	Crimp Terminals
Series	6459
Crimp Quality Equipment	Yes
Product Name	KK 254
Taxonomy	Crimp Terminals
UPC	800753844018

Physical

Net Weight	0.069/g
------------	---------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	6459-(558)
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-2759-002-001
Product Specification	PS-10-07-001
Sales Drawing	SD-6459-001
Test Summary	TS-10-07-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

6459 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	11030022
Insertion Tool for KK 2.54mm Terminals, 22-30 AWG	638120000
Mini-Mac Applicator for KK and Cat Ear Terminals for 22-30 AWG Wire with Insulation Diameter 1.09-1.57mm and 22-28	638882000
AWG Wire with Insulation Diameter 1.20-1.70mm Mini-Mac Applicator for KK and Cat Ear Terminals for 22-30 AWG Wire with Insulation Diameter 0.96-1.20mm	638882100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION