

KERN OIV 345



The entry level video microscope with bright image reproduction and intuitive operation



Category

Brand	Optics
Product category	Microscope
Product group	Video microscope
Product family	OIV-3

Display

Display type	LCD
Display screen size	12"
Display resolution	1920×1080 HD

Languages of the user interface	German
	English
	French
	Spanish
	Italian
	Russian

Construction

Dimension (W×D×H)	320×260×450 mm
Dimension display device (W×D×H)	275×170×12 mm
Material display housing	plastic
Optical system	Axial
Tube type	Display
Contrasting methods	Bright field

Functions

Camera - Applicable software	S-Viewer (OXM 904) integrated camera software
Camera - Software functions	Image capturing Video capturing Image editing/

Documentation Measurements

Supported operating systems	Win 7
	Win 8
	Win 10
	Win 11
Memory - total size	32 GB
System requirements CPU	Intel Core i3 or higher AMD Ryzen 5 or higher
System requirements RAM	8 GB
System requirements SSD storage	128 GB SSD
System requirements graphics card	NVIDIA GeForce RTX 3060
	AMD Radeon RX 6600
System requirements screen	20" HD or larger
System requirements clock speeds	2.8 GHz

Interface

Interfaces	USB 2.0
	HDMI
	MicroSD card slot

Objective

Objectives magnifications	0,7x - 4,5x
---------------------------	-------------

Illumination

Illuminance	Reflected light
Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination dimmable	Incident light

Focussing

Field of view [Min]	2,5 mm
Field of view [Max]	16 mm
Click-Stop-Zoom	✓
Zoom [Min]	0,7x
Zoom [Max]	4,5x
Sample height [Max]	110 mm
Working distance	100 mm
Magnification ratio	6,4:1
Focusing mechanism	coarse drive

Stereomicroscope stand

Stand type	mechanical
Column height	330 mm

Camera

Cameratype	integrated tablet-camera
------------	--------------------------

KERN OIV 345

KERN

The entry level video microscope with bright image reproduction and intuitive operation

Camera - Resolution	5 MP
Camera - Sensor type	Sony CMOS
Camera - Sensor size	1/2,8"
Camera - Framerate	60 fps
Camera - Exposure method	Rolling Shutter

Power Supply

Supplied power supply	Power supply unit
Power supply type	Table power supply (separable)
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Power supply - Cable length	2,5 m
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 2000 mA
Power socket for mains adapter	Inside plus, outside minus

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	420×390×250 mm
Shipping method	Parcel service
Net weight approx.	4,4 kg
Gross weight approx.	6 kg
Shipping weight	8,2 kg

Product information

GTIN/EAN number	4045761478985
REACH classification	no prohibited substances

Pictograms

STANDARD

