




Part Number : [191930157](#)
Product Description : VersaKrimp Ring
Tongue Terminal for 8 AWG Wire, Stud Size
5/16" (M8)
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : D-350-56



Documents & Resources

Drawings
[Drawing 191930157_sd.pdf](#)

Specifications
[Product Specification PS-19902-011-001.pdf](#)
[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8)
Keyword	Ring Terminal, Ring Terminals
Product Family	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Type	Ring
UPC	800755050073

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.559/g
Packaging Type	Bag
Stud Size	5/16" (M8)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	8
Wire Size mm ²	6.60-10.50

Application Tooling

Global

Description	Part Number
Manual Putt Pump Hydraulic System, Die set required	<u>0192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>0192900001</u>
Hydraulic Dieless Crimping Tool	<u>0638161700</u>
PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	<u>0640013900</u>
RHT1080 Hand Crimp Tool	<u>0640034400</u>
Square "DIN" style dies for 8 AWG	<u>0640037670</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640074400</u>

This document was generated on Sep 26, 2023