



Part Number : [393800102](#)
Product Description : 6.35mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 2 Circuits
Series Number : 39380
Status : Active
Product Category : Terminal Blocks and Barrier Strip
Engineering Number : MX-MSP0200S-0N



Documents & Resources

Drawings
[Drawing 393800102_sd.pdf](#)

3D Models and Design Files
[3D Model 393800102_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39380
Description	6.35mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 2 Circuits
Application	N/A
Component Type	One Piece
Product Family	Eurostyle Terminal Blocks
Product Name	Eurostyle Fixed Mount
Type	Euro Block
UPC	822348022977

Electrical

Current - Maximum per Contact	30.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	2
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Resin	Nylon
Net Weight	5.950/g
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PC Tail Length	5.20mm

PCB Retention	None
PCB Thickness - Recommended	4.00mm
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	N/A
Shrouded	Fully
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size (AWG)	10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm ²	0.05-2.50

This document was generated on Sep 26, 2023