



Part Number : [192030389](#)
Product Description : Krimptite Ring Tongue
Terminal for 10 to 12 AWG Wire, Stud Size 10
(M5)
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals



Documents & Resources

Drawings
[Drawing 192030389_sd.pdf](#)

Specifications
[Product Specification PS-19902-011-001.pdf](#)
[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)
Keyword	Ring Terminal, Ring Terminals
Product Family	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite
Type	Ring
UPC	822348424788

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Net Weight	1.180/g
Packaging Type	Carton
Stud Size	10 (M5)
Temperature Range - Operating	483°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.70mm max.
Wire Size (AWG)	10, 12
Wire Size mm ²	4.00-6.00

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>

This document was generated on Sep 26, 2023