


95x210mm


SMART PET FEEDER

User Manual




Introduction


1. The power port is located at the bottom of the feeder as shown in the picture.Plug in the power supply the power cord can be selected from the right or behind.
- 2.The battery compartment can be put 3pcs (not included in factory).D Battery to keep the feeder feeds normally in case of a power outage.




Fix the main part (Tip 2) , hold the Grain barrels (Tip 1) with both hands and drag it upward to disassemble; Similarly, fix the main body (Tip 2) , align the Grain barrels (Tip 1) with the main part hole (Tip 2) and lightly press to complete the installation.



Align the front end of the feeder (Tip 3) with the hole in the food bowl (Tip 4) and place it gently to fix it.



Press the opening position of the feeder lid to open the granary cover and pour the food into the granary and it can be used normally.There is a moisture-proof box inside the granary cover which can be put in a moisture-proof bag to prevent food from spoiling due to moisture



1. Feed key/lock key
Short press: manually feed one portion
Long press: In the unlocked state press and hold for 5s (the red light flashes once)
Key lock: In the locked state, press and hold for 5s (the red light flashes once)
Button unlock: (this function is to prevent pets from touching the button to eat)

2. Setting key
Short press: no function
Long press: long press in the networked state the device resets and the green light flashes slowly; During connecting network the green light flashes quickly



3. Microphone hole
Please speak directly into the microphone hole when recording.

4. Indicator light
Green light flashing slowly: the device is connected to the Internet
Green light flashes quickly: the device is networking
The edge light is always on: the device is connected to the Internet successfully
Steady red light: battery power supply
Red light flashes quickly: low battery or device failure.


5. Record key
Long control: long press 3 times, when you hear "DI" start recording.release.
Key casting: when you hear the sound of "DIDI" the recording ends.
Short: Play recording.
The device only supports one recording message the longest recording is 10 seconds and it will be played automatically when feeding.

APP Install



Scan QR to Download


Register & Login



After the installation is complete register an account and Log into the APP .You can also directly press the phone number with one key Login or WeChat authorized login or Apple ID authorized login.


Add Device

1. Turn on the mobile phone Wi-Fi and Bluetooth Function
2. Click "+" to add devices
3. Choose to manually add devices, click Hit the pet feeder
4. Choose a visual pet feeder perform Wi-Fi configuration.




1. Turn on the power and make sure that the green light of the device flashes slowly;
2. Select the 2.4G Wi-Fi network and enter the password;
3. Align the QR code of the mobile phone with the camera and adjust the distance between the mobile phone and the device appropriately (WIFI The distribution network and QR code distribution network are turned on at the same time), and "DIDI" is heard, and the device is successfully connected to the network;
4. Follow the guide page to complete the operation steps;
5. The device is added.

Live Video




1. Take a photo: capture the current screen of the video
2. Microphone: light up the icon you can talk to the pets nearby
3. Image quality: SD/HD
4. Timing feeding: click to enter timing feeding interface
5. Full screen switching: click on the full screen/normal mode switch
6. Video: Click to record the current video
7. One-key feeding: food is delivered according to the selected number of servings
8. Video Playback:Viewable pet video replay

Timing Feeding



1. Click "Feeding Plan" to enter the feeding plan list
2. Click "Add" to enter "Add Plan
3. Choose feeding time and repeat date
4. Choose the number of servings according to the pet's food intake
5. In "Feeding Records" you can check the pet's feeding records.

One Key Feeding




1. Choose the number of servings according to the pet's food intake
2. Click "One-key feeding"
3. It will display "feeding" and the equipment will start to deliver food
4. About 10g per serving

Custom Voice



1. Press and hold the panel of the device, the device will start recording after the "DI" sound, release the button, the device will sound "DIDI" sounds, the recording is over and the device supports a maximum of 10 seconds of recording
2. Short press to play the recording
3. The recording is played along with feeding, calling the pet to eat.

Device Settings



1. On the video page click the setting button in the upper right corner to enter the device interface
2. Configure the device as required in the setting page
3. On the about Device page, click "Restore Factory settings" to restore the device to factory settings when the operation is complete the device is removed from the APP and restart the device to add according to the operation method

Remind:

1. This device only supports 2.4G network temporarily and does not support 5G
2. It is only suitable for dry grain and the recommended grain diameter is 2-14mm
3. Regularly observe the grain barrels. When the grain is insufficient please add in time
4. It is recommended to reasonably arrange the number of food servings according to the appropriate amount of pets, and scientifically feed them
5. The grain bucket is detachable. It is recommended to disassemble it regularly clean it and dry it before using
6. If you need to change wifi please long press the set button to reset the camera to factory default and re connect the device again