







TOP VIEW





SECTION A-A
SIDE VIEW




INSIDE BOX



SECTION B-B
END VIEW



INSIDE LID



POLYCARBONATE
VERSION ONLY
UL US LISTED
FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 2 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 85 - 92 ozf-in (60-65 cN-m)

1554A	
1554A Regular Enclosure	
General Purpose ABS RAL-7035	1554AGY
Polycarbonate RAL-7035	1554A2GY
1554A Clear / Smoke Lid Enclosure	
Polycarbonate Box / Clear Polycarbonate Lid	1554A2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid	1554A2GYSL
ACCESSORIES	
Steel Inner Panels	1554APL
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554AGASKET



1554A

www.hammondmfg.com

Dimensions:
mm
[inches]