







TOP VIEW




SECTION A-A  
END VIEW




SECTION B-B  
SIDE VIEW



INSIDE LID



INSIDE BOX



UL US LISTED  
FILE #E71073  
NEMA 4, 4X

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)  
Contact Factory (modshop@hammfg.com) for quotes  
Solid models of this enclosure available in .stp or .x\_t  
(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)

#### NOTE

Purchased assembly includes box, lid, silicone gasket, and 4 cover screws.  
Box and lid are made from Diecast Aluminum Alloy.  
Bottom flange is welded.

Recommended Cover screw torque 5-7.5 lbf.in (50 -75 cN.m)

#### PART NUMBERS

##### 1550Z139 Flange Enclosure

|                          |             |
|--------------------------|-------------|
| Natural Finish Enclosure | 1550Z139F   |
| Black Textured Enclosure | 1550Z139FBK |

##### ACCESSORIES

|                                                                                                                |                |
|----------------------------------------------------------------------------------------------------------------|----------------|
| Stainless Steel Cover screws<br>[M4 - 0.7 x 30mm] (30 Pack)                                                    | SC1550Z116-30  |
| Ground Hardware (50 Pack)<br>#6 Phos. Bronze plate Lock Washer<br>#6-32 x 5/16 Copper plate Self-Tapping screw | SCG060-50      |
| Pre-Formed Silicone Gasket (2 Pack)                                                                            | 1550Z139GASKET |



**HAMMOND®**

**1550Z139F**

www.hammondmfg.com

Dimensions:  
mm  
[inches]