



Part Number : [191930360](#)
Product Description : VersaKrimp Ring
Tongue Terminal for 3/0 AWG Wire, Closed-
Braided Barrel, Stud Size 5/16" (M8), Carton
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : K-390-56



Documents & Resources

Drawings
[191930360_sd.pdf](#)

3D Models and Design Files
[191930360_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	800755052510

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	35.046/g
Packaging Type	Carton
Stud Size	5/16" (M8)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	19.02mm max.
Wire Size (AWG)	3/0
Wire Size mm ²	95.00

Application Tooling

Global

Description	Part Number
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900028</u>