




Part Number : [192210648](#)
Product Description : Compression Style Ring
Tongue Terminal for 4/0 AWG Wire, Stud Size
1/4" (M6), Plated, Barrel Length 19.05mm
Series Number : 19221
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : BCL-4014-PL



Documents & Resources

Drawings

[192210648_sd.pdf](#)

3D Models and Design Files

[192210648_stp.zip](#)

Specifications

[PS-19901-017-001.pdf](#)

[PS-19902-011-001.pdf](#)

[PS-19902-013-001.pdf](#)

[PS-19902-017-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19221
Description	Compression Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 1/4" (M6), Plated, Barrel Length 19.05mm
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Battery Cable Lug
Type	Ring
UPC	822348117277

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	39.191/g
Packaging Type	Bag
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm

Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	4/0

Application Tooling

Global

Description	Part Number
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900031</u>
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 4/0 AWG	<u>640038370</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>