

8

7

6

5

4

3

2

1

F


E

D

C

B

SD-55516-005.S01



SECTION A-A

注 記

NOTES

1. 材 質
MATERIAL
ハウジング : ガラス入りPBT UL94V-0グレー
HOUSING : PBT,G.F.UL94V-0
ターミナル : 黄 銅
TERMINAL : BRASS
2. メッキ仕様
PLATING
金メッキ : 0.1μm MIN.(接点部)
GOLD : 0.1μm MIN.(CONTACT AREA)
錫メッキ : 1.0μm MIN.(リセプタクル嵌合部)
TIN : 1.0μm MIN.(RECEPTACLE CONNECTED AREA)
ニッケルメッキ : 2.0μm MIN.(下地メッキ)
NICKEL : 2.0μm MIN.(UNDER PLATING)
3. 適合プラグカバー
APPLICABLE PLUG COVER
COVER A : 55513-1605, 55513-1615
55513-1625, 55513-1635
COVER B : 55514-1605
4. 適合リセプタクル : 54596-0810, 54596-0910
APPLICABLE RECEPTACLE
5. 本製品は 55516-1605 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 55516-1605.

EC NO. DRWN: CHK: APPR:		EC NO. DRWN: CHK: APPR:		EC NO. DRWN: CHK: APPR:		EC NO. DRWN: CHK: APPR:		RELEASED EC NO. J2004-4286 DRWN: M.NABEI '04/05/18 CHK: K.TOJO APPR: M.SASAO		DESCRIPTION		MATERIAL 材料 注記参照 SEE NOTES		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE 2-1		DESIGN UNITS ☒ mm ☐ INCH		THIRD ANGLE PROJECTION		☐ mm INCH ☐ INCH mm ☒ mm ONLY		REVISE ON CAD ONLY			
										FINISH 仕上付 注記参照 SEE NOTES				10 UNDER 未満		±0.2		DRAWN BY & DATE M.NABEI '04/05/18		TITLE: SMALL-MGC PLUG INNER HS'G ASS'Y -LEAD FREE-							
												10 OVER 30 UNDER 以上 未満		±0.25		CHECKED BY & DATE K.TOJO '04/05/18											
														30 OVER 以上		±0.3		APPROVED BY & DATE M.SASAO '04/05/18		MOLEX INCORPORATED							
												WIRE RANGE 適用電線範囲		— —		ANGLE 角度		±3°		CAD FILENAME SD-55516-005.S01		MATERIAL NO. SEE CHART		DRAWING NO. SD-55516-005		SHEET NO. 1 OF 1	
								Ø		REV		INS. RANGE 被覆外径		— —						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				SIZE B			