



Part Number : 1120080013


Product Description : NetMeter Hand Held
Digital DeviceNet

Series Number : 112008

Status : Obsolete

Product Category : Network Diagnostic Tools

Engineering Number : DN-MTR



NO IMAGE AVAILABLE

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Network Diagnostic Tools
Series	112008
Description	NetMeter Hand Held Digital DeviceNet
Approvals	CE, CUL, UL certified
Comments	NetMeter; Measures 667 Parameters
IP Rating	N/A
Product Name	DeviceNet,NetMeter
Type	Hand Held Digital NetMeter
UPC	78172506708

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	7-30V DC

Physical

Cable Diameter	N/A
Communication Speed	125, 250, 500 Kbaud
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
I/O Connector	5-pole Micro-Change (M12)
Keyway	N/A
Material - Connector Body	N/A
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	343.360/g
Orientation	N/A
Poles	N/A
Temperature Range - Operating	0°C to +40°C

Wire Size (AWG)	N/A
-----------------	-----