

F

E

D

C

B

A

F



E

D


C

B






A



SECTION Z-Z



カプトンテープ付き
WITH KAPTON TAPE



嵌合図

MATED CONNECTORS

NOTES

- 嵌合相手: 502380-****
MATE WITH : 502380-****
- 端子テール部 及び ネイルの平坦度: 0.1MAX.
TAIL AND NAIL COPLANARITY TO BE 0.1 MAX.
- 極数/2=偶数に適用。
APPLY FOR CKT. SIZE / 2 = EVEN.
- 端子テール部 及び ネイルに錫めっきを使用しているため、
外觀に摺動痕が付く場合が御座います。
THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS
BECAUSE THE TIN PLATING IS USED FOR THA TAIL AND NAIL.
- 本製品のプラスチック部に黒点等が確認される場合や
色合いが異なる場合がありますが、製品性能に影響はありません。
THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH
THE BLACK SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC PART
OF THIS PRODUCT AND THE SHADE MIGHT BE DIFFERENT.
- ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT

3.4	7.5	11	12.1	502386-07**	7
3.4	6.25	9.75	10.85	502386-06**	6
3.4	5	8.5	9.6	502386-05**	5
3.4	3.75	7.25	8.35	502386-04**	4
2.6	2.5	6	7.1	502386-03**	3
2.2	1.25	4.75	5.85	502386-02**	2
D	C	B	A	EMBOSSSED TAPE PACKAGE オーダー番号 ORDER No.	極数 CKT. NO.

番号 NO.	部品 PART	材質 MATERIAL
①	ハウジング HOUSING	耐熱性樹脂 UL94V-0 色:SHEET 3 参照 HEATPROOF RESIN UL94V-0 COLOR : SEE SHEET 3
②	ターミナル TERMINAL	銅合金 COPPER ALLOY 錫めっき : 1.0 micro-meter MIN. TIN (TAIL AREA) ニッケルめっき (下地): 1.0 micro-meter MIN. NICKEL (UNDER PLATING)
③	ネイル NAIL	銅合金 COPPER ALLOY 錫めっき : 1.0 micro-meter MIN. TIN ニッケルめっき (下地): 1.0 micro-meter MIN. NICKEL (UNDER PLATING)

REVISED EC NO: J2013-0870 TDRWN:KAWASHIO CHKD:KASAKAWA APPR:Y01ITO	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	T.MIYAZAKI	2006/08/28	TITLE 1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.				
		10 OVER 30 UNDER	±0.25	K.ASAKAWA	2006/08/28					
		30 OVER	±0.3	Y01ITO	2006/08/28				molex	
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.	SHEET NO.			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-502386-001 1 OF 3				
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				




2 CKT.




3 CKT.




4 CKT.



5 CKT.




6 CKT.



7 CKT.


極数の種類

KIND OF CKT. NO.(FRONT VIEW)




吸着範囲
VACUME AREA

SECTION Y-Y





基板パターンレイアウト (参考)
RECCOMENDED P.C.B. PATTERN LAYOUT (REF.)



REVISED EC NO.: J2013-0870 DRWN:KASHIO CHKD:KASAKAWA APPR:Y01TO	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION				
		10 UNDER	±0.2	T.MIYAZAKI	DATE 2006/08/28	TITLE 1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.						
		10 OVER 30 UNDER	±0.25	K.ASAKAWA	DATE 2006/08/28							
		30 OVER	±0.3	APPROVED BY Y01.ITO	DATE 2006/08/28	molex						
		ANGULAR ±3 °		MATERIAL NO.						DOCUMENT NO.		SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE						SD-502386-001		2 OF 3
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								


	10	9	8	7	6	5	4	3	2	1																																																																																
F											F																																																																															
E											E																																																																															
D	<table><tr><td colspan="10">WITH CAPTON TAPE</td><td></td></tr><tr><td colspan="2">HSG COLOR : GREEN</td><td colspan="2">HSG COLOR : BLUE</td><td colspan="2">HSG COLOR : RED</td><td colspan="2">HSG COLOR : BLACK</td><td colspan="2">HSG COLOR : NATURAL</td><td></td></tr><tr><td>502386-0736</td><td rowspan="5">502386-**-16</td><td>502386-0734</td><td rowspan="5">502386-**-14</td><td>502386-0732</td><td rowspan="5">502386-**-12</td><td>502386-0731</td><td rowspan="5">502386-**-11</td><td>502386-0772</td><td rowspan="5">502386-**-08</td><td>7</td></tr><tr><td>502386-0636</td><td>502386-0634</td><td>502386-0632</td><td>502386-0631</td><td>502386-0672</td><td>6</td></tr><tr><td>502386-0536</td><td>502386-0534</td><td>502386-0532</td><td>502386-0531</td><td>502386-0572</td><td>5</td></tr><tr><td>502386-0436</td><td>502386-0434</td><td>502386-0432</td><td>502386-0431</td><td>502386-0472</td><td>4</td></tr><tr><td>502386-0336</td><td>502386-0334</td><td>502386-0332</td><td>502386-0331</td><td>502386-0372</td><td>3</td></tr><tr><td>502386-0236</td><td></td><td>502386-0234</td><td></td><td>502386-0232</td><td></td><td>502386-0231</td><td></td><td>502386-0272</td><td></td><td>2</td></tr><tr><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>極数 (KT. NO.)</td></tr></table>										WITH CAPTON TAPE											HSG COLOR : GREEN		HSG COLOR : BLUE		HSG COLOR : RED		HSG COLOR : BLACK		HSG COLOR : NATURAL			502386-0736	502386-**-16	502386-0734	502386-**-14	502386-0732	502386-**-12	502386-0731	502386-**-11	502386-0772	502386-**-08	7	502386-0636	502386-0634	502386-0632	502386-0631	502386-0672	6	502386-0536	502386-0534	502386-0532	502386-0531	502386-0572	5	502386-0436	502386-0434	502386-0432	502386-0431	502386-0472	4	502386-0336	502386-0334	502386-0332	502386-0331	502386-0372	3	502386-0236		502386-0234		502386-0232		502386-0231		502386-0272		2	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	極数 (KT. NO.)	D
WITH CAPTON TAPE																																																																																										
HSG COLOR : GREEN		HSG COLOR : BLUE		HSG COLOR : RED		HSG COLOR : BLACK		HSG COLOR : NATURAL																																																																																		
502386-0736	502386-**-16	502386-0734	502386-**-14	502386-0732	502386-**-12	502386-0731	502386-**-11	502386-0772	502386-**-08	7																																																																																
502386-0636		502386-0634		502386-0632		502386-0631		502386-0672		6																																																																																
502386-0536		502386-0534		502386-0532		502386-0531		502386-0572		5																																																																																
502386-0436		502386-0434		502386-0432		502386-0431		502386-0472		4																																																																																
502386-0336		502386-0334		502386-0332		502386-0331		502386-0372		3																																																																																
502386-0236		502386-0234		502386-0232		502386-0231		502386-0272		2																																																																																
EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	極数 (KT. NO.)																																																																																
C											C																																																																															
B	<table><tr><td colspan="10">WITHOUT CAPTON TAPE</td><td></td></tr><tr><td colspan="2">HSG COLOR : GREEN</td><td colspan="2">HSG COLOR : BLUE</td><td colspan="2">HSG COLOR : RED</td><td colspan="2">HSG COLOR : BLACK</td><td colspan="2">HSG COLOR : NATURAL</td><td></td></tr><tr><td>502386-0746</td><td rowspan="5">502386-**-26</td><td>502386-0744</td><td rowspan="5">502386-**-24</td><td>502386-0742</td><td rowspan="5">502386-**-22</td><td>502386-0741</td><td rowspan="5">502386-**-21</td><td>502386-0770</td><td rowspan="5">502386-**-09</td><td>7</td></tr><tr><td>502386-0646</td><td>502386-0644</td><td>502386-0642</td><td>502386-0641</td><td>502386-0670</td><td>6</td></tr><tr><td>502386-0546</td><td>502386-0544</td><td>502386-0542</td><td>502386-0541</td><td>502386-0570</td><td>5</td></tr><tr><td>502386-0446</td><td>502386-0444</td><td>502386-0442</td><td>502386-0441</td><td>502386-0470</td><td>4</td></tr><tr><td>502386-0346</td><td>502386-0344</td><td>502386-0342</td><td>502386-0341</td><td>502386-0370</td><td>3</td></tr><tr><td>502386-0246</td><td></td><td>502386-0244</td><td></td><td>502386-0242</td><td></td><td>502386-0241</td><td></td><td>502386-0270</td><td></td><td>2</td></tr><tr><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.</td><td>コネクタ シリズ CONNECTOR SIRIES</td><td>極数 (KT. NO.)</td></tr></table>										WITHOUT CAPTON TAPE											HSG COLOR : GREEN		HSG COLOR : BLUE		HSG COLOR : RED		HSG COLOR : BLACK		HSG COLOR : NATURAL			502386-0746	502386-**-26	502386-0744	502386-**-24	502386-0742	502386-**-22	502386-0741	502386-**-21	502386-0770	502386-**-09	7	502386-0646	502386-0644	502386-0642	502386-0641	502386-0670	6	502386-0546	502386-0544	502386-0542	502386-0541	502386-0570	5	502386-0446	502386-0444	502386-0442	502386-0441	502386-0470	4	502386-0346	502386-0344	502386-0342	502386-0341	502386-0370	3	502386-0246		502386-0244		502386-0242		502386-0241		502386-0270		2	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	極数 (KT. NO.)	B
WITHOUT CAPTON TAPE																																																																																										
HSG COLOR : GREEN		HSG COLOR : BLUE		HSG COLOR : RED		HSG COLOR : BLACK		HSG COLOR : NATURAL																																																																																		
502386-0746	502386-**-26	502386-0744	502386-**-24	502386-0742	502386-**-22	502386-0741	502386-**-21	502386-0770	502386-**-09	7																																																																																
502386-0646		502386-0644		502386-0642		502386-0641		502386-0670		6																																																																																
502386-0546		502386-0544		502386-0542		502386-0541		502386-0570		5																																																																																
502386-0446		502386-0444		502386-0442		502386-0441		502386-0470		4																																																																																
502386-0346		502386-0344		502386-0342		502386-0341		502386-0370		3																																																																																
502386-0246		502386-0244		502386-0242		502386-0241		502386-0270		2																																																																																
EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	EMBOSSSED TAPE PACKAGE オーダー番号ORDER No.	コネクタ シリズ CONNECTOR SIRIES	極数 (KT. NO.)																																																																																
A	<table><tr><td rowspan="5">REVISED EC NO: J2013-0870 DRAWN:KAWASHIO CHKD:KASAKAWA APPR:YO ITO 2013/02/07 2013/02/13 2013/02/13</td><td rowspan="5">DESCRIPTION</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE -----</td><td>DESIGN UNITS METRIC</td><td rowspan="5"> THIRD ANGLE PROJECTION</td></tr><tr><td>10 UNDER</td><td>± 0.2</td><td colspan="2">DRAWN BY DATE T.MIYAZAKI 2006/08/28</td><td colspan="2" rowspan="3">TITLE 1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.</td></tr><tr><td>10 OVER 30 UNDER</td><td>± 0.25</td><td colspan="2">CHECKED BY DATE K.ASAKAWA 2006/08/28</td></tr><tr><td>30 OVER</td><td>± 0.3</td><td colspan="2">APPROVED BY DATE YO. ITO 2006/08/28</td></tr><tr><td colspan="2">ANGULAR ±3 °</td><td colspan="2">MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SIZE A3</td><td colspan="6">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>										REVISED EC NO: J2013-0870 DRAWN:KAWASHIO CHKD:KASAKAWA APPR:YO ITO 2013/02/07 2013/02/13 2013/02/13	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE -----	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	10 UNDER	± 0.2	DRAWN BY DATE T.MIYAZAKI 2006/08/28		TITLE 1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.		10 OVER 30 UNDER	± 0.25	CHECKED BY DATE K.ASAKAWA 2006/08/28		30 OVER	± 0.3	APPROVED BY DATE YO. ITO 2006/08/28		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						A																																						
REVISED EC NO: J2013-0870 DRAWN:KAWASHIO CHKD:KASAKAWA APPR:YO ITO 2013/02/07 2013/02/13 2013/02/13	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE -----	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION																																																																																		
		10 UNDER	± 0.2	DRAWN BY DATE T.MIYAZAKI 2006/08/28		TITLE 1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.																																																																																				
		10 OVER 30 UNDER	± 0.25	CHECKED BY DATE K.ASAKAWA 2006/08/28																																																																																						
		30 OVER	± 0.3	APPROVED BY DATE YO. ITO 2006/08/28																																																																																						
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.			SHEET NO.																																																																																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																						
tb_frame_A3_J_ME_S Rev G 2012/01/25	9	8	7	6	5	4	3	2																																																																																		



NOTES

- 製品詳細寸法については、SD-502386-001, -002 を参照下さい。
PLEASE REFER TO SD-502386-001, -002 FOR THE DETAILED DIMENSION OF THE CONNECTOR.
- 梱包数量 : 1200個
NUMBER OF CONNECTIORS : 1200 PIECES/REEL.
- リードテープ長さ
LEAD TAPE LENGTH

トップテープ接着部 (空エンボス)
20 PIECES MIN.



- 材料
MATERIAL
キャリアテープ : ポリスチレン
CARRIER TAPE : POLYSTYRENE
トップテープ : ポリエステル、ポリエチレン、ポリエチレンテレフタレート
TOP TAPE : POLYESTER, POLYETHLENE, POLYETHYLENE TEREPHTHALATE
リール : ポリスチレン <リサイクル材を含む>
REEL : POLYSTYRENE <RECYCLE MATERIAL CONTAINED>

- ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT

45.5	20.2	44	502386-15**	15
45.5	20.2	44	502386-14**	14
33.5	14.2	32	502386-13**	13
33.5	14.2	32	502386-12**	12
33.5	14.2	32	502386-11**	11
33.5	14.2	32	502386-10**	10
25.5	11.5	24	502386-09**	9
25.5	11.5	24	502386-08**	8
25.5	11.5	24	502386-07**	7
25.5	11.5	24	502386-06**	6
25.5	11.5	24	502386-05**	5
25.5	11.5	24	502386-04**	4
17.5	7.5	16	502386-03**	3
17.5	7.5	16	502386-02**	2
C	B	エンボステープ幅 A WIDTH OF TAPE	製品番号 MATERIAL NO.	極数 CKT. NO.

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
		DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#513389.				molex					
		mm		NTS											
10 UNDER		± 0.2		GENERAL TOLERANCES (UNLESS SPECIFIED)						EC NO: 781755 DRWN: RAVINR1 CHK'D: GGA APPR: GGA 2024/03/14 2024/04/10 2024/04/10					
10 OVER 30 UNDER		± 0.25		ANGULAR TOL ± 30 °											
30 OVER		± 0.3		4 PLACES ± 0.2											
				3 PLACES ± 0.25		INITIAL REVISION: DRWN: TMIYAZAKI APPR: YOITO 2006/10/16 2006/10/16				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
				2 PLACES ± 0.3						PRODUCT CUSTOMER DRAWING					
				1 PLACE ±											
				0 PLACES ±											
ANGULAR ± 3 °				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A3-SIZE	502386	SEE TABLE		GENERAL MARKET		1 OF 2			
										SD-502386-003		PSD	001	F1	

[illegible]

F

E

D

C

B

A

F



E

D



C

B




A



SECTION Z-Z



カプトンテープ付き
WITH KAPTON TAPE



嵌合図
MATED CONNECTORS

NOTES

1. 嵌合相手: 502380-****
MATE WITH : 502380-****
2. 端子テール部 及び ネイルの平坦度: 0.1MAX.
TAIL AND NAIL COPLANARITY TO BE 0.1 MAX.
3. 極数/2=偶数に適用.
APPLY FOR CKT. SIZE / 2 = EVEN.
4. 端子テール部 及び ネイルに錫めっきを使用しているため、
外觀に摺動痕が付く場合が御座います。
THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS
BECAUSE THE TIN PLATING IS USED FOR THA TAIL AND NAIL.
5. 本製品のプラスチック部に黒点等が確認される場合や
色合いが異なる場合がありますが、製品性能に影響はありません。
THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH
THE BLACK SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC PART
OF THIS PRODUCT AND THE SHADE MIGHT BE DIFFERENT.
6. ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT


番号 NO.	部品 PART	材質 MATERIAL
①	ハウジング HOUSING	耐熱性樹脂 UL94V-0 色: ナチュラル HEATPROOF RESIN UL94V-0 COLOR : NATURAL
②	ターミナル TERMINAL	銅合金 COPPER ALLOY 金めっき : 0.1 micro-meter MIN. GOLD ニッケルめっき (下地): 1.0 micro-meter MIN. NICKEL (UNDER PLATING)
③	ネイル NAIL	銅合金 COPPER ALLOY 錫めっき: 1.0 micro-meter MIN. TIN ニッケルめっき (下地): 1.0 micro-meter MIN. NICKEL (UNDER PLATING)

3.4	7.5	11	12.1	502386-0707	7
3.4	6.25	9.75	10.85	502386-0607	6
3.4	5	8.5	9.6	502386-0507	5
3.4	3.75	7.25	8.35	502386-0407	4
2.6	2.5	6	7.1	502386-0307	3
2.2	1.25	4.75	5.85	502386-0207	2
D	C	B	A	EMBOSSSED TAPE PACKAGE オーダー番号 ORDER No.	極数 CKT. NO.

RELEASED EC NO: J2016-0012 DRWN: TAKAIKE 2015/02/23 CHKD: KASAKAWA 2015/07/21 APPR: NUKITA 2015/07/21	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
		0.25 UNDER UNDER ±0.03			DRAWN BY DATE		TITLE		1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.		molex	
		0.25 OVER 0.5 UNDER ±0.05			TAKAIKE 2015/02/23							
		0.5 OVER 1.0 UNDER ±0.1			CHECKED BY DATE							
		1.0 OVER 10 UNDER ±0.2			KASAKAWA 2015/07/21							
10 OVER 30 UNDER ±0.25			APPROVED BY DATE		NUKITA 2015/07/21		DOCUMENT NO.		SHEET NO.			
30 OVER ±0.3			MATERIAL NO.		SEE TABLE		SD-502386-006		1 OF 2			
ANGULAR ±3 °			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												




2 CKT.




5 CKT.




3 CKT.



6 CKT.




4 CKT.




7 CKT.


極数の種類
KIND OF CKT. NO.(FRONT VIEW)




吸着範囲
VACUME AREA



SECTION Y-Y



基板パターンレイアウト (参考)
RECCOMENDED P.C.B. PATTERN LAYOUT (REF.)



RELEASED EC NO: J2016-0012 DRWN: TAKAIKE CHKD: KASAKAWA APPR: NUKITA A	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
		0.25 UNDER UNDER ± 0.03			DRAWN BY DATE		TITLE 1.25 W/B CONN. SINGLE R/A REC. ASS'Y 2-7CKT.							
		0.25 OVER 0.5 UNDER ± 0.05			TAKAIKE 2015/02/23									
		0.5 OVER 1.0 UNDER ± 0.1			CHECKED BY DATE									
		1.0 OVER 10 UNDER ± 0.2			KASAKAWA 2015/07/21									
		10 OVER 30 UNDER ± 0.25			APPROVED BY DATE									
	30 OVER 30 UNDER ± 0.3			NUKITA 2015/07/21		molex								
	ANGULAR ±3 °			MATERIAL NO.							DOCUMENT NO.		SHEET NO.	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE							SD-502386-006		2 OF 2	
				SIZE A3							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			