



Product data sheet

Power tools for trade & industry

Polisher

PRO GPO 12V-77



Polishing precision the easy way

The most important data

No-load speed	600 – 2,200 rpm
Polishing sponge, diameter	77 mm

Part Number 0 601 9L3 003

Technical data

Technical data

No-load speed	600 – 2,200 rpm
Rubber sanding plate, diameter	77 mm
Polishing sponge, diameter	77 mm
Packaging dimensions (width x length x height)	208 x 341 x 111 mm
Battery voltage, works with	12.0 V

Noise/vibration information

Polishing

Vibration emission value ah	0.6 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Consistent performance thanks to brushless motor
- Convenient and flexible with variable speed trigger for fine adjustment
- Comfortable to use with locking switch for fatigue-free continuous operation
- Compact and ergonomic design makes removing deep scratches and polishing small, hard-to-reach areas easy

**HEAVY
DUTY**

Ø 77 mm

600–
2200
min⁻¹/rpmSPEED
SELECTIONCONSTANT
SPEEDUSER
INTERFACE

ERGONOMIC

BRUSHLESS
MOTORL-BOXX
READY

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

