


H-AA1800H Specifications



Nominal Capacity	1800mAh
Nominal Voltage	1.2V
Internal Impedance (at 1000Hz)	<20mΩ
Charge	
Standard Charge	180mA x 16h
Trickle Charge	90mA x 48m
Discharge Cut-off Voltage	1.0V
Max Dimension (without tube)	
D	14.20±0.10mm
d	6.60±0.08mm
H	49.20±0.50mm
h	48.50±0.50mm
Weight	28.5g
Operating Temperature	
Standard charge	0 ~ 70℃
Trickle charge	0 ~ 70℃
Discharge	-20 ~ 70℃
Storage Temperature	-20 ~ 55℃

