


380 Push Button Snap Action Switches 16(4)A 250Vac



383 2510 K BL



383 2510 RR 383 2510 PR

- ▶ Snap action switches
- ▶ Ratings up to 16A, 250Vac
- ▶ Round and rectangular buttons



RoHS

16(4)A 250Vac 5E4 T85

16A 125/250Vac 3/4hp T85 50E3

125V 1/2 HP, 250V 3/4 HP, 0.4A 125Vdc, 0.2A 250Vdc

RoHS compliant

Approvals apply to switch mechanism only.
μ contact gap.

Blank for switch only

E	R	B								
Red	Red	Black								
P	R	B								
Red	Red	Black								
K	R	B	BL	G	W					
Red	Red	Black	Blue	Green	White					
R	R	B	BL	G	W					
Red	Red	Black	Blue	Green	White					
M	R	B	BL	G	W					
Red	Red	Black	Blue	Green	White					


383 2510 K BL
 TERMINAL FUNCTION ACTUATOR ACTUATOR
 CODE CODE CODE COLOR

▶ **ORDER FORMAT**


▶ TERMINAL	▶ FUNCTION	▶ ACTUATOR	BODY	▶ OPTIONS
383 	ON - ON (momentary 1 side)	R Rectangular bezel P Short K with satin chrome bezel M with nylon bezel	Panel Cut-out Panel thickness Both nuts 2.5mm No backnut 4.0mm	Color Call factory for custom colors A full range is available for large orders

Dimensions (mm)

R



P & E



K & M

