

0021800	DATA SHEET	
valid from: 01.01.2019	ÖLFLEX® ROBUST 200	

Application

ÖLFLEX® ROBUST 200 cables are power cables for flexible use and fixed installation for a robust mechanical use. They are suitable for use in dry, damp and wet rooms. They are suitable for outdoor use if the indicated temperature range is observed. At room temperature, they are increased resistant to the effects of acids, alkalis and oils, as well as greases and plant-, animal-, mineral- or synthetic-based waxes. They are suitable for constant use in fresh water to a depth of 10 m and at a maximum water temperature of 40°C according to EN 50565-2. They are suitable for occasional, non-automated movements. The maximum tensile load is 15 N/mm² of conductor cross-section during installation and operation. Compulsory guidance is not permitted. All materials used are halogen-free.

Application range

ÖLFLEX® ROBUST 200 cables are used as flexible power cable in machine tool building, in medical technology, in laundries, in car washing equipment, in chemical industry, in composting plants, in sewage works and submersible pumps. They are for use in the food and beverage industry, especially for production and processing equipment of milk and meat products.

Design

Design	based on EN 50525-2-51 resp. VDE 0285-525-2-51
Conductor	fine wire strands of bare copper, acc. to IEC 60228 resp. VDE 0295, Class 5
Insulation	modified PP-compound
Core identification code	up to 5 cores: acc. to VDE 0293-308 from 6 cores: black cores with white numbers with or without GN/YE ground conductor acc. to DIN EN 50334 resp. VDE 0293-334
Outer sheath	special TPE-compound colour: black, similar RAL 9005

Electrical properties at 20°C

Rated voltage	U ₀ / U:	450 / 750 V
Test voltage	Core/Core:	4000 V AC

Mechanical and thermal properties

Minimum bending radius	occasional flexing: 10 x outer diameter fixed installation: 4 x outer diameter
Temperature range	occasional flexing: -40 °C up to +80 °C max. conductor temperature fixed installation: -50 °C up to +80 °C max. conductor temperature
UV resistance	acc. to EN 50618 resp. VDE 0283-618 acc. to EN 50620 resp. VDE 0285-620 acc. to EN ISO 4892-2-2013, method A (change of colour allowed)
Ozone resistance	acc. to EN 50396 resp. VDE 0473-396, method B
Oil resistance	TM5 gemäß EN 50363-4-1 bzw. VDE 0207-363-4-1
Water-resistance	acc. to EN 50525-2-21 resp. VDE 0285-525-2-21
Tests	acc. to IEC 60811 resp. VDE 0473, VDE 0472, EN 50395, EN 50396
General requirements	These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive)

Creator: LABU / PDC	Document: DB0021800EN	Page 1 of 1
Released: ALTE / PDC	Version: 07	