


Pushbutton switch**Version 01/24**

6MAX: means the panel thickness, the max thickness for the panel no more than 6mm.

Specification

Switch rating.....	2A/36VAC/DC
Mounting diameter.....	12mm
Head shape	Round raised head
Operation type.....	1NO latching
Illumination type	Ring illumination
LED voltage.....	12V/DC
Terminal	Pin terminal (2X0.5mm)
Operating and storage temperature	-25 to +55°C
Operating and storage humidity	45 to 85 % RH
Material.....	Stainless steel
Mechanical life.....	500,000 cycles
Electrical life	50,000 cycles
Dielectric strength.....	1,500V, RMS 50Hz, 1min.
Protection class.....	IP67
Actuating force	2.5 N
Insulation resistance.....	≥ 1000 MΩ (500 V DC)
transitional resistance.....	≤ 50 mΩ

	LED Color
92106c194	Red
92106c195	Green

Data Sheet



92106c196	Yellow
92106c197	Blue
92106c198	White