

SL 83

Art. No. 2278 – 4 Ω



Technische Daten / Technical Data

Nennbelastbarkeit Rated power	8 W
Impedanz Impedance	4 Ω
Mittlerer Schalldruckpegel Mean sound pressure level	88 dB (1 W/1 m)
Übertragungsbereich (-10 dB) Frequency response (-10 dB)	130–16.000 Hz
Resonanzfrequenz Resonant frequency	250 Hz
Obere Polplattenhöhe Height of front pole-plate	3 mm
Schwingspuldurchmesser Voice coil diameter	16,5 mm
Wickelhöhe Height of winding	4,6 mm
Schallwandöffnung Cut-out diameter	72 mm
Anschluss Terminal	4,8 x 0,8/2,8 x 0,8 mm
Gewicht netto Net weight	252 g

8 cm (3.3") Breitbandlautsprecher mit Kunststoffmembran und Ferritmagnet optimiert für anspruchsvolle Umweltbedingungen.


Anwendungsmöglichkeiten:

- AVAS Systeme
- Schallzeilen

8 cm (3.3") full-range speaker with plastic cone and ferrite magnet optimized for demanding environmental conditions.

Typical applications:

- AVAS Systems
- Column speakers



Directivity pattern

