

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

LI-ION (AAA) RECHARGEABLE BATTERY




Item No.: 3628515 (8 PCS)


TECHNICAL DATA

Type	AAA
Model	10430 / Round Cell
Chemical system	Li-ion
Nominal output voltage	1.5 V
Capacity	Nominal: 1250 mAh Discharge at 0.2C (250mA): 1200 mAh Discharge at 0.5C (625mA): 1150 mAh Minimum: 1150 mAh
Rated energy	1.925 Wh
Supply voltage	5 V ± 0.25 V
Charge current	100 mA $\pm 10\%$
Lifetime expectance	≥ 1500 cycles (at 0.2C discharge rate, C > 70% of min. capacity)
Ambient temperature range:	Charge: 0 to +45 °C Discharge: -10 to +60 °C
Storage time (full battery)	Max. 36 months: -20 to +25 °C Max. 12 months: -20 to +45 °C

DISCHARGE RATE



DIMENSIONS



Ø d1	10.5 - 0.7 mm
Ø d2	3.2 ± 0.5 mm
h1	44.5 - 1 mm
h2	1.3 ± 0.5 mm
Weight	9 ± 1 g

