

Transfer or duplication of this document as well as the utilization or communication of its contents are prohibited unless explicit authorization is granted. Violations will be liable for compensation. All rights reserved for patent, utility model or designs registrations. 除经给予明确授权外, 否则禁止转让、复制、利用、交流本文档的内容。未经授权的复制或通信, 使用模型和外观专利的所有权利。

FOR-1759 Rev.2.1

2

3

4




5

6

7

8

未注公差/General tolerances(mm)													
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	0.1/10
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50
													



2	Screw	Steel	Ni Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES
间距/Pitch(mm)/线数范围/Poles			9.00/N=02P
使用温度范围/Operating temperature(°C)			-40~+105
符合RoHS环保要求/Conform to RoHS			Yes

		MATERIAL:		SURFACE/COLOR:		
		MAT NO./REV:		MAT STATUS: 小批量		
APPD: 蓝贵凡		2024.07.05		NAME DGBSC-ACC03-02P-11-01Z(H)		
CHKD: 朱伟明		2024.07.05				
DRFT: 孙科豪		2024.07.05				
 A3						
		DRAWING NO. 200315375		TYPE CUSTOMER DRAWING		DRAWING STATUS 已发布
				SCALE 1:1		SHEET 1/1

00				
REV	ECN	DESCRIPTION	DRFT	DATE

1

2

3

4

5

6

7

8