

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

BS-807

WINDABLE BORESCOPE CAMERA



Item no. 3733409

FEATURES

1280 x 720 camera // 20 m gooseneck // 8 LEDs // IP67 (camera and neck)

TECHNICAL DATA

Compatible endoscopes (item no.)	3553223 / 3553224 / 3553225
Camera Head Dia.	10 mm
Resolution	1280 x 720 px
Sensor	1/9" HD CMOS
Field of View (FOV)	87°
Fixed Focus	20 - 80 mm
Min. bending radius	45 mm
LEDs	8 (brightness adjustable)
LED brightness (at a distance of 35 mm)	1500 ±150 lux
Ingress protection	IP67 (camera head and camera neck)
Operating temperature	0 to +45 °C
Operating humidity	15 - 85 % RH
Storage temperature	-10 to +50 °C
Storage humidity	15 - 85 % RH
Gooseneck length	20 m
Reel dimensions (Ø x W)	29.7 x 11.5 cm
Weight	1465 g



PACKAGE CONTENTS

Camera reel with camera // Extension cable // Operating instructions