



LogiLink®

Magnetic Phone Holder with Vacuum Suction Cup

Art. No.: AA0198



Fully Adjustable. Perfectly Secure.

Designed for flexibility and convenience, this phone holder offers a 360° rotating base and 180° dual-axis folding arms for precise viewing angles. Switch seamlessly between portrait and landscape modes at home, in the office, or in the car. Its foldable design keeps the mount compact when not in use, and the twist-lock vacuum suction ensures a secure, dependable hold.



Strong
Magnet



Adjust to
Any Angle



Vacuum
Suction



Twist
Lock



Foldable
Design



For Car
Home & Office



Universally Compatible

Built-in industrial grade N52H magnets with strong holding force up to 250 g to keep smartphones securely intact, even when driving on bumpy roads, the phone does not fall off.

Works with MagSafe compatible smartphones/cases, and if your smartphone or case does not have the magnetic suction, you can attach the included metal ring to the case.



Strong Suction with Manual Rotation Enhancement

Twist-lock vacuum suction ensures a firm and secure hold on smooth surfaces.

Also include multi-surface adhesive pad for extra support.



Adjustable to Any Angle

With joints that can be rotated and tilted, so you can position your smartphone at the optimal viewing angle at any time, according to your needs.



Foldable and Space-Saving

Fold the phone holder to be stored, save space and easily take it anywhere. Ideal for travel, business trips or daily use in the car.

Specifications:

Dimensions	4.4 x 5.9 x 5.9 cm
Weight	89 g
Application	Windshield, screen, glass, mirror, kitchen, bathroom, gym, treadmill *Not suitable for rough cement, seam area, curved surfaces
Magnetic Force	1.6 KGF/16N (with MagSafe case)
Material	ABS
Color	Black/bronze

Package Contents:

- » 1 x Magnetic Phone Holder
- » 1 x Adhesive Metal Ring
- » 1 x Round PC pad
- » 1 x Alcohol Prep Pad
- » 1 x User Manual

Package Information:

- » Packing Dimension: 82 x 63 x 88 mm
- » Packing Weight: 0.128 kg
- » Carton Dimension: 435 x 335 x 198 mm
- » Carton Q'ty: 50 pcs
- » Carton Weight: 6.73 kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



AA0198



Made in China