


Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	Arozzi			
	Supplier's address.	Arozzi Europe AB, Transformatorgatan 9, 59535 MJÖLBY, SE			
2.	Model identifier	AZ-NO-34T2K165			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	F			
4.	On mode power demand in SDR	29,6			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	F			
6.	On mode power demand in HDR, if implemented	29,8			W
7.	Off mode, power demand, if applicable	0,3			W
8.	Standby mode power demand, if applicable	0,5			W
9.	Networked standby mode power demand, if applicable	2,0			W
10.	Electronic display category	Monitor			
11.	Size ratio	21	:	9	
12.	Screen resolution	3 440	x	1 440	pixels
13.	Screen diagonal	87,0			cm
14.	Screen diagonal	34			inches
15.	Visible screen area	26,6			dm²
16.	Panel technology used	LCD			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	165			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	3			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	3			Years
23.	Minimum guaranteed product support	3			Years
	Minimum duration of the general guarantee offered by the supplier	2			Years
24.	Power supply type	External			
25.	External power supply (non standardized and included in the product box)				
	i	DC12V,5A			
	ii	Input voltage	-		V

	<i>iii</i>	Output voltage	-	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

Model placed on the Union market from 10/04/2025



EPREL registration number: 2326577

<https://eprel.ec.europa.eu/qr/2326577>

Supplier: Arozzi Europe AB (Manufacturer)

Website:

Customer care service:

Name: Arozzi Europe AB

Website:

Email: info@arozzi.com

Phone: +46702612832

Address:

Transformatorgatan 9
59535 MJÖLBY
Sweden