




Bauteile

LED and Carbon- film resistor assortment
 Assortiment de LED et Résistances de carbone
 Assortiment LED en Koollaagweerstanden

LED und Kohleschicht-Widerstände Sortiment



Inhalt:

ø 3mm LED		
Farbe	lv. typ.	Winkel °
Rot	80mcd	30°
Grün	40mcd	35°
Gelb	30mcd	35°
Blau	2000mcd	20°
Weiß	1200mcd	25°
Je 10 Stück		
ø 5mm LED		
Farbe	lv. typ.	Winkel °
Rot	70mcd	35°
Grün	80mcd	35°
Gelb	80mcd	35°
Blau	1000mcd	12°
Weiß	3000mcd	12°
Je 10 Stück		
Kohleschicht-Widerstände		
10Ω	47Ω	68Ω 150Ω 220Ω
Je 20 Stück		
LED Fassung		
3mm , 5mm		
Je 20 Stück		



Contents:

ø 3mm LED		
Color	lv. typ.	Angle °
Red	80mcd	30°
Green	40mcd	35°
Yellow	30mcd	35°
Blue	2000mcd	20°
White	1200mcd	25°
10pcs. each		
ø 5mm LED		
Color	lv. typ.	Angle °
Red	70mcd	35°
Green	80mcd	35°
Yellow	80mcd	35°
Blue	1000mcd	12°
White	3000mcd	12°
10pcs. each		
Carbon-film resistor		
10Ω	47Ω	68Ω 150Ω 220Ω
20pcs. each		
LED Holder		
3mm , 5mm		
20pcs. each		



Contenu:

ø 3mm LED		
Couleur	lv. typ.	Angle °
Rouge	80mcd	30°
Vert	40mcd	35°
Jaune	30mcd	35°
Bleu	2000mcd	20°
Blanc	1200mcd	25°
Resp. 10 pièces		
ø 5mm LED		
Couleur	lv. typ.	Angle °
Rouge	70mcd	35°
Vert	80mcd	35°
Jaune	80mcd	35°
Bleu	1000mcd	12°
Blanc	3000mcd	12°
Resp. 10 pièces		
Résistances de carbone		
10Ω	47Ω	68Ω 150Ω 220Ω
Resp. 20 pièces		
LED Monture		
3mm , 5mm		
Resp. 20 pièces		




Inhoud:


ø 3mm LED		
Kleur	lv. typ.	Hoek °
Rood	80mcd	30°
Groen	40mcd	35°
Geel	30mcd	35°
Blauw	2000mcd	20°
Wit	1200mcd	25°
per 10 stuks		
ø 5mm LED		
Kleur	lv. typ.	Hoek °
Rood	70mcd	35°
Groen	80mcd	35°
Geel	80mcd	35°
Blauw	1000mcd	12°
Wit	3000mcd	12°
per 10 stuks		
Koolfilmweerstn		
10Ω	47Ω	68Ω 150Ω 220Ω
per 20 stuks		
LED Houder		
3mm , 5mm		
per 20 stuks		




Resistor Color Code Guide



LED 3mm



LED 5mm



NOTE: _____

LED ø3mm	LED ø3mm	LED ø3mm	LED ø3mm	LED ø3mm	LED ø5mm	LED ø5mm	LED ø5mm	LED ø5mm	LED ø5mm
Rot	Grün	Gelb	Blau	Weiß	Rot	Grün	Gelb	Blau	Weiß
Red	Green	Yellow	Blue	White	Red	Green	Yellow	Blue	White
Rouge	Vert	Jaune	Bleu	Blanc	Rouge	Vert	Jaune	Bleu	Blanc
Rood	Groen	Geel	Blauw	Wit	Rood	Groen	Geel	Blauw	Wit
Angle:typ. 30° Iv:typ. 80mcd I _f :20mA / U _f :2V	Angle:typ. 35° Iv:typ. 40mcd I _f :20mA / U _f :22V	Angle:typ. 35° Iv:typ. 30mcd I _f :20mA / U _f :21V	Angle:typ. 20° Iv: typ.2000mcd I _f :20mA / U _f :35V	Angle:typ. 25° Iv: typ.1200mcd I _f :20mA / U _f :35V	Angle:typ. 35° Iv:typ.70mcd I _f :30mA / U _f :2V	Angle:typ. 35° Iv:typ. 80mcd I _f :30mA / U _f :22V	Angle:typ. 35° Iv: typ. 80mcd I _f :30mA / U _f :21V	Angle:typ. 12° Iv:typ.1000mcd I _f :20mA / U _f :26V	Angle:typ. 12° Iv:typ.3000mcd I _f :20mA / U _f :35V
10Ω 1/4W ±5%	47Ω 1/4W ±5%	68Ω 1/4W ±5%	150Ω 1/4W ±5%	220Ω 1/4W ±5%	470Ω 1/4W ±5%	680Ω 1/4W ±5%	1k Ω 1/4W ±5%	<u>LED ø3mm</u> LED Fassung LED Holder LED Monture LED Houder	<u>LED ø5mm</u> LED Fassung LED Holder LED Monture LED Houder