



Deutsch



English



Español



Français



Nederlands



Polski



Русский


Kemo[®]

Electronic

M032S

UNIVERSAL AMPLIFIER 12W
"PLUG & PLAY"

UNIVERSAL AMPLIFIER 12W
"PLUG & PLAY"



Brilliant output signal!

M032S | Universal Verstärker 12 W „Plug & Play“

Verstärkermodul mit Buchsen für den Signaleingang und für die Stromversorgung. Eingebauter Lautstärkeregler, Lautsprecheranschluss über Kabel.

Technische Daten:

Betriebsspannung: 8 - 16 V/DC | **Stromaufnahme:** max. 800 mA | **Eingangsempfindlichkeit:** <80 mV | **Lautsprecheranschluss:** 4 - 16 Ohm | **Musikleistung:** max. 12 W bei 16 V an einem 4 Ohm Lautsprecher | **Frequenzgang:** ca. 40 - 20.000 Hz | **Stromversorgungsbuchse:** für Netzstecker 2,1 mm


M032S | Universal Amplifier 12 W “Plug & Play”

Amplifying module with jacks used for the signal input and for the power supply. Inserted loudspeaker regulator and loudspeaker connection are over the cables.

Technical data:

Operating voltage: 8 - 16 V/DC | **Current consumption:** max. 800 mA | **Input sensitivity:** <80 mV | **Loudspeaker connection:** 4 - 16 ohm | **Music power:** max. 12 W with 16 V at a 4 ohm loudspeaker | **Frequency response:** approx. 40 - 20.000 Hz | **Power supply jack:** for mains plug 2.1 mm

ES Amplificador Universal 12 W “Plug & Play” | **FR** Amplificateur universel 12 W « Plug & Play » | **NL** Universeel versterker 12 W “Plug & Play” | **PL** Wzmocniacz uniwersalny 12 W „Plug & Play“ | **RU** Универсальный усилитель 12 Ватт «Plug & Play»



Dimensions:
approx. 73 x 60 x 43 mm
(without fixing straps)

Lieferbares Zubehör / Available accessory:
M040N Universal-Vorverstärker /
M040N Universal preamplifier

191512

www.kemo-electronic.de



Kemo Electronic GmbH
Leher Landstrasse 20
27607 Geestland, Germany

P / Module / M032S / Ver.005 / KV008