

Symbol Pro Serie

1

High fidelity
for IN-and OUTDOOR



Symbol Pro 110- Schwarz / black



Symbol Pro 130 - Weiß/white



Symbol Pro 160 Schwarz / black

Home HiFi

Magnet[®]

Symbol Pro Serie

2



Besonderheiten

- Kompakte Regalbox mit resonanzarmen, glasverstärktem ABS Gehäuse
- Auch geeignet für Feuchträume und Außenbereich
- Magnetisch abgeschirmt
- Magnesium-Hochtonkalotte
- tieftöner mit stabiler Polypropylenmembran
- Vergoldete Schraubanschlüsse
- stabile Wandhalterung, horizontal und vertikal stufenlose verstellbar
- Dynamische Überlastsicherung

Highlights

- Bookshelf speaker with low resonant ABS (galsfibre-filled) cabinet
- Ready for outdoor use
- Magnetically shielded
- Magnesium Tweeter-dome
- Woofer with stiff polypropylene membrane
- Gold plated screw terminal
- Horizontal and vertical adjustable heavyduty wallmount device
- Dynamic overload-protection

Home HiFi

Magnat®

Symbol Pro 110



Schwarz / black:
Weiss / white:

Art.-Nr: 160 110 EAN:40 18843 6811 08
Art.-Nr: 160 210 EAN:40 18843 6821 05

Technische Daten

- Konfiguration 2-Wege Regallautsprecher / Bassreflex
- Belastbarkeit RMS / max. 60 / 150 Watt
- Impedanz 4-8 Ohm
- Frequenzbereich 40 - 30.000 Hz
- Übergangsfrequenz 4.000 Hz
- Empfohlene Verstärkerleistung 20 - 150 Watt
- Wirkungsgrad (1 Watt / 1 m) 89 dB
- Maße (B x H x T) 120 x 205 x 160 mm ohne Wandhalter
- Ausführung Schwarz und Weiss

Specifications

- configuration 2-way book shelf speaker/ bass reflex
- power handling RMS / max. 60 / 150 watts
- impedance 4-8 ohms
- frequency response 40 - 30,000 Hz
- crossover frequency 4,000 Hz
- recommended amplifier output 20 - 150 watts
- sensitivity (1 Watt / 1m) 89 dB
- dimensions (W x H x D) 120 x 205 x 160 mm without wallmount device
- cabinet surface black and white

Home HiFi

Magnat®

Symbol Pro 130

4

Schwarz / black:
Weiss / white:

Art.-Nr: 168 600
Art.-Nr: 168 601

EAN:40 18843 68600 4
EAN:40 18843 68601 1

Technische Daten

- Prinzip 2-Wege Bassreflex Regallautsprecher / bassreflex
- Belastbarkeit RMS / max. 80 / 200 Watt
- Impedanz 4-8 Ohm
- Frequenzbereich 35 - 30.000 Hz
- Übergangsfrequenz 4.000 Hz
- Empfohlene Verstärkerleistung 20 - 200 Watt
- Wirkungsgrad (1 Watt / 1 m) 90 dB
- Maße (B x H x T) 151 x 255 x 215 mm ohne Wandhalter
- Ausführung Schwarz und Weiss
- Gewicht 3,0 kg inkl. Wandhalter

Specifications

- configuration 2-waybook shelf speaker / bass reflex
- power handling RMS / max. 80/ 200 watts
- impedance 4-8 ohms
- frequency response 35 - 30,000 Hz
- crossover frequency 4,000 Hz
- recommended amplifier output 20 - 200 watts
- sensitivity (1 Watt / 1m) 90 dB
- dimensions (W x H x D) 151 x 255 x 215 mm without wallmount device
- cabinet surface black and white
- Weight 3.0 kg inclusive wallmount device

Home HiFi

Magnat®

Symbol Pro 160



Schwarz / black:
Weiss / white:

Art.-Nr: 168 160 EAN:40 18843 68160 3
Art.-Nr: 168 260 EAN:40 18843 68260 0

Technische Daten

- Prinzip 2-Wege Regallautsprecher / bassreflex
- Belastbarkeit RMS / max. 100 / 225 Watt
- Impedanz 4-8 Ohm
- Frequenzbereich 30 - 30.000 Hz
- Übergangsfrequenz 4.000 Hz
- Empfohlene Verstärkerleistung 20 - 225 Watt
- Wirkungsgrad (1 Watt / 1 m) 92 dB
- Maße (B x H x T) 180 x 310 x 240 mm ohne Wandhalter
- Ausführung Schwarz und Weiss

Specifications

- configuration 2-waybook shelf speaker / bass reflex
- power handling RMS / max. 100 / 225 watts
- impedance 4-8 ohms
- frequency response 30 - 30,000 Hz
- crossover frequency 4,000 Hz
- recommended amplifier output 20 - 225 watts
- sensitivity (1 Watt / 1m) 92 dB
- dimensions (W x H x D) 180 x 310 x240 mm without wallmount device
- cabinet surface black and white

Home HiFi

Magnat®